# **PHILIPS** Lighting



# **PL-T Triple 4-Pin Base**

# PL-T 32W/830/A/4P/ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum effciency and sleek design solutions are required.

#### Product data


General Information	
Cap-Base	GX24Q-3 [ GX24q-3]
LSF Preheat 2000 h Rated	99 %
LSF Preheat 4000 h Rated	98 %
LSF Preheat 6000 h Rated	97 %
LSF Preheat 8000 h Rated	90 %
Light Technical	
Color Code	830 [ CCT of 3000K]
Luminous Flux (Nom)	2250 lm
Luminous Flux (Rated) (Nom)	2250 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	68.2 lm/W
Color Rendering Index (Nom)	>80
LLMF 2000 h Rated	92 %
LLMF 4000 h Rated	88 %
LLMF 6000 h Rated	85 %
LLMF 8000 h Rated	84 %
LLMF 12000 h Rated	81 %

Operating and Electrical	
Power (Rated) (Nom)	33.0 W
Lamp Current (Nom)	0.320 A
Temperature	
Design Temperature (Nom)	28 °C
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-Base Information	4P
Approval and Application	
Mercury (Hg) Content (Nom)	1.4 mg
Desiduat Data	
Product Data	
Order product name	PL-T 32W/830/A/4P/ALTO
EAN/UPC - Product	046677268329
Order code	458299
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10

### PL-T Triple 4-Pin Base

Material Nr. (12NC)	927911083050
Net Weight (Piece)	70.000 g
ILCOS Code	FSM-32/30/1B-E-GX24q=3


#### **Dimensional drawing**



 Product
 D (max)
 A (max)
 B (max)
 C (max)


 PL-T 32W/830/A/4P/ALTO
 41 mm
 98.7 mm
 123.0 mm
 138.7 mm

#### Photometric data



#### Lightcolor /830

Lifetime





300

400


500

400

300

200

100



500

600

Life Expectancy 3 h cycle

#### \_\_\_\_\_


Lumen Maintenance 3 h and 12 h cycle

λnm

700

## PL-T Triple 4-Pin Base

#### Lifetime



Life Expectancy 12 h cycle



© 2016 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2016, October 10 - data subject to change