



PL-T Triple 4-Pin Base

PL-T 26W/827/A/4P/ALTO

Philips Linear Compact Fluorescent Lamps offer designers, specifiers and end-users new levels of efficiencies and versatility in sizes, configurations and application possibilities. With so many elegant fixtures available to complement their small size, high light output and advanced technology, Philips Energy Advantage lamps are fast becoming the preferred choice when maximum efficiency and sleek design solutions are required.


Product data

General Information		Operating and Electrical	
Cap-Base	GX24Q-3 [GX24q-3]	Power (Rated) (Nom)	27.0 W
LSF Preheat 2000 h Rated	99 %	Lamp Current (Nom)	0.335 A
LSF Preheat 4000 h Rated	98 %	Temperature	
LSF Preheat 6000 h Rated	97 %	Design Temperature (Nom)	28 °C
LSF Preheat 8000 h Rated	90 %	Controls and Dimming	
Light Technical		Dimmable	Yes
Color Code	827 [CCT of 2700K]	Mechanical and Housing	
Luminous Flux (Nom)	1750 lm	Cap-Base Information	4P
Luminous Flux (Rated) (Nom)	1750 lm	Approval and Application	
Color Designation	Incandescent White	Mercury (Hg) Content (Nom)	1.4 mg
Correlated Color Temperature (Nom)	2700 K	Product Data	
Luminous Efficacy (rated) (Nom)	64.8 lm/W	Order product name	PL-T 26W/827/A/4P/ALTO
Color Rendering Index (Nom)	82	EAN/UPC - Product	046677384401
LLMF 2000 h Rated	92 %	Order code	458240
LLMF 4000 h Rated	88 %	Numerator - Quantity Per Pack	1
LLMF 6000 h Rated	85 %	Numerator - Packs per outer box	10
LLMF 8000 h Rated	84 %		
LLMF 12000 h Rated	81 %		

PL-T Triple 4-Pin Base

Material Nr. (12NC)	927910982750
Net Weight (Piece)	64.000 g
ILCOS Code	FSM-26/27/1B-E-GX24q=3


Dimensional drawing




PL-T ALTO 26W/827/4P A

Product	D (max)	A (max)	B (max)	C (max)
PL-T 26W/827/A/4P/ALTO	41 mm	86.7 mm	111.0 mm	126.7 mm

Photometric data




Lightcolor /827




Lightcolor /827

Lifetime




Lumen Maintenance 3 h and 12 h cycle



Life Expectancy 3 h cycle

PL-T Triple 4-Pin Base

Lifetime



Life Expectancy 12 h cycle

