



Nonmetallic Boxes



Cat. No.	Volume (Cu. in.)	Width (in.)	Edge Height (in.)	Edge Width (in.)	Cable Entries	Use with
2-3/4 in. Deep - 3-3/4 in. High – Device boxes						
WSW	18.0	2-1/4	—	—	4	Nonmetallic sheathed cable
WSW-BX	18.0	2-1/4	5	4-1/4	4	AC90-Armoured cable
WSW-N	18.0	2-1/4	—	—	4	Nonmetallic sheathed cable
2-WSW	33.0	4	5	5-1/2	8	Nonmetallic sheathed cable
3-WSW	48.0	5-3/4	5	7-1/2	12	Nonmetallic sheathed cable
4-WSW	67.0	7-5/8	5	8-3/4	16	Nonmetallic sheathed cable
WSW-FC	18.0	2-1/4	—	—	4	Nonmetallic sheathed cable
2-3/4 in. Deep - 3-3/4 in. High - 4 in. Wide – Ceiling boxes						
WOCT	26.0	—	—	—	4	Nonmetallic sheathed cable
WOCT-FC	26.0	—	5-1/4	—	4	Nonmetallic sheathed cable
3 in. Deep - 4-7/8 in. High - 4-7/8 in. Wide – Oven and dryer						
WRD	61.0	—	6-7/8	6-7/8	4	Nonmetallic sheathed cable

Nonmetallic Boxes

Airtight Model



Cat. No.	Volume (Cu. in.)	Width (in.)	Edge Height (in.)	Edge Width (in.)	Cable Entries	Use with
2-3/4 in. Deep - Non-Gangable - 3-3/4 in. High – Device boxes						
F-WSW	18.0	2-1/4	—	—	4	Nonmetallic sheathed cable
FWSWBX	18.0	2-1/4	5	4-1/4	4	AC90 – Armoured cable
2-FWSW	33.0	4	5	5-1/2	8	Nonmetallic sheathed cable
3-FWSW	48.0	5-3/4	5	7-1/2	12	Nonmetallic sheathed cable
4-FWSW	67.0	7-5/8	5	8-3/4	16	Nonmetallic sheathed cable
2-3/4 in. Deep - 3-3/4 in. High - 4 in. Wide – Ceiling boxes						
FWOC	26.0	—	5-1/4	—	4	Nonmetallic sheathed cable
3 in. Deep - 4-7/8 in. High - 4-7/8 in. Wide – Oven and dryer						
FWRD	61.0	—	6-7/8	6-7/8	4	Nonmetallic sheathed cable

Cat. No.	Description
Partition	
WSW-P	Voltage partition – For 4-WSW and 4-FWSW only

Note: CEC 2012 rule 30-302: 4) Where the weight of a luminaire does not exceed 23 kg (50 lb.), the luminaire shall be permitted to be supported by a ceiling outlet box attached directly to the building structure or by a ceiling outlet box attached to a bar hanger. Requires that a ceiling-mounted luminaire weighing 23 kg or less be supported on a ceiling outlet box attached directly to the building structure. A bar hanger may also be used to attach a ceiling box to the building structure when the luminaire weighs 23 kg or less.

Nonmetallic Boxes

Fire Resistance Rating: 2 hours



WSW-US



F-WSW-US



2WSW-US



2-FWSW-US



WOCT-US



F-WOCT-US



Cat. No.	Volume (Cu. in.)	Width (in.)	Edge Height (in.)	Edge Width (in.)	Cable Entries	Use with
2-3/4 in. Deep - Non-gangable - 3-3/4 in. High – Device boxes						
WSW-US	18.0	2-1/4	—	—	4	Nonmetallic sheathed cable
F-WSW-US	18.0	2-1/4	—	—	4	Nonmetallic sheathed cable
2WSW-US	33.0	4	5	5-1/2	8	Nonmetallic sheathed cable
2-FWSW-US	33.0	4	5	5-1/2	8	Nonmetallic sheathed cable
2-3/4 in. Deep - 3-3/4 in. High - 4 in. Wide – Ceiling boxes						
WOCT-US	26.0	—	—	—	4	Nonmetallic sheathed cable
F-WOCT-US	26.0	—	—	—	4	Nonmetallic sheathed cable