




IS=Instant Start ballast PS=Program Start ballast PRS=Program Rapid Start ballast

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Rated life IS (3 hrs)	Rated life IS (12 hrs)	Rated life PS/PRS (3 hrs)	Rated life PS/PRS (12 hrs)	Initial lumens (lm)	Mean lumens (lm)	Nominal length in. (mm)	Efficacy (lm/W)	Case qty
T8														
Dia. : 1 in. (26 mm)														
10426	F13T8/CW/PH/G13/STD	13	G13	4 100	62	6 000	7 500	N/A	N/A	530	498	12 (305)	41	48
15805	F14T8/CW/PH/G13/STD	14	G13	4 100	62	6 000	7 500	N/A	N/A	685	644	15 (381)	49	48
10634	F14T8/DL/PH/G13/STD	14	G13	6 500	62	6 000	7 500	N/A	N/A	575	541	15 (381)	41	48
62021	F15T8/WW/PH/G13/STD	15	G13	3 000	50	N/A	N/A	24 000	30 000	900	800	18 (457)	60	25
62022	F15T8/CW/PH/G13/STD	15	G13	4 100	60	N/A	N/A	24 000	30 000	850	750	18 (457)	57	25
62023	F15T8/DL/PH/G13/STD	15	G13	6 500	75	N/A	N/A	24 000	30 000	800	700	18 (457)	53	25
10510	F30T8/CW/PH/G13/STD	30	G13	4 100	62	6 000	7 500	N/A	N/A	2 180	2 049	36 (915)	73	48
10614	F30T8/DL/PH/G13/STD	30	G13	6 500	62	6 000	7 500	N/A	N/A	1 500	1 410	36 (915)	50	24
700 series														
Dia. : 1 in. (26 mm)														
10010	F17T8/35K/7/RS/G13/STD ESV	17	G13	3 500	75	N/A	N/A	24 000	30 000	1 300	1 235	24 (610)	76	25
10011	F17T8/41K/7/RS/G13/STD ESV	17	G13	4 100	75	N/A	N/A	24 000	30 000	1 300	1 235	24 (610)	76	25
10794	F25T8/35K/7/RS/G13/STD ESV	25	G13	3 500	75	24 000	30 000	30 000	36 000	2 000	1 800	36 (915)	80	25
10013	F25T8/41K/7/RS/G13/STD ESV	25	G13	4 100	75	24 000	30 000	30 000	36 000	2 000	1 800	36 (915)	80	25
51163	F32T8/35K/7/RS/G13/STD ESV	32	G13	3 500	75	20 000	24 000	24 000	30 000	2 850	2 700	48 (1 220)	89	25
51164	F32T8/41K/7/RS/G13/STD ESV	32	G13	4 100	75	20 000	24 000	24 000	30 000	2 800	2 650	48 (1 220)	88	25
51165	F32T8/50K/7/RS/G13/STD ESV	32	G13	5 000	75	20 000	24 000	24 000	30 000	2 800	2 650	48 (1 220)	88	25
10308	F40T8/41K/7/RS/G13/STD	40	G13	4 100	75	20 000	24 000	24 000	30 000	3 300	3 135	60 (1 524)	83	25



T8 Lamps



- ▶ The 900 series provides an excellent colour rendering
- ▶ High system efficiency
- ▶ Compatible with all T8 electronic ballasts
- ▶ Energy savings and reduced maintenance cost
- ▶ Low mercury content and TCLP compliant
- ▶ One System extended lamp/ballast warranty

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Rated life IS (3 hrs)	Rated life IS (12 hrs)	IS=Instant Start ballast		PS=Program Start ballast		PRS=Program Rapid Start ballast		Efficacy (lm/W)	Case qty
								Rated life PS/PRS (3 hrs)	Rated life PS/PRS (12 hrs)	Initial lumens (lm)	Mean lumens (lm)	Nominal length in. (mm)			
800 series															
Dia. : 1 in. (26 mm)															
10014	F17T8/30K/8/RS/G13/STD ESV	17	G13	3 000	85	N/A	N/A	24 000	30 000	1 400	1 330	24 (610)	82	25	
10015	F17T8/35K/8/RS/G13/STD ESV	17	G13	3 500	85	N/A	N/A	24 000	30 000	1 400	1 330	24 (610)	82	25	
10002	F17T8/41K/8/RS/G13/STD ESV	17	G13	4 100	85	N/A	N/A	24 000	30 000	1 400	1 330	24 (610)	82	25	
10016	F25T8/30K/8/RS/G13/STD ESV	25	G13	3 000	85	24 000	30 000	30 000	36 000	2 150	2 040	36 (915)	86	25	
10912	F25T8/35K/8/RS/G13/STD ESV	25	G13	3 500	85	24 000	30 000	30 000	36 000	2 150	2 040	36 (915)	86	25	
10003	F25T8/41K/8/RS/G13/STD ESV	25	G13	4 100	85	24 000	30 000	30 000	36 000	2 150	2 040	36 (915)	86	25	
58635	F25T8/830HL/ES/STD	25	G13	3 000	85	24 000	30 000	40 000	42 000	2 400	2 300	48 (1 220)	96	25	
57124	F25T8/835HL/ES/STD	25	G13	3 500	85	24 000	30 000	40 000	42 000	2 400	2 300	48 (1 220)	96	25	
57122	F25T8/841HL/ES/STD	25	G13	4 100	85	24 000	30 000	40 000	42 000	2 400	2 300	48 (1 220)	96	25	
56505	F28T8/830HL/ES/STD	28	G13	3 000	85	24 000	30 000	40 000	42 000	2 725	2 560	48 (1 220)	97	25	
56506	F28T8/835HL/ES/STD	28	G13	3 500	85	24 000	30 000	40 000	42 000	2 725	2 560	48 (1 220)	97	25	
65490	F28T8/841HL/ES/STD	28	G13	4 100	85	24 000	30 000	40 000	42 000	2 725	2 560	48 (1 220)	97	25	
56508	F28T8/850HL/ES/STD	28	G13	5 000	85	24 000	30 000	40 000	42 000	2 625	2 500	48 (1 220)	94	25	
56501	F30T8/830HL/ES/STD	30	G13	3 000	86	24 000	30 000	40 000	42 000	2 850	2 700	48 (1 220)	95	25	
56502	F30T8/835HL/ES/STD	30	G13	3 500	86	24 000	30 000	40 000	42 000	2 850	2 700	48 (1 220)	95	25	
56503	F30T8/841HL/ES/STD	30	G13	4 100	86	24 000	30 000	40 000	42 000	2 850	2 700	48 (1 220)	95	25	
56504	F30T8/850HL/ES/STD	30	G13	5 000	86	24 000	30 000	40 000	42 000	2 750	2 600	48 (1 220)	92	25	
62981	F32T8/30K/8/RS/G13/STD ESV BULK	32	G13	3 000	85	24 000	30 000	40 000	42 000	3 050	2 900	48 (1 220)	95	25	
51167	F32T8/35K/8/RS/G13/STD ESV	32	G13	3 500	85	24 000	30 000	40 000	42 000	3 050	2 900	48 (1 220)	95	25	
51168	F32T8/41K/8/RS/G13/STD ESV	32	G13	4 100	85	24 000	30 000	40 000	42 000	3 050	2 900	48 (1 220)	92	25	
59898	F32T8/41K/8/RS/G13/STD ESV BULK	32	G13	4 100	85	24 000	30 000	40 000	42 000	3 050	2 900	48 (1 220)	94	25	
10004	F32T8/50K/8/RS/G13/STD ESV	32	G13	5 000	85	24 000	30 000	40 000	42 000	2 950	2 800	48 (1 220)	92	25	
62984	F32T8/65K/8/RS/G13/STD ESV BULK	32	G13	6 500	85	24 000	30 000	40 000	42 000	2 900	2 750	48 (1 220)	91	25	
10309	F40T8/41K/8/RS/G13/STD	40	G13	4 100	85	20 000	24 000	24 000	30 000	3 700	3 600	60 (1 524)	93	25	
900 series¹															
Dia. : 1 in. (26 mm)															
51170	F32T8/50K/9/RS/G13/STD ESV	32	G13	5 000	98	20 000	24 000	24 000	30 000	2 100	2 000	48 (1 220)	66	25	
51174	F32T8/FS/RS/G13/STD	32	G13	5 700	92	20 000	24 000	24 000	30 000	2 300	2 185	48 (1 220)	72	25	

OUTDOOR

INDOOR

WARRANTY

CRI 90+

COMPLIANT

RECYCLABLE

ENERGY SAVING

ONE SYSTEM WARRANTY

T8 Lamps



- ▶ Excellent colour rendering
- ▶ High system efficiency
- ▶ Compatible with all T8 electronic ballasts
- ▶ Energy savings and reduced maintenance cost
- ▶ Low mercury content and TCLP compliant
- ▶ One System extended lamp/ballast warranty
- ▶ XL31 lamps are ideal for applications where a high lumen rating is necessary
- ▶ Long life lamps are ideal for applications where relamping is a challenge



IS=Instant Start ballast PS=Program Start ballast PRS=Program Rapid Start ballast

Order code	Description	Watts (W)	Base	Colour temp. (K)	CRI	Rated life IS (3 hrs)	Rated life IS (12 hrs)	Rated life PS/PRS (3 hrs)	Rated life PS/PRS (12 hrs)	Initial lumens (lm)	Mean lumens (lm)	Nominal length in. (mm)	Efficacy (lm/W)	Case qty
------------	-------------	-----------	------	------------------	-----	-----------------------	------------------------	---------------------------	----------------------------	---------------------	------------------	-------------------------	-----------------	----------

T8 XL31 ¹

Dia.: 1 in. (26 mm)

10914	F32T8/830K/XL31/STD	32	G13	3 000	89	20 000	24 000	24 000	30 000	3 100	2 950	48 (1 220)	97	25
10915	F32T8/835K/XL31/STD	32	G13	3 500	89	20 000	24 000	24 000	30 000	3 100	2 950	48 (1 220)	97	25
10916	F32T8/841K/XL31/STD	32	G13	4 100	89	20 000	24 000	24 000	30 000	3 100	2 950	48 (1 220)	97	25
10917	F32T8/850K/XL31/STD	32	G13	5 000	89	20 000	24 000	24 000	30 000	3 000	2 850	48 (1 220)	94	25

T8 Long Life ²

Dia.: 1 in. (26 mm)

60855	F28T8/35K/8/RS/G13/STD ESV LL	28	G13	3 500	85	36 000	40 000	55 000	60 000	2 675	2 540	48 (1 220)	96	25
60854	F28T8/41K/8/RS/G13/STD ESV LL	28	G13	4 100	85	36 000	40 000	55 000	60 000	2 675	2 540	48 (1 220)	96	25
60857	F28T8/50K/8/RS/G13/STD ESV LL	28	G13	5 000	85	36 000	40 000	55 000	60 000	2 575	2 450	48 (1 220)	92	25
60853	F32T8/35K/8/RS/G13/STD ESV LL	32	G13	3 500	85	36 000	40 000	55 000	60 000	2 950	2 800	48 (1 220)	92	25
60852	F32T8/41K/8/RS/G13/STD ESV LL	32	G13	4 100	85	36 000	40 000	55 000	60 000	2 950	2 800	48 (1 220)	92	25
60856	F32T8/50K/8/RS/G13/STD ESV LL	32	G13	5 000	85	36 000	40 000	55 000	60 000	2 850	2 700	48 (1 220)	89	25



OUTDOOR



INDOOR



2 YEARS WARRANTY



3 YEARS WARRANTY



TCLP COMPLIANT



RECYCLABLE



ENERGY SAVING



ONE SYSTEM WARRANTY

T8 Lamps