

## **FEATURES & SPECIFICATIONS**

INTENDED USE — The OneUp™ recessed direct-wire LED downlight includes integrated junction box, trim, pre-installed non-metallic bushings and 3-port push wire quick connectors in one package. The OneUp is the most economical means to create a well lit environment with exceptional energy efficiency and pear zero maintenance.

**CONSTRUCTION** — Spun steel, round baffle trim. Integrated galvanized steel junction box with captive door for easy access. Suitable for daisy chaining (pulling wires). Available in 3000K color temperature LEDs.

**OPTICS** — Round baffle recesses optical system into the ceiling to prevent glare and provide a traditional look. Diffused lens provides even light distribution for general illumination, equivalent to 50W incandescent flood lamp. Wide flood beam angle at  $>90^\circ$ . CRI >90. Maintains at least 70% light output for 50,000 hours.

**INSTALLATION** — Tool-less installation. Secure trim retention with two side-mounted spring clips for easy installation in plaster, sheet rock, or plywood ceilings. The integrated junction box - with pre-installed non-metallic bushing - allows non-metallic cable to be fed through without the hassle of knockouts. The captive junction box door provides easy access to pre-installed 3-port push wire quick connectors for straight-forward wiring. Rated for Type IC installations. Maximum of 4 No. 12AWG through branch circuit conductor suitable for 90°C permitted in box. Ground wire provided.

**ELECTRICAL SYSTEM** — LED module with high-efficiency on board driver. Dimming down to 10%. For compatible dimmers, refer to: Compatible dimmers chart.

Actual wattage may differ by  $\pm$ -5% when operating at 120V  $\pm$ -10%.

**LISTINGS** — ETL certified to US and Canadian safety standards. Can be used to comply with California Title 24 Part6 High Efficacy LED Light Source Requirements. WSEC ASTEM E283 for Air-Tight rated with gasket or caulking between fixture trim and ceiling. ENERGY STAR® certified. Wet location listed\*. Indoor damp location only for items in Brushed Nickel finish.

**WARRANTY** — 5-year limited warranty. Complete warranty terms located at: www.acuitybrands.com/CustomerResources/Terms and conditions.aspx

**Note:** Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at 25 °C. Specifications subject to change without notice.

#### Specifications

Aperture: 2-7/8" (72.0)

Overlap Trim: 4" (103.0)


Height: 4-5/8" (118.7)

Ceiling Opening: 3-3/4" (95)

Min Ceiling Thickness: 1/2" (12.7)

Max Ceiling Thickness: 1-1/2" (38.1)

All dimensions are inches (millimeters).



### **Direct-Wire LED Recessed Downlight**

# 3JBK RD

Remodel


















#### ORDERING INFORMATION

For shortest lead times, configure product using standard options (shown in bold).

Series	Shape	CCT/ Watts/Lumens <sup>1</sup>	CRI	Finish
зјвк	RD Round	27K 2700K/6.9W/490L 30K 3000K/6.9W/500L 40K 4000K/6.9W/520L 50K 5000K/6.9W/525L	<b>90CRI</b> 90 CRI	MW Matte White BN Brush Nickel²  ORB Oil-Rubbed Bronze

## Accessories: Order as separate catalog number.

OUJBK643 PAN U Universal Construction Pan



#### Notes

1 Total System Delivered Lumens.

**Example:** 3JBK RD 30K 90CRI MW


2 Indoor damp location only for items in Brushed Nickel Finish.

DOWNLIGHTING 3JBK RD

## **PHOTOMETRICS**

Distribution Curve	<b>Distribution Data</b>	Output Data	Coefficient of Utilization	Illuminance Data at 30" Above Floor for
				a Single Luminaire

**3JBK RD 30K**, 3000 K LEDs, input watts: 6.90, delivered lumens: 502.9, LM/W=72.88, test no. ISF 35035



			pf				20	)%				
			pc pc		80%			70%			50%	
Zone	Lumens	% Lamp	pw	50%	30%	10%	50%	30%	10%	50%	30%	10%
0°-30°	169.4	33.7	0	119	119	119	116	116	116	111	111	111
0°-40°	271.7	54.1	1	106	103	99	104	101	98	100	97	95
0°-60°	442.9	88.2	2	94	88	83	93	87	82	89	85	81
0°-90°	502.2	100.0	3	84	77	71	83	76	70	80	74	69
90° - 120°	0.0	0.0	4	75	67	61	74	67	61	72	65	60
90° - 130°	0.0	0.0	5	68	60	53	67	59	53	65	58	53
90° - 150°	0.0	0.0	6	61	53	47	61	53	47	59	52	47
90° - 180°	0.0	0.0	7	56	48	42	55	47	42	54	47	42
0°-180°	502.2	*100.0	8	51	43	38	51	43	38	49	42	37
*	Efficiency		9	47	39	34	47	39	34	46	39	34
			10	44	36	31	43	36	31	42	36	31

0% 111 95		Inital FC	50% be 62.1		10% be 104.3		
81 69	Mounting	Center					
60	Height	Beam	Diameter	FC	Diameter	FC	
53	8.0	7.3	6.6	3.7	14.1	0.7	
47	10.0	3.9	9.0	2.0	19.3	0.4	
42	12.0	2.5	11.4	1.2	24.4	0.2	
37	14.0	1.7	13.9	8.0	29.6	0.2	
34	16.0	1.2	16.3	0.6	34.7	0.1	

## **ENERGY DATA**

3" ROUND ENERGY DATA						
Color Temperature	2700K	2700K 3000K 4000K		5000K		
Lumens	490	500	520	525		
CRI		ç	90			
Lumens/Watt	71.01	72.46	75.36	76.09		
Min. starting temperature		-18°C	(-0°F)			
EMI/RFI	FCC Title 47 CFR, Part 15, Class B					
Sound rating	Class A Standards					
Input voltage	120V AC					
Min. power factor	0.9					
Input frequency	50/60HZ					
Rated wattage	6.9W					
Input power	6.9W					
Input current	0.06A					

## **DIMMER COMPATIBILITY**

COMPATIBLE DIMMERS							
Lutron	Leviton	Pass & Seymour	Synergy/Leviton	Sensorswitch			
DV-603P-LA	6633-PA	HCL453PTCCCV6	ISD 600 I 120 / IPI06	nSP5 PCD 2W			
CT-603PR-WH	6615-P	LS 603 PWV	ISD 1000 I 120 / IPI10	nSP5 PCD ELV 120			
DVELV-300P			ISD 400 ELV 120 / IPE04				
300P SELV							
DV-600P							
NTELV-300P							
NLV-600							
Caseta PD-6WCL dimmer (requires Lutron Smart Bridge L-BDG2-WH which is sold separately from the dimmer)							

## **LIGHTING FACTS**

