

FLUORESCENT LIGHT FIXTURE

1 & 2 lamps

IP RATING
65



Approvals:
CSA Certified
Suitable for damp & wet locations



DESCRIPTION

The VP4 series of IP65 rated linear fluorescent fixtures are sealed against water and moisture making them ideal for wet and damp locations. Uniform gasketing is inserted around the entire housing, ensuring a complete seal. The polycarbonate housing and lens are corrosion resistant and will not rot or rust. A high performance, metal reflector provides superior light output and helps dissipate ballast heat.

POWER RANGE

- 32W T8 lamp
- 28W T5 lamp
- 54W T5HO lamp

HOUSING

- Lightweight, flexible, durable and sealed polycarbonate construction
- Integral gasket forms uniform, long-life seal around the entire enclosure
- Reinforced plastic lens latch clips
- UV stabilized, high clarity lens with prismatic cut-off
- Sealed strain relief/cable gland kit included

BALLAST

T5 & T5HO: Our fixtures come standard with electronic **program start** ballasts.

T8: Our fixtures come standard with electronic **instant start** ballasts (not intended for use with occupancy sensors).

Dimming ballasts and other ballast types are optional.

ACCESSORIES (ORDER SEPARATELY)

HAR06-TPBIT-UDR	Tamper proof 2" Steel Power Bit
------------------------	---------------------------------

SELF-POWERED EMERGENCY BACK-UP (OPTIONAL)

- High-performance, sealed Ni-Cad battery
- 90 minutes emergency duration (standard)
- Automatic transfer and battery charger


REFLECTOR

- High efficiency, white metal reflector shaped for optimal light output

MOUNTING

- Row mount aligners molded into housing ends
- Stainless steel mounting hardware for wall, ceiling or suspended mounting

DIMENSIONS



ORDERING GUIDE

Series	Lamp type	Nbr of lamps	Wattage	Operation	Voltage	Ballast type	Options
VP4	T8	1 - 1 lamp	32 - 32W	AC - AC only (standard)	120 - 120V	FRZ** - Low ambient starting temperature (-29°C)	TAN - Tandem mount
	T5	Blank - 2 lamps	28 - 28W	DL* - Dual AC and emergency	277 - 277V	PSP*** - Program start parallel ballast	FU - Fuse
	T5HO		54 - 54W		347 - 347V	LBF - Low ballast factor (T8 only)	FLN - Frosted lens
					120-277 - 120-277V	HBF - High ballast factor >1.0 (T8 only)	L6 - 6' cable length
							L10 - 10' cable length
							SR - Specular reflector alanoind 320 (not available for 1 lamp)
							SS - Stainless steel latches
							OSI***** - Occupancy sensor
							DIM1***** - Dimming ballast 0-10V DC
							DIM2***** - Dimming ballast line voltage 120V
							HT***** - High ambient temperature 40°C. (T5HO)
							TP***** - Vandal resistant screws

VP4T5HO54 only available with 120-277 or 347V voltage.

* Available for 120/277V only.

** Not available with Program Start T8 ballasts.

*** Due to the fact that not all lamp/ballast combinations are compatible, please consult factory.

**** To see available options, please consult the OSI selection guide on our website.

***** Available 120V only.

***** VP4 fixtures used with T5HO 54W lamps rated for max. temperature: 25°C. For higher ambient temperatures (up to 40°C), select the HT option.

***** 1 tamper proof bit required per order (see accessories)