


TYPE YC-A

ALUMINUM CRIMPIT™

Line Tap for Combinations of Aluminum, ACSR, 6201, 5005, Compressed and Compact Conductors



Range-taking, C-shaped aluminum compression tap, or dead-ending connector designed to eliminate effects of cold flow. Can be gripped in tool and slipped over line for easy crimping. Pre-filled with PENETROX™ joint compound and Stripsealed.

E-20

CATALOG NUMBER	RUN		TAP		L	DIE INDEX	TOOLS, DIE SET CATALOG NO., & (NUMBER OF CRIMPS)	
	ALUMINUM	ACSR, 6201, 5005	ALUMINUM	ACSR, 6201, 5005			MD7, MD6	Y35, Y750, Y45†, Y46‡
YC4A6	6 Sol. - 4 Str.	6	6 Sol. & Str.	—	1-1/4	BG or 5/8	BG (4)	U-BG (2)*
YC4A4			4 Sol. & Str.	6			W-BG (2)*	
YC2A4	2 Sol. & Str.	4 - 2	4 Sol. & Str.	6	1-1/2	C	W-C (4)	U-C (2)*
YC2A2			2 Sol. & Str.	4 - 2			W-C (4)	
YC25A4	1/0 Str.	1/0	6 Str. - 4 Str.	6 - 4	1-1/2	C	W-C (4)	U-C (2)*
YC25A2			2 Sol. & Str.	2	2-1/4	C	W-C (6)	U-C (3)*
YC25A25	1/0 Str. - 2/0 Str.	1/0 - 2/0	1/0 Str. - 2/0 Str.	1/0	1-3/4	Q	W-Q (6)*	
YC26A25	1/0 Str. - 2/0 Str.		1/0 Str.	1/0	2-1/2	D**	—	U-D (3)
YC26A26	1/0 Str. - 2/0 Str.	2/0 Str.	2/0					
YC28A2	3/0 Str. - 4/0 Str.	3/0 - 4/0	6 Sol. - 2 Str.	6 - 2	2-3/4	H	—	U-H (3)
YC28A25			1/0 Str.	1/0				
YC28A26			2/0 Str.	2/0				
YC28A28			3/0 Str. - 4/0 Str.	3/0 - 4/0				
YC33R26	300 - 397.5	336.4 (18-1) (26-7)	2 Str. - 2/0 Str.	2 - 1/0	1-1/2	R	—	U-R (2)

* Multiple crimp die set; makes more than one crimp per tool compression. Figure indicates number of compressions.

** Index number "D" is not "D3" Cabelok CRIMPIT™ die.

† U Die with adapter PT-6515.

‡ U Die with adapter PUADP-1.