



PRODUCT SEARCH

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CO](#)**TERMINALS**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps &
Miscellaneous](#)

Name:
Mobile Storage Chests

Cat #:
2448

UPC #:
23273

Spec:
CAPACITY: 16FT3 .45m3 HEIGHT: 24 (610)IN. (mm) WIDTH: 48 (1219)IN. (mm) DEPTH: 24 (610)IN. (mm) WEIGHT: 159LBS. 72kg

Description:

Patented, recessed and concealed lock protectors for maximum security against drilling and cutting lock. (Model 1332 one lock protector only.) Enhanced lid bolster for added support and durability. Finger-groove lid handle for easy opening. Convenient storage tray on back wall for small items (except Model 1332). Steel support arms to hold lid in open position. Heavy-duty piano hinges with non-removable pin. Large, fold-down recessed handles for convenient lifting. Built-in 3-1/2" high skids with holes for easy caster installation. Optional casters are available separately for easy mobility.

