



Material Safety Data Sheet

Copyright, 2011, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

PRODUCT NAME: Scotchcast™ Flame-Retardant Compound 2130 (Parts A and B)

MANUFACTURER: 3M

DIVISION: Electrical Markets Division

ADDRESS: 3M Center, St. Paul, MN 55144-1000

EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)

Issue Date: 04/01/11

Supersedes Date: 12/17/08

Document Group: 26-0459-3

ID Number(s):

78-8025-2873-3, 78-8025-2874-1, 78-8046-9214-9, 78-8131-7899-9, 80-6100-7694-7, 80-6100-7695-4, 80-6101-3292-2, 80-6114-3665-2

This product is a kit or a multipart product which consists of multiple, independently packaged components. An MSDS for each of these components is included. Please do not separate the component MSDSs from this cover page. The document numbers of the MSDSs for components of this product are:

06-9232-7, 06-9230-1

Revision Changes:

Kit: Component document group number(s) was modified.

Page Heading: Product name was modified.

Kit: Product name was modified.

Kit initial issue message was modified.

Section 1: Manufacturer name was added.

Section 16: Disclaimer (first paragraph) was added.

Section 16: Disclaimer (second paragraph) was added.

Section 16: Web address was added.

Section 1: Address was added.

Copyright was added.

Company logo was added.
Telephone header was added.
Company Telephone was added.
Section 1: Emergency phone information was added.
Company Logo was deleted.
Copyright was deleted.
Kit: Manufacturer's name was deleted.
Kit: Emergency phone information was deleted.
Kit: Disclaimer (first paragraph) was deleted.
Kit: Disclaimer (second paragraph) was deleted.
Kit: Address line 1 was deleted.
Kit: Address line 2 was deleted.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M

3M USA MSDSs are available at www.3M.com



Material Safety Data Sheet

Copyright, 2011, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: Scotchcast™ Flame-Retardant Compound 2130 (Part A)
MANUFACTURER: 3M
DIVISION: Electrical Markets Division
ADDRESS: 3M Center, St. Paul, MN 55144-1000

EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)

Issue Date: 05/09/11
Supersedes Date: 03/28/11

Document Group: 06-9230-1

Product Use:

Intended Use: Electrical
Specific Use: Part A of two part electrical resin
Use – Nordic only: Kaapelinjatkoshartsi. Osa A. Unipak (osat A ja B samassa pakkauksessa).

SECTION 2: INGREDIENTS

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>% by Wt</u>
POLYETHER-HYDROCARBON-URETHANE POLYMER	154517-54-1	35 - 45
P,P'-METHYLENEBIS(PHENYL ISOCYANATE)	101-68-8	25 - 35
BENZENE, 1,1'-METHYLENEBIS[ISOCYANATO-, HOMOPOLYMER	39310-05-9	5 - 15
DIUNDECYL PHTHALATE	3648-20-2	0 - 15
DIUNDECYL PHTHALATE, BRANCHED AND LINEAR	85507-79-5	0 - 15
1,1'-METHYLENEBIS(ISOCYANATOBENZENE)	26447-40-5	< 2
4-VINYLCYCLOHEXENE	100-40-3	< 0.0005

SECTION 3: HAZARDS IDENTIFICATION

3.1 EMERGENCY OVERVIEW

Odor, Color, Grade: Light straw colored liquid with pungent odor.

General Physical Form: Liquid

Immediate health, physical, and environmental hazards: Hazardous polymerization may occur. May cause severe eye irritation. May cause allergic skin reaction. May cause severe skin irritation. May cause allergic respiratory reaction. May

cause target organ effects.

3.2 POTENTIAL HEALTH EFFECTS

Eye Contact:

Severe Eye Irritation: Signs/symptoms may include significant redness, swelling, pain, tearing, cloudy appearance of the cornea, and impaired vision.

Skin Contact:

Severe Skin Irritation: Signs/symptoms may include localized redness, swelling, itching, dryness, cracking, blistering, and pain.

Allergic Skin Reaction (non-photo induced): Signs/symptoms may include redness, swelling, blistering, and itching.

Inhalation:

May be harmful or fatal if inhaled.

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

Allergic Respiratory Reaction: Signs/symptoms may include difficulty breathing, wheezing, cough, and tightness of chest.

Prolonged or repeated exposure may cause:

Respiratory Effects: Signs/symptoms may include cough, shortness of breath, chest tightness, wheezing, increased heart rate, bluish colored skin (cyanosis), sputum production, changes in lung function tests, and/or respiratory failure.

Ingestion:

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

May be absorbed following ingestion and cause target organ effects.

Target Organ Effects:

Central Nervous System (CNS) Depression: Signs/symptoms may include headache, dizziness, drowsiness, incoordination, nausea, slowed reaction time, slurred speech, giddiness, and unconsciousness.

Persons previously sensitized to isocyanates may develop a cross-sensitization reaction to other isocyanates.

SECTION 4: FIRST AID MEASURES

4.1 FIRST AID PROCEDURES

The following first aid recommendations are based on an assumption that appropriate personal and industrial hygiene practices are followed.

Eye Contact: Immediately flush eyes with large amounts of water for at least 15 minutes. Get immediate medical attention.

Skin Contact: Remove contaminated clothing and shoes. Immediately flush skin with large amounts of water. Get medical attention. Wash contaminated clothing and clean shoes before reuse.

Inhalation: Remove person to fresh air. If signs/symptoms develop, get medical attention.

If Swallowed: Do not induce vomiting unless instructed to do so by medical personnel. Give victim two glasses of water. Never give anything by mouth to an unconscious person. Get medical attention.

SECTION 5: FIRE FIGHTING MEASURES

5.1 FLAMMABLE PROPERTIES

Autoignition temperature	No Data Available
Flash Point	>=300 °F [Test Method: Closed Cup]
Flammable Limits(LEL)	No Data Available
Flammable Limits(UEL)	No Data Available
OSHA Flammability Classification:	Class IIIB Combustible Liquid

5.2 EXTINGUISHING MEDIA

Use fire extinguishers with class B extinguishing agents (e.g., dry chemical, carbon dioxide).

5.3 PROTECTION OF FIRE FIGHTERS

Special Fire Fighting Procedures: Wear full protective equipment (Bunker Gear) and a self-contained breathing apparatus (SCBA).

Unusual Fire and Explosion Hazards: Not applicable. Closed containers exposed to heat from fire may build pressure and explode. No unusual fire or explosion hazards are anticipated.

Note: See STABILITY AND REACTIVITY (SECTION 10) for hazardous combustion and thermal decomposition information.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Evacuate unprotected and untrained personnel from hazard area. The spill should be cleaned up by qualified personnel. Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapors, in accordance with good industrial hygiene practice. Warning! A motor could be an ignition source and could cause flammable gases or vapors in the spill area to burn or explode. Cover, but do not seal for 48 hours.

6.2. Environmental precautions

Place in a container approved for transportation by appropriate authorities, but do not seal the container for 48 hours to avoid pressure build-up. For larger spills, cover drains and build dikes to prevent entry into sewer systems or bodies of water. Collect the resulting residue containing solution. Dispose of collected material as soon as possible.

Clean-up methods

Pour isocyanate decontaminant solution (90% water, 8% concentrated ammonia, 2% detergent) on spill and allow to react for 10 minutes. Or pour water on spill and allow to react for more than 30 minutes. Cover with absorbent material. Observe precautions from other sections. Call 3M- HELPS line (1-800-364-3577) for more information on handling and managing the spill. Contain spill. Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Collect as much of the spilled material as possible. Clean up residue with an appropriate solvent selected by a qualified and authorized person. Ventilate the area with fresh air. Read and follow safety precautions on the solvent label and MSDS.

In the event of a release of this material, the user should determine if the release qualifies as reportable according to local, state, and federal regulations.

SECTION 7: HANDLING AND STORAGE

7.1 HANDLING

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water. For industrial or professional use only. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below Occupational Exposure Limits. If ventilation is not adequate, use respiratory protection equipment. Keep out of the reach of children. Do not breathe vapors. Do not get in eyes, on skin or on clothing. Avoid contact with water.

7.2 STORAGE

Store away from heat. Store out of direct sunlight. Keep container in well-ventilated area. Store away from areas where product may come into contact with food or pharmaceuticals. Keep container tightly closed. Store in a cool, dry place.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 ENGINEERING CONTROLS

Do not use in a confined area or areas with little or no air movement. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below Occupational Exposure Limits and/or control mist, vapor, or spray. If ventilation is not adequate, use respiratory protection equipment.

8.2 PERSONAL PROTECTIVE EQUIPMENT (PPE)

8.2.1 Eye/Face Protection

Do not get in eyes.

The following eye protection(s) are recommended: Full Face Shield
Indirect Vented Goggles

8.2.2 Skin Protection

Do not get on skin or on clothing.

Select and use gloves and/or protective clothing to prevent skin contact based on the results of an exposure assessment. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible materials.

Gloves made from the following material(s) are recommended: Butyl Rubber

Polymer laminate

. The following protective clothing material(s) are recommended: Coveralls - Disposable, laminate

Boots - Rubber

8.2.3 Respiratory Protection

Do not breathe vapors.

Select one of the following NIOSH approved respirators based on airborne concentration of contaminants and in accordance with OSHA regulations: Half facepiece or fullface air-purifying respirator with organic vapor cartridges and P100 particulate prefilters

. Select and use respiratory protection to prevent an inhalation exposure based on the results of an exposure assessment. Consult with your respirator manufacturer for selection of appropriate types of respirators.

8.2.4 Prevention of Swallowing

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water.

8.3 EXPOSURE GUIDELINES

<u>Ingredient</u>	<u>Authority</u>	<u>Type</u>	<u>Limit</u>	<u>Additional Information</u>
P,P'-METHYLENEBIS(PHENYL ISOCYANATE)	ACGIH	TWA	0.005 ppm	
P,P'-METHYLENEBIS(PHENYL ISOCYANATE)	OSHA	CEIL	0.2 mg/m3	

SOURCE OF EXPOSURE LIMIT DATA:

ACGIH: American Conference of Governmental Industrial Hygienists

CMRG: Chemical Manufacturer Recommended Guideline

OSHA: Occupational Safety and Health Administration

AIHA: American Industrial Hygiene Association Workplace Environmental Exposure Level (WEEL)

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Odor, Color, Grade:	Light straw colored liquid with pungent odor.
General Physical Form:	Liquid
Autoignition temperature	<i>No Data Available</i>
Flash Point	>=300 °F [<i>Test Method: Closed Cup</i>]
Flammable Limits(LEL)	<i>No Data Available</i>
Flammable Limits(UEL)	<i>No Data Available</i>
Boiling Point	>=300 °F
Vapor Density	<i>No Data Available</i>
Vapor Pressure	<i>No Data Available</i>
Specific Gravity	1.08 [<i>Ref Std: WATER=1</i>]
pH	<i>Not Applicable</i>
Melting point	<i>Not Applicable</i>
Solubility in Water	Nil
Evaporation rate	<i>No Data Available</i>
Volatile Organic Compounds	<i>No Data Available</i>
Kow - Oct/Water partition coef	<i>No Data Available</i>
Percent volatile	Nil
VOC Less H2O & Exempt Solvents	<i>No Data Available</i>
Viscosity	700 - 900 centipoise

SECTION 10: STABILITY AND REACTIVITY

Stability: Stable.

Materials and Conditions to Avoid:

10.1 Conditions to avoid

None known

10.2 Materials to avoid

Strong bases
Alcohols
Water

Hazardous Polymerization: Hazardous polymerization may occur.

Hazardous Decomposition or By-Products

<u>Substance</u>	<u>Condition</u>
Carbon monoxide	During Combustion
Carbon dioxide	During Combustion
Hydrogen Cyanide	During Combustion
Oxides of Nitrogen	During Combustion

SECTION 11: TOXICOLOGICAL INFORMATION

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its components.

SECTION 12: ECOLOGICAL INFORMATION

ECOTOXICOLOGICAL INFORMATION

Not determined.

CHEMICAL FATE INFORMATION

Not determined.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste Disposal Method: Dispose of completely cured (or polymerized) wastes in a sanitary landfill. As a disposal alternative, dispose of waste product in a facility permitted to accept chemical waste.

EPA Hazardous Waste Number (RCRA): Not regulated

Since regulations vary, consult applicable regulations or authorities before disposal.

SECTION 14: TRANSPORT INFORMATION

ID Number(s):

LH-A100-0638-1, LH-A100-0638-2, LH-A100-0638-3, LH-A100-0638-4, 80-6107-3192-1

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: REGULATORY INFORMATION

US FEDERAL REGULATIONS

Contact 3M for more information.

311/312 Hazard Categories:

Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - Yes

Section 313 Toxic Chemicals subject to the reporting requirements of that section and 40 CFR part 372 (EPCRA):

<u>Ingredient</u>	<u>C.A.S. No</u>	<u>% by Wt</u>
P,P'-METHYLENEBIS(PHENYL ISOCYANATE)	101-68-8	25 - 35

STATE REGULATIONS

Contact 3M for more information.

CHEMICAL INVENTORIES

The components of this product are in compliance with the chemical notification requirements of TSCA.

Contact 3M for more information.

INTERNATIONAL REGULATIONS

Contact 3M for more information.

This MSDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: OTHER INFORMATION

NFPA Hazard Classification

Health: 3 Flammability: 1 Reactivity: 0 Special Hazards: None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

HMIS Hazard Classification

Health: 2 Flammability: 1 Reactivity: 0 Protection: X - See PPE section.

Hazardous Material Identification System (HMIS®) hazard ratings are designed to inform employees of chemical hazards in the workplace. These ratings are based on the inherent properties of the material under expected conditions of normal use and are not intended for use in emergency situations. HMIS® ratings are to be used with a fully implemented HMIS® program. HMIS® is a registered mark of the National Paint and Coatings Association (NPCA).

Revision Changes:

Section 3: Other health effects information was modified.

Section 2: Ingredient table was modified.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M

3M USA MSDSs are available at www.3M.com



Material Safety Data Sheet

Copyright, 2011, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

SECTION 1: PRODUCT AND COMPANY IDENTIFICATION

PRODUCT NAME: Scotchcast™ Flame-Retardant Compound 2130 (Part B)

MANUFACTURER: 3M

DIVISION: Electrical Markets Division

ADDRESS: 3M Center, St. Paul, MN 55144-1000

EMERGENCY PHONE: 1-800-364-3577 or (651) 737-6501 (24 hours)

Issue Date: 06/24/11

Supersedes Date: 04/12/11

Document Group: 06-9232-7

Product Use:

Intended Use: Electrical
 Specific Use: Part B of two part electrical resin

SECTION 2: INGREDIENTS

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>% by Wt</u>
DBDPE	1163-19-5	20 - 30
HOMOPOLYMER	69102-90-5	20 - 30
DIUNDECYL PHTHALATE	3648-20-2	10 - 20
ALUMINUM POTASSIUM SODIUM SILICATE	12736-96-8	1 - 10
N,N-DI(2-HYDROXYPROPYL)ANILINE	3077-13-2	1 - 10
CASTOR OIL	8001-79-4	1 - 10
ANTIMONY TRIOXIDE	1309-64-4	1 - 10
POLYPROPYLENE ETHER DIOL	25322-69-4	1 - 10
DIPROPYLENE GLYCOL	25265-71-8	1 - 10
CARBON BLACK	1333-86-4	1 - 5
HYDROCINNAMIC ACID, 3,5-DI-TERT-BUTYL-4-HYDROXY-, OCTADECYL ESTER	2082-79-3	0.3 - 0.8

SECTION 3: HAZARDS IDENTIFICATION

3.1 EMERGENCY OVERVIEW

Odor, Color, Grade: Smooth black liquid with pungent odor.

General Physical Form: Liquid

Immediate health, physical, and environmental hazards: Contains a chemical or chemicals which can cause cancer. May cause target organ effects.

3.2 POTENTIAL HEALTH EFFECTS

Eye Contact:

Moderate Eye Irritation: Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

Skin Contact:

Mild Skin Irritation: Signs/symptoms may include localized redness, swelling, and itching.

Inhalation:

Respiratory Tract Irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

May be absorbed following inhalation and cause target organ effects.

Ingestion:

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

May be absorbed following ingestion and cause target organ effects.

Target Organ Effects:

Central Nervous System (CNS) Depression: Signs/symptoms may include headache, dizziness, drowsiness, incoordination, nausea, slowed reaction time, slurred speech, giddiness, and unconsciousness.

Carcinogenicity:

Contains a chemical or chemicals which can cause cancer.

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>Class Description</u>	<u>Regulation</u>
ANTIMONY TRIOXIDE	1309-64-4	Grp. 2B: Possible human carc.	International Agency for Research on Cancer
CARBON BLACK	1333-86-4	Grp. 2B: Possible human carc.	International Agency for Research on Cancer

SECTION 4: FIRST AID MEASURES

4.1 FIRST AID PROCEDURES

The following first aid recommendations are based on an assumption that appropriate personal and industrial hygiene practices are followed.

Eye Contact: Flush eyes with large amounts of water. If signs/symptoms persist, get medical attention.

Skin Contact: Wash affected area with soap and water. If signs/symptoms develop, get medical attention.

Inhalation: Remove person to fresh air. If signs/symptoms develop, get medical attention.

If Swallowed: Do not induce vomiting unless instructed to do so by medical personnel. Give victim two glasses of water. Never give anything by mouth to an unconscious person. Get medical attention.

SECTION 5: FIRE FIGHTING MEASURES

5.1 FLAMMABLE PROPERTIES

Autoignition temperature

No Data Available

Flash Point

≥ 290 °F [*Test Method: Closed Cup*]

Flammable Limits(LEL)

No Data Available

Flammable Limits(UEL)

No Data Available

OSHA Flammability Classification:

Class IIIB Combustible Liquid

5.2 EXTINGUISHING MEDIA

Ordinary combustible material. Use fire extinguishers with class A extinguishing agents (e.g., water, foam).

5.3 PROTECTION OF FIRE FIGHTERS

Special Fire Fighting Procedures: Water may be used to blanket the fire. Wear full protective equipment (Bunker Gear) and a self-contained breathing apparatus (SCBA).

Unusual Fire and Explosion Hazards: Non-flammable: ordinary combustible material. None inherent in this product.

Note: See STABILITY AND REACTIVITY (SECTION 10) for hazardous combustion and thermal decomposition information.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Evacuate unprotected and untrained personnel from hazard area. The spill should be cleaned up by qualified personnel. Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapors, in accordance with good industrial hygiene practice. Warning! A motor could be an ignition source and could cause flammable gases or vapors in the spill area to burn or explode.

6.2. Environmental precautions

For larger spills, cover drains and build dikes to prevent entry into sewer systems or bodies of water. Collect the resulting residue containing solution. Place in a closed container approved for transportation by appropriate authorities. Dispose of collected material as soon as possible.

Clean-up methods

Observe precautions from other sections. Call 3M- HELPS line (1-800-364-3577) for more information on handling and managing the spill. Contain spill. Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Collect as much of the spilled material as possible. Clean up residue with an appropriate solvent selected by a qualified and authorized person. Ventilate the area with fresh air. Read and follow safety precautions on the solvent label and MSDS.

In the event of a release of this material, the user should determine if the release qualifies as reportable according to local, state, and federal regulations.

SECTION 7: HANDLING AND STORAGE

7.1 HANDLING

Avoid eye contact. Contents may be under pressure, open carefully. Avoid breathing of vapors, mists or spray. For industrial or professional use only. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below Occupational Exposure Limits. If ventilation is not adequate, use respiratory protection equipment. Avoid skin contact. Do not ingest.

7.2 STORAGE

Store away from heat. Keep container in well-ventilated area. Store in a cool, dry place.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 ENGINEERING CONTROLS

Use with appropriate local exhaust ventilation. Provide appropriate local exhaust ventilation on open containers. If exhaust ventilation is not available, use appropriate respiratory protection.

8.2 PERSONAL PROTECTIVE EQUIPMENT (PPE)

8.2.1 Eye/Face Protection

Avoid eye contact.

The following eye protection(s) are recommended: Indirect Vented Goggles

8.2.2 Skin Protection

Avoid skin contact.

Select and use gloves and/or protective clothing to prevent skin contact based on the results of an exposure assessment. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible materials.

Gloves made from the following material(s) are recommended: Butyl Rubber

8.2.3 Respiratory Protection

Avoid breathing of vapors, mists or spray.

Select one of the following NIOSH approved respirators based on airborne concentration of contaminants and in accordance with OSHA regulations: Half facepiece or fullface air-purifying respirator with organic vapor cartridges

Select and use respiratory protection to prevent an inhalation exposure based on the results of an exposure assessment. Consult with your respirator manufacturer for selection of appropriate types of respirators.

8.2.4 Prevention of Swallowing

Do not eat, drink or smoke when using this product. Wash exposed areas thoroughly with soap and water. Not applicable.

8.3 EXPOSURE GUIDELINES

<u>Ingredient</u>	<u>Authority</u>	<u>Type</u>	<u>Limit</u>	<u>Additional Information</u>
ANTIMONY TRIOXIDE	CMRG	TWA, as Sb	0.2 mg/m3	
CARBON BLACK	ACGIH	TWA	3.5 mg/m3	
CARBON BLACK	CMRG	TWA	0.5 mg/m3	
CARBON BLACK	OSHA	TWA	3.5 mg/m3	
DBDPE	AIHA	TWA	5 mg/m3	
DBDPE	CMRG	TWA	5 mg/m3	
HYDROCINNAMIC ACID, 3,5-DI-TERT-BUTYL-4-HYDROXY-, OCTADECYL ESTER	CMRG	TWA	10 mg/m3	
POLYPROPYLENE ETHER DIOL	AIHA	TWA, as aerosol	10 mg/m3	
POLYPROPYLENE GLYCOLS	AIHA	TWA, as aerosol	10 mg/m3	

SOURCE OF EXPOSURE LIMIT DATA:

ACGIH: American Conference of Governmental Industrial Hygienists

CMRG: Chemical Manufacturer Recommended Guideline

OSHA: Occupational Safety and Health Administration

AIHA: American Industrial Hygiene Association Workplace Environmental Exposure Level (WEEL)

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Odor, Color, Grade:	Smooth black liquid with pungent odor.
General Physical Form:	Liquid
Autoignition temperature	<i>No Data Available</i>
Flash Point	>=290 °F [<i>Test Method: Closed Cup</i>]
Flammable Limits(LEL)	<i>No Data Available</i>
Flammable Limits(UEL)	<i>No Data Available</i>
Boiling Point	>=290 °F
Vapor Density	<i>No Data Available</i>
Vapor Pressure	< 27 psia [@ 131 °F]
Specific Gravity	1.29 [<i>Ref Std: WATER=1</i>]
pH	<i>Not Applicable</i>
Melting point	<i>Not Applicable</i>
Solubility in Water	Nil
Evaporation rate	<i>No Data Available</i>
Volatile Organic Compounds	<i>No Data Available</i>
Kow - Oct/Water partition coef	<i>No Data Available</i>
VOC Less H2O & Exempt Solvents	<i>No Data Available</i>
Viscosity	7,000 centipoise

SECTION 10: STABILITY AND REACTIVITY

Stability: Stable.

Materials and Conditions to Avoid:

10.1 Conditions to avoid

None known

10.2 Materials to avoid

None known

Hazardous Polymerization: Hazardous polymerization will not occur.

Hazardous Decomposition or By-Products

<u>Substance</u>	<u>Condition</u>
Carbon monoxide	During Combustion
Carbon dioxide	During Combustion
Oxides of Nitrogen	During Combustion
Oxides of Antimony	During Combustion

SECTION 11: TOXICOLOGICAL INFORMATION

Please contact the address listed on the first page of the MSDS for Toxicological Information on this material and/or its components.

SECTION 12: ECOLOGICAL INFORMATION

ECOTOXICOLOGICAL INFORMATION

Not determined.

CHEMICAL FATE INFORMATION

Not determined.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste Disposal Method: Incinerate in an industrial or commercial facility in the presence of a combustible material. As a disposal alternative, dispose of waste product in a facility permitted to accept chemical waste.

EPA Hazardous Waste Number (RCRA): Not regulated

Since regulations vary, consult applicable regulations or authorities before disposal.

SECTION 14: TRANSPORT INFORMATION

ID Number(s):

LH-A100-0639-9, LH-A100-0640-0, LH-A100-0640-1, LH-A100-0640-2, 80-6107-3193-9

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: REGULATORY INFORMATION

US FEDERAL REGULATIONS

Contact 3M for more information.

311/312 Hazard Categories:

Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - Yes

Section 313 Toxic Chemicals subject to the reporting requirements of that section and 40 CFR part 372 (EPCRA):

<u>Ingredient</u>	<u>C.A.S. No</u>	<u>% by Wt</u>
ANTIMONY TRIOXIDE (ANTIMONY COMPOUNDS)	1309-64-4	1 - 10
DBDPE	1163-19-5	20 - 30

This material contains a chemical which requires export notification under TSCA Section 12[b]:

<u>Ingredient (Category if applicable)</u>	<u>C.A.S. No</u>	<u>Regulation</u>	<u>Status</u>
DBDPE	1163-19-5	Toxic Substances Control Act (TSCA) 4 Test Rule Chemicals	Applicable

STATE REGULATIONS

Contact 3M for more information.

CALIFORNIA PROPOSITION 65

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>Classification</u>
ANTIMONY TRIOXIDE	1309-64-4	**Carcinogen
CARBON BLACK	1333-86-4	**Carcinogen

** WARNING: contains a chemical which can cause cancer.

CHEMICAL INVENTORIES

The components of this product are in compliance with the chemical notification requirements of TSCA.

Contact 3M for more information.

INTERNATIONAL REGULATIONS

Contact 3M for more information.

This MSDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: OTHER INFORMATION

NFPA Hazard Classification

Health: 2 Flammability: 1 Reactivity: 0 Special Hazards: None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

HMIS Hazard Classification

Health: 2 Flammability: 1 Reactivity: 0 Protection: X - See PPE section.

Hazardous Material Identification System (HMIS®) hazard ratings are designed to inform employees of chemical hazards in the workplace. These ratings are based on the inherent properties of the material under expected conditions of normal use and are not intended for use in emergency situations. HMIS® ratings are to be used with a fully implemented HMIS® program. HMIS® is a registered mark of the National Paint and Coatings Association (NPCA).

Revision Changes:

- Section 1: Product use information was modified.
- Section 3: Potential effects from skin contact information was modified.
- Section 4: First aid for skin contact - decontamination - was modified.
- Section 4: First aid for skin contact - medical assistance - was modified.
- Section 2: Ingredient table was modified.
- Section 8: Exposure guidelines ingredient information was modified.
- Section 3: Immediate skin hazard(s) was deleted.
- Section 4: First aid for skin contact - termination of exposure - was deleted.
- Section 4: First aid for skin contact - handling - was deleted.

DISCLAIMER: The information in this Material Safety Data Sheet (MSDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a

particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the MSDS available directly from 3M

3M USA MSDSs are available at www.3M.com