

# **POWER PRODUCT Panelboards**







# **Contents**

Features, Reference Guide & General Specifications Distributor Stock - Type P1 Panelboards	10-2 – 10-9 10-10 – 10-11
Warehouse Stock/Unassembled – Type P1 Panelboards	10-12 – 10-14
Panelboard Replacement, Modification, and Additions	10-15
Factory Assembled Panelboard Coding System	10-16
Type P1	
Specifications	10-17
Main Breaker	10-18
Main Lug and Branch Circuit Breakers	10-19
Kits and Accessories	10-20 - 10-21
Panel Options & Modifications	10-22 – 10-23
Enclosure Dimensions	10-24
Type P2	
Specifications	10-25
Distributor Stock/Unassembled -Type P2 Main Lug Only	10-26 - 10-27
Main Breaker and Subfeed Breakers	10-28 - 10-30
Branch Breakers	10-31
Modifications and Additions	10-32
SEM3 Embedded Micro Metering Module	10-33 - 10-34
Standard Modifications and Additions	10-35
Enclosure Modifications	10-36
Kits and Accessories	10-37
Enclosure Dimensions	10-38
Type P3	
Specifications	10-39
Enclosure Selection/ Dimensions	10-40
Alternate Main, Branch and Subfeed Breakers	10-41 - 10-42
Modifications and Additions	10-43 - 10-45
Kits and Accessories	10-46
Enclosure Dimensions	10-47
Type S5	
Specifications	10-48
Main Lug and Main Breaker Selection	10-49
Branch Breakers	10-50
Modifications and Additions	10-51
Modifications, Additions, Replacements for Circuit Breakers	10-52
Type F2	
Specifications and Fuse Types	10-53
Main Lug and Main Fusible	10-54
Modifications and Additions	10-55
Modifications, Additions, Replacements for Fusible Switches	10-56
SEM3 Embedded Micro Metering Module	10-57
Panel Skirt/System Types, AC & DC Voltages	10-58
Type HCP Switchboard Units	
Selection and accessories	10-59
Dimensions	10-60
Type C1/C2	
Specifications	10-61
Main, Branch and Subfeed Breakers	10-62
Circuit Breaker / Column Type, Modifications and Additions	10-63
Conduit Enclosing Shield (Panel Skirts)	10-64
Enclosure/System Types, AC & DC Voltages	10-65
Dimensions and Panelboard Configurations	10-66 – 10-67
Fuse Curves	10-68

This generation of panelboards from Siemens offers the high level of engineering and innovation you've come to expect from the leader in power distribution technology. The "P Series" line of panelboards offers a stepped approach to power distribution.

Additional strength has been added to an already rugged and durable panelboard family. Engineered specifically to provide maximum flexibility, the new designs simplify wiring and reduce material requirements making them easier to install and less costly than competitive products. At the heart of the product line is the extensive research and technology found among Siemens circuit protection devices - both fusible switches and molded case circuit breakers.

The line is anchored by the innovative P1. Featuring the industry's most flexible designs, the P1 virtually eliminates common errors, such as feed direction, and main lug versus main breaker. Increasing distribution is simplified by the ability to add feedthru lugs. The Next Gen P1 design introduced in June 2015 has added Extended Circuits up to 66 and has available smaller Enclosures with no Subfeed option for added flexibility.

Subsequent steps in the P Series offer increased capacity and more design options:

- The highly flexible P2 provides options to fit the most demanding specifications.
- Sized more like a lighting panel, the P3 packs the power of a distribution panel in a space-saving, highly flexible design.

• The powerful S5 and F2 are distribution power panels that allow circuit breakers as branch and main devices.

Siemens also offers a number of specialty panels, like column panels, SEM3 (Embedded Micro Metering Module™) and others. Don't see a panel to meet your requirements? Ask your Siemens representative about our custom capabilities.

#### **Features Overview**

P Series lighting panel features include Fas-Latch trim, which is popular among installers; the jacking screw system, that permits adjustments even after wiring has been installed; our exclusive split neutral, and more. Many panelboards have the capability of mixing and matching breakers of different sizes and ratings - or changing from main lug to main breaker, or adding subfeed breakers without changing the box size. Other models accept a wide range of fuse types, including Siemens exclusive Vacu-Break® technology.

#### **Key Panelboard Features**

	P1	P2	P3	S5	F2
Lighting And Appliance Applications	•	•	•	•	•
Power Panelboard Applications	_	•	•	•	•
Convertible From Top Feed To Bottom Feed Or Vice Versa	•	_	_	_	_
Change From Main Lug To Main Breaker Or Add Subfeed Without Changing Enclosure Size <sup>©</sup>	•	_	_	_	_
Space-Saving, Horizontally Mounted Main Breaker	Up To 250 Amps	Up To 250 Amps	_	•	•
Short-Circuit Rating Label Giving Performance Level	•	•	•	•	•
Standard Aluminum Ground Assembly	•	•	•	•	•
Blank End-Walls Standard <sup>①</sup>	•	•	•	•	•
Bolted Current-Carrying Parts	•	•	•	•	•
Split Neutral	•	_	•	•	•
Connection Accessible From Front	•	•	•	•	•
Screw-Type Mechanical Lugs	•	•	•	•	•
Time-Reducing Wing Nuts To Secure Interior Without Tools	•	•	•	•	•
Main and Branch Devices Connected With Case- Hardened Hardware	•	•	•	•	•
Flush Lock, Concealed Door Hinges/Trim Screws	•	•	•	_	_
Symmetrical Interior Mounting Studs To Eliminate Upside-Down Mounting of Box	•	•	•	•	•
Interior Height Adjustment For Flush Applications	•	•	•	_	-
Shallow Depth	5.75"	5.75"	7.75"	12.75"	12.75"
Accepts A Wide Range Of Fuse Types	_	_	_	_	•
Accepts Vacu-Break Fusible Switch	_	_	_	_	•
Accepts A Wide Range Of Circuit Breakers	•	•	•	•	•
Optional Compression Lugs	•	•	•	•	•

KO's available on P1 and P2 – 5.75" Deep x 20" Wide boxes and P3 7.75" deep X 24" wide boxes.

<sup>@</sup> For Next Gen P1, only when Subfeed Space is selected, Interior Part Number ends with "T". When "N" is at end there is no Subfeed Space available

## **General Specifications**

#### **Service Entrance Equipment**

When a panelboard is used as service entrance equipment, it must be located as close as practicable to the point of entrance of building supply conductors. Panelboards must be identified as "Service Entrance" at the time of order entry in order to be supplied with the appropriate CSA certification and labelling. Panels must include a connector for bonding and grounding neutral conductor. Please consult CSA, CEC and local inspection authorities for specification and installation guidelines.

#### **Integrated Equipment Short Circuit Rating**

The term "Integrated Equipment Short Circuit Rating" refers to the application of series connected circuit breakers in a combination that allows some breakers to have lower individual interrupting ratings than the available fault current. This is permitted as long as the series combination has been tested and certified by CSA. "Series Rated" must be identified at the time of order entry.

#### **Standards**

CSA: C22.2 No.29. Certified under files # 93833 UL: 67 and 50. Listed by Underwriter's Laboratories, Inc., under "Panelboards" File #E2269, and #E4016.


#### **Wire Connectors**


Standard wire connectors in Siemens panels are suitable for copper or aluminum cables rated 60/75 degree. Copper main lugs are a price-added option for most panel types and some Circuit Breakers (check with Siemens sales for availability). It should be noted that most copper lugs will only accept copper cables. Some applications, 100% rated devices in particular, require that the cable and connectors be rated 90 degree but are sized to the 75 degree tables.

Standard ground connectors are also suitable for copper or aluminum wire. Ground connector assemblies (EGK, IGK) have (7) 1/0 max, and (15) #6 max, connections. The 1/0 holes are capable of connecting up (3) #10 max. wires. Copper ground assemblies (ECGK, ICGK) are rated for copper wire only and have the same wiring capacity as the Al/Cu connectors.

Standard neutrals, like standard main lugs, are also rated for copper or aluminum wire. The neutral cross bar material follows the selection bus. Copper neutral lugs are rated for copper cable only and available as a price added option.

## Lug Data Feed-Thru Lugs





Feed-thru lugs are mounted at the opposite end of the main bus from the main lugs or main breaker and are used to connect two or more panelboards to the incoming feeder. The feeder cables are brought into Panelboard 1 and connected to the main lugs or main breaker. Cables interconnecting the two panelboards are connected to the feed-thru lugs in Panelboard 1 and are carried over the main lugs in Panelboard 2. This arrangement could be reversed with the main lugs located at the top and the feed-thru lugs at the bottom of the panel.

Subfeed lugs are mounted directly beside the main incoming lugs and are used to connect two or more panelboards to the incoming feeder. The feeder cables are brought into Panelboard 1 and connected to the main lugs. Another set of cables that are the same size are connected to the subfeed lugs of Panelboard 1 and are carried over the main lugs of Panelboard 2.

10-3

## General

## **Bussing Sequence**

Interiors are designed to accommodate top or bottom feed.

All breakers have bolted connections.

The panel design provides bracing up to 200,000A IR CSA short circuit rating. Case-hardened, high performance, thread rolling screws are used on branch bus.



**Circuit Breaker Lighting** Panel Type P1



Circuit Breaker Lighting or Distribution Panel Types P2/P3



**Circuit Breaker Distribution** Panel Type S5



**Fusible Switch Distribution** Panel Type F2

## **Panelboard Ratings**

Description	Next Gen P1	P2	P3	S5	F2
Max. Voltage	600Y/347V AC Max.	600V AC Max. 250V DC Max.	600V AC Max. 250V DC Max.	600V AC Max. 250V DC Max.	600V AC Max. 250V DC Max.
System	1-Phase, 2-wire 1-Phase, 3-wire 3-Phase, 3-wire 3-Phase, 4-wire	1-Phase, 2-wire 1-Phase, 3-wire 3-Phase, 3-wire 3-Phase, 4-wire	1-Phase, 2-wire 1-Phase, 3-wire 3-Phase, 4-wire 3-Phase, 3-wire	1-Phase, 3-wire 3-Phase, 4-wire 3-Phase, 3-wire	1-Phase, 3-wire 3-Phase, 4-wire 3-Phase, 3-wire
Mains					
Main Lugs Main Breaker Main Switch	125A-400A 100A-400A —	125A-600A 100A-600A —	400A-800A 400A-600A —	225A-1200A 400A-1200A —	225A-1200A - 200A-600A
Circuits	18, 30, 42, 54, 66 (250A) 30, 42, 54, 66 (400A)	18, 30, 42, 54, 66 78, 90 <sup>©</sup>	18, 30, 42, 54, 66, 78, 90	_	_
Branch Ratings	15-125A	15-400A	15-400A	15-1200A MCCB	30-1200A Fusible
Branch Disconnect Devices	BL, BLH, HBL, BQD, BQD6, BLE, BLEH, BLF2, BLHF2, HBLF2, BLFB, BLHFB, BAF2, BAFH2, HBAF2, BFGA2, BFGAH2, HBFGA2, NGB <sup>©</sup>	BL, BLH, HBL, BQD, BQD6, QJ2®, QJH2®, QJ2H®, QR2®, QRH2®, HQR2®, HQR2H®, ED2, ED4, HED4, ED6, CED6, BLE, BLEH, BLF2, BLHF2, HBLF2, BLFB, BLHFB, BAF2, BAFH2, HBAF2, BFGA2, BFGAH2, HBFGA2, NGB2, HGB2, LGB2	BL, BLH, HBL, BQD, BQD6, QJ2©, QJH2©, QJ2H®, QR2®, QRH2®, HQR2®, HQR2H®, ED2, ED4, HED4, ED6, BLE, BLHF, BLEH, BLF2, BLHF2, HBLF2, BLFB, BAF2, BAFH2, HBAF2, BFGA2, BFGAH2, HBFGA2, NGB2, HGB2, LGB2	All 15-1200A MCCBs, and VL DG, FG, JG	All 30-600A VB switches, 30-200A VK switches, and 800- 1200A HCP switches
Subfeed Circuit Breakers 23	ED2, ED4, ED6, HED4, QJ2, QJH2, QJ2H, QR2, QRH2, HQR2, HQR2H, FD6, HFD6, FXD6, HFXD6	JD6, HJD6, JXD6, HJXD6, FD6, HFD6, FXD6, HFXD6	JD6, HJD6, JXD6, FD6, HFD6, FXD6, HFXD6	_	_
Enclosure Heights Inches – (mm)	26, 32, 38, 44, 50, 56 @250A (660, 813, 965, 1118, 1270, 1422) 56, 62, 68, 74 @400A (1422, 1575, 1727, 1880)	26, 32, 38, 44, 50, 56, 62, 68, 74 (660-1880)	56, 62, 68, 74, 80 (1422-2032)	60, 75, 90 (1524, 1905, 2286)	60, 75, 90 (1524, 1905, 2286)
Standard Trims	Fas-Latch – 1 Piece Surface or Flush	Fas-Latch – 1 Piece Surface or Flush	Fas-Latch – 1 Piece Surface or Flush	_	_

① P1 panels with NGB breakers are limited to NGB branch devices

only. BL and BQD frames may not be mixed in this panel type.

P1 can have max. 1 subfeed breaker when Subfeed Space is available. P2 and P3 can have up to (2) FD subfeed breakers.

<sup>3</sup> JD and FD breakers are mounted vertical.

Limitations apply.

A maximum of (3) QJ/QR breakers may be mounted in a P2 Panel and are single mounted.

<sup>(</sup>a) A maximum of (4) QJ/QR breakers may be mounted in a P3 panel and are twin mounted.

## **General Specifications**

## **Typical Panelboard Modifications**

General

Lighting and	Distribution Panelb	Distribution Panelboards		
P1	P2	P3	S5	F2
	,			
Standard (20" W)	Standard (20" W)	Standard (24" W)	Standard	Standard
•	•	•	•	•
•	•	•	•	•
•	•	•	•	•
•	•	•	•	•
•	•	•	_	_
• (24"W)	• (24", 30" or 36"W)	• (30" or 36"W)	• (custom)	• (custom)
(7.75"D)	• (7.75"D)	• (custom)	• (custom)	• (custom)
Standard	Standard	Standard	•	•
I –	_	_	Standard	Standard
<u> </u>	_	_	•	•
•	•	•	(see Door-in-Door)	(see Door-in-Door
•	•	•	•	•
•	•	•	_	_
•	•	•	•	•
•	•	•	•	•
Standard	Standard	Standard	Standard	Standard
•	•	•	•	•
•	•	•	•	•
-	•	•	•	•
•	•	•	•	•
•	•	•	•	•
•	•	•	•	•
•	•	•	400 - 600A	400 - 600A
Standard	Standard	Standard	Standard	Standard
•	•	•	•	•
_	•	•	•	•
_	_	_	_	•
	P1  Standard (20" W)   (20" W)  (7.75"D)  Standard	P1         P2           Standard (20" W)         Standard (20" W)           •         •	Standard (20" W)         Standard (24" W)         Standard (24" W)           •         •         •           •<	P1         P2         P3         S5           Standard (20" W)         Standard (24" W)         Standard           (20" W)         •         •           •         •         •

Available as an option.

Not Available


## Trim / Front Dimensions

**Standard Trim (FAS-Latch)** (14 Gage Standard)


(Into stock includes surface or flush versions of this style in chart on page 11.

# Standard Trim (FAS-Latch) Typical Dimensions (Hinges available as shown on right side only)


(Typical 14 Gage Steel construction or approved equivalent)



	Surface	Flush	# of
Box Size	Α	Α	Hinges
26	26	27.5	2
32	32	33.5	2
38	38	39.5	2
44	44	45.5	3
50	50	51.5	3



	Surface	Flush	# of
Box Size	Α	Α	Hinges
56	56	57.5	3
62	62	63.5	3
68	68	69.5	3
74	74	75.5	3



Door in Door Front (14 Gage Standard)



Hinged to Box Front (14 Gage Standard)

## Also available

- Screw to Box Trim (14 Gauge Std.)
- Piano Hinge Trim (14 Gauge Std.)
  - a) Screw to box with Piano Hinge Door
  - b) Hinge to Box with Piano Hinge and Piano Hinge Door
  - c) Door-in-Door with Piano Hinge, Both Doors

#### **Special Enclosures Options**



**TYPE 3R/12 Enclosures** (Sizes vary by construction)



**TYPE 4 Enclosures/TYPE 4X Enclosures** (Sizes vary by construction)

## Panel Family Portrait



"P" Series Panelboard Family for Lighting and Appliance and Distribution Panel Applications

# **Distribution Connector Kits (Circuit Breakers)**

## Reference

Max Amp Rating	Breaker Family	Branch Breaker Type	Next Gen P1	P2	P3	S5	F2
100	General	BL, BLH, HBL, BQD6	No kit required	BBK32	BBKB32	6BL2C <sup>3</sup>	_
	General	NGB	No kit required <sup>①</sup>	BBKNB32	BBKNB32	SNBD	_
	General	NGB2, HGB2, LGB2	_	BBKGB32	BBKGB32	SGB2D	_
125	General	HEB	_	_	BBKEB32	SEBD	_
	Sentron	ED2, ED4, ED6, HED4	_	BBKED32	BBKED32	6E62 <sup>②③</sup>	_
	Sentron	CED6	_	BBKCED32	_	6CLE2 <sup>©</sup>	_
150	VL	NDG, LDG	_	_	_	SDGD	_
005	General Purpose	QJ2, QJH2, QJ2H	_	BBKQ1	BBKQ2	6QJ2 <sup>2</sup>	_
225	General Purpose	QR2, QR2H, HQR2, HQR2H	_	BBKQR1	BBKQR2	6QR2 <sup>2</sup> 4	_
	Sentron	FXD6, FD6, HFD6, HHFD6	_	_	_	6F62 <sup>②</sup>	_
250	VL	NFG, LFG	_	_	_	SFGD	_
	Sentron	CFD6	_	_	_	6CLF1C	_
	Sentron	JXD6, JD6, HJD6, HHJD6	_	_	_	6JJ62 <sup>②</sup>	_
400	VL (Single)	NJG, LJG	_	_	_	SJG1D	_
400	VL (Twin)	NJG, LJG	_	_	_	SJG2D	_
	Sentron	CJD6	_	_	_	6CLJ1C	_
	Sentron	LXD6, LD6, HLD6, HHLD6, SLD6, SHLD6	_	_	_	6LL61C	_
600	Sentron	CLD6	_	_	_	6CLL1C	_
	Sentron	SCLD6	_	_	_	6SCL61C	_
800	Sentron	MXD6, MD6, HMD6, CMD6, SHMD6, SCMD6	_	_	_	6M61C	_
1200	Sentron	NXD6, ND6, HND6, CND6, SHND6, SCND6	_	_	_	6N61C	_


① NGB branch breakers can be installed in P1 interior ending with

Suffix "-NGB" only.
 These are aluminum connectors. If copper is required please add suffix C.

 <sup>3.75&</sup>quot; plate accommodates six 1-pole breakers.
 For QR filler plate only, use p/n: 6QR2FK.

Features / Benefits Reference

The standard Siemens P1 panelboard has some unique features that make it easier to design for an engineer, easier to reconfigure in the field for a contractor, and easier to upgrade and maintain for the Owner. The P1 is the smallest panel in the Siemens lineup, with bus sizes up to 400A. What makes it different is the split neutral design and the open ended bus. In the Siemens panel, instead of the common single neutral bus on one end, we have a neutral bus on both sides that is cross-bussed. This makes branch wiring simpler and cleaner – the lead lengths for line and neutral can now be made nearly the same, creating more room and a neater installation. It also allows access to both ends of the bus as a standard feature – this provides the flexibility to make changes in the field, even if it wasn't part of the original configuration. Next Gen P1 introduced in 2015 has extended circuits up to 66 available and also non-feed thru versions are available, without the Subfeed Space, in a 6'' smaller enclosure.



The following can be done to a standard P1 panelboard in the field with no modifications:

- Change from top fed to bottom fed
- Add feed-through lugs<sup>①</sup>
- Add an Integral bus-mounted SPD<sup>①</sup>
- Add a sub feed breaker up to 250 amps<sup>①</sup>
- Change from Main Lugs to Main Breaker
- Change from Main Breaker to Main Lugs
- Panel may have up to two ground assemblies. Options are: (a) standard aluminum, (b) optional copper, or (c) optional insulated/isolated aluminum or copper. Mounting provisions in opposing corners of the box are standard. Any of these options may be added after installation.

① Only when Subfeed Space is selected/available.

## Distributor stock - Type P1 Ready To Assemble Panelboards

Type P1 ready to assemble panelboards are completely convertible from main lug to main breaker and vice-versa. Additionally, feed-thru lugs or subfeed circuit breakers up to 400 amperes can be added without increasing the box height for Next Gen P1 with "T" suffix, see the chart.


- 1. Compute total number of poles to determine interior catalog number. (Note: BL / BQD (or) or NGB Main Breaker will use unit space. The total number of poles should include 2 or 3 poles for 1-phase or 3-phase mains.
- 2. List catalog number of interior, box and front.
- 3. Select main lug kit or main breaker kit from appropriate tables.

## Reference

Note: Main/Subfeed Breaker mounting kits may be ordered with or without breakers included, see page 10-12 and 10-13 for selection.

- 4. List required branch circuit breakers and filler plates to cover any unused positions.
- 5. Select any modifications or accessories.

Note: Next Gen P1 was introduced in June 2015. All original P1 devices do not include the "Subfeed Space" Indicator. All original P1 included the Subfeed Space as standard.



NONE = BL/BQD type NGB = NGB type only

## **Branch Breakers**

Panel Type	Voltage (Max.)	Breaker Type	Additional Information
	240	BL, BLH, HBL, BQD, NGB	
Next Gen P1	480 / 277	BQD, NGB	See Page 10-13 and 10-14
	600 / 347	BQD6, NGB	

# Distributor Stock - Type P1 Ready To Assemble Panelboards

## 400A Max. - 20" Wide x 5.75" Deep

- 1. Choose the appropriate Interior from the table below.
- 2. Choose the Main Device: Main Lugs from page 10-12, Main Breaker Kit from pages 10-12 10-13.
- 3. Choose Branch Breakers. BL, BQD and NGB breakers from pages 10-13 10-14.
- 4. Choose Feed-Thru Lugs or Subfeed Breaker Kit from page 10-12.

Type P1 Into Stock Panelboards (Next Gen P1 introduced in June 2015)

Amps	Max. #of	Original Main Lugs Interior Cat. Number	Next Gen P1 Main Lug Interior Cat. Number	Original Main Convertible Interior Cat. Number	Next Gen P1 Main Convertible Interior Cat. Number	Box Size	Type 1 Encl.	Type 3R/12 Encl. <sup>①</sup>	Type 1 Front Surface	Type1 Front Flush
		re 120/240V	Cat. Ivuiliber	Cat. Ivuiliber	Cat. Number	Size	Enci.	Enci.⊕	Surrace	riusn
250	18 30 42 54	P1A18ML250A P1A30ML250A P1A42ML250A	P1A18MC250AT P1A30ML250AT P1A42ML250AT P1A54ML250AT	P1A18MC250A P1A30MC250A P1A42MC250A	P1A18MC250AT P1A30MC250AT P1A42MC250AT P1A54MC250AT	32 38 44 50	B32 B38 B44 B50	WP32 WP38 WP44 WP50	S32B S38B S44B S50B	F32B F38B F44B F50B
400	18 30 42 54	P1A18ML400A P1A30ML400A P1A42ML400A	P1A30ML400AT P1A42ML400AT P1A54ML400AT	P1A18MC400A P1A30MC400A P1A42MC400A	P1A30MC400AT P1A42MC400AT P1A54MC400AT	- 62 68 74	– В62 В68 В74	— WP62 WP68 WP74	- S62B S68B S74B	 F62B F68B F74B
250	18 30 42 54	P1A18ML250C P1A30ML250C P1A42ML250C	P1A18ML250CT P1A30ML250CT P1A42ML250CT P1A54ML250CT	P1A18MC250C P1A30MC250C P1A42MC250C	P1A18MC250CT P1A30MC250CT P1A42MC250CT P1A54MC250CT	32 38 44 50	B32 B38 B44 B50	WP32 WP38 WP44 WP50	S32B S38B S44B S50B	F32B F38B F44B F50B
400	18 30 42 54	P1A18ML400C P1A30ML400C P1A42ML400C	 P1A30ML400CT P1A42ML400CT P1A54ML400CT	P1A18MC400C P1A30MC400C P1A42MC400C	 P1A30MC400CT P1A42MC400CT P1A54MC400CT	- 62 68 74	— В62 В68 В74	— WP62 WP68 WP74	- S62B S68B S74B	 F62B F68B F74B
3-Phas		re 208Y / 120V	· · · · · · · · · · · · · · · · · · ·	T				1	L	
250	18 30 42 54	P1C18ML250A P1C30ML250A P1C42ML250A	P1C18ML250AT P1C30ML250AT P1C42ML250AT P1C54ML250AT	P1C18MC250A P1C30MC250A P1C42MC250A	P1C18MC250AT P1C30MC250AT P1C42MC250AT P1C54MC250AT	32 38 44 50	B32 B38 B44 B50	WP32 WP38 WP44 WP50	S32B S38B S44B S50B	F32B F38B F44B F50B
400	18 30 42 54	P1C18ML400A P1C30ML400A P1C42ML400A	P1C30ML400AT P1C42ML400AT P1C54ML400AT	P1C18MC400A P1C30MC400A P1C42MC400A	P1C30MC400AT P1C42MC400AT P1C54MC400AT	- 62 68 74	— В62 В68 В74	— WP62 WP68 WP74	- S62B S68B S74B	 F62B F68B F74B
250	18 30 42 54	P1C18ML250C P1C30ML250C P1C42ML250C	P1C18ML250CT P1C30ML250CT P1C42ML250CT P1C54ML250CT	P1C18MC250C P1C30MC250C P1C42MC250C	P1C18MC250CT P1C30MC250CT P1C42MC250CT P1C54MC250CT	32 38 44 50	B32 B38 B44 B50	WP32 WP38 WP44 WP50	S32B S38B S44B S50B	F32B F38B F44B F50B
400	18 30 42	P1C18ML400C P1C30ML400C P1C42ML400C	P1C30ML400CT P1C42ML400CT	P1C18MC400C P1C30MC400C P1C42MC400C	P1C30MC400CT P1C42MC400CT P1C54MC400CT	- 62 68	– В62 В68	— WP62 WP68	- S62B S68B	– F62B F68B
2 Phon	54	- 600V/247V	P1C54ML400CT	<u> </u>	P1C54IVIC4UUC1	74	B74	WP74	S74B	F74B
250	18 30 42 54	re 600Y/347V P1L18ML250A P1L30ML250A P1L42ML250A	P1L18ML250AT P1L30ML250AT P1L42ML250AT P1L54ML250AT	P1L18MC250A P1L30MC250A P1L42MC250A	P1L18MC250AT P1L30MC250AT P1L42MC250AT P1L54MC250AT	32 38 44 50	B32 B38 B44 B50	WP32 WP38 WP44 WP50	S32B S38B S44B S50B	F32B F38B F44B F50B
400	18 30 42 54	P1L18ML400A P1L30ML400A P1L42ML400A	P1L30ML400AT P1L42ML400AT P1L54ML400AT	P1L18MC400A P1L30MC400A P1L42MC400A	P1L30MC400AT P1L42MC400AT P1L54MC400AT	- 62 68 74	— В62 В68 В74	— WP62 WP68 WP74	- S62B S68B S74B	 F62B F68B F74B
250	18 30 42 54	P1L18ML250C P1L30ML250C P1L42ML250C	P1L18ML250CT P1L30ML250CT P1L42ML250CT P1L54ML250CT	P1L18MC250C P1L30MC250C P1L42MC250C	P1L18MC250CT P1L30MC250CT P1L42MC250CT P1L54MC250CT	32 38 44 50	B32 B38 B44 B50	WP32 WP38 WP44 WP50	S32B S38B S44B S50B	F32B F38B F44B F50B
400	18 30 42 54	P1L18ML400C P1L30ML400C P1L42ML400C	 P1L30ML400CT P1L42ML400CT P1L54ML400CT	P1L18MC400C P1L30MC400C P1L42MC400C	 P1L30MC400CT P1L42MC400CT P1L54MC400CT	- 62 68 74	— В62 В68 В74	— WP62 WP68 WP74	- S62B S68B S74B	 F62B F68B F74B
Interio		NGB Breakers — 3-Pl	hase, 4-Wire 600Y/34	17V						
250	18 30 42 54	_ _ _ _	P1L18ML250AT-NGB P1L30ML250AT-NGB P1L42ML250AT-NGB P1L54ML250AT-NGB	- - -	P1L18MC250AT-NGB P1L30MC250AT-NGB P1L42MC250AT-NGB P1L54MC250AT-NGB		B32 B38 B44 B50	WP32 WP38 WP44 WP50	S32B S38B S44B S50B	F32B F38B F44B F50B
400	18 30 42 54	- - -	P1L30ML400AT-NGB P1L42ML400AT-NGB P1L54ML400AT-NGB	- - -	P1L30MC400AT-NGB P1L42MC400AT-NGB P1L54MC400AT-NGB	68	- B62 B68 B74	— WP62 WP68 WP74	- S62B S68B S74B	 F62B F68B F74B
250	18 30 42 54	_ _ _	P1718ML250CT-NGB P1730ML250CT-NGB P1742ML250CT-NGB P1L54ML250CT-NGB	- - -	P1L18MC250CT-NGB P1L30MC250CT-NGB P1L42MC250CT-NGB P1L54MC250CT-NGB	32	B32 B38 B44 B50	WP32 WP38 WP44 WP50	S32B S38B S44B S50B	F32B F38B F44B F50B
400	18 30 42 54	_ _ _ _	P1L30ML400CT-NGB P1L42ML400CT-NGB P1L54ML400CT-NGB	_ _ _ _	P1L30MC400CT-NGB P1L42MC400CT-NGB P1L54MC400CT-NGB	- 62 68	- B62 B68 B74	— WP62 WP68 WP74	- S62B S68B S74B	- F62B F68B F74B

## Reference









## **Warehouse Stock - Type P1 Panelboards**

## Lug Kits - Main or Feed Thru

Amp Rating	Matl.	Wire Range (includes Neutral)	Service	Original P1 Cat. No.	Next Gen P1 Cat. No.
	AL	(1) #6 AWG- 350 kcmil	1 Phase	MLKA1	MLKA1A
250	AL	(CU or AL)	3 Phase	MLKA3	MLKA3A
250	CU	(1) #6 AWG- 350 kcmil	1 Phase	MLKC1	MLKC1A
	CO	(CU or AL)	3 Phase	MLKC3	MLKC3A
	AL	(2) 1/0 - 250 kcmil or	1 Phase	4MLKA1	4MLKA1A
400	AL	(1) #2 AWG-600 kcmil	3 Phase	4MLKA3	4MLKA3A
400	CU	(2) 1/0 - 4/0	1 Phase	4MLKC1	4MLKC1A
	CU	or (1) 1/0 - 600 kcmil	3 Phase	4MLKC3	4MLKC3A
400	(2) AL/CLI 250 kcmil may	1 Phase	_	4MLKA1B	
400	[max.(1) 600 kcmil C wire]		3 Phase	_	4MLKA3B

## Breaker Mounting Kits 250A Max. - Main or Subfeed w/o Breaker

Amp Rating	Breaker Types	Service	Original P1 Cat. No.	Next Gen P1 Cat. No. <sup>2</sup>
100A	BL, BLH, HBL	1-Phase	MBKBL1	MBKBL1A
TOUA	BE, BEH, HBE	3-Phase	MBKBL3	MBKBL3A
100A	BQD	1-Phase	_	MBKBC1NBA
TOUA	BQD	3-Phase	_	MBKBC3NBA
125A	NGB	1-Phase	MBKNB1	MBKBC1NBA
125A	INGB	3-Phase	MBKNB3	MBKBC3NBA
125A	ED4, ED6, HED4, HED6	1-Phase	MBKED1	MBKED1A
125A	ED4, ED6, HED4, HED6 	3-Phase	MBKED3	MBKED3A
225A	QJ2, QJH2, QJ2H	1-Phase	MBKQJ1	MBKQJ1A
225A	Q32, Q3H2, Q32H 	3-Phase	MBKQJ3	MBKQJ3A
225A <sup>3</sup>	QR2, QRH2, HQR2, HQR2H	1-Phase	MBKQR1	MBKQR1A
ZZSA®	UR2, URH2, HUR2, HUR2H	3-Phase	MBKQR3	MBKQR3A
250A	EVDS EDS HEDS HEVDS	1-Phase	MBKFD1	MBKFD1A
250A	FXD6, FD6, HFD6, HFXD6	3-Phase	MBKFD3	MBKFD3A
400A <sup>①</sup>	JXD2, JD6, JXD6,	1-Phase	MBKJD1	MBKJD1A
400A	HJD6, HJXD6	3-Phase	MBKJD3	MBKJD3A

## Copper Neutral Lug Kits - 250A

No.of Circuits	Description	Original P1 Cat. No.	Next Gen P1 Cat. No.
18		CNKL18	Use 30 ckt kit
30	2 or 4 Branch Neutral Strips, 1 Main Neutral Lug, Hardware	CNKL30	CNLK30A
42		CNKL42	CNLK42A
54, 66		_	CNLK54A

## 2/0 Neutral Lug Kits - 250A and 400A

18		_	Use 30 ckt kit
30	2 or 4 Branch Neutral Strips,	_	LNLK30A
42	Hardware	_	LNLK42A
54, 66		_	LNLK54A

## 200% Neutral Lug Kits/250A

18	2 or 4 Branch Neutral Strips,	2NLK18	Use 30 ckt kit
30		2NLK30	2NLK30A
42		2NLK42	2NLK42A
54, 66		_	2NLK54A

## 200% Neutral Lug Kits/400A

18	2 or 4 Branch Neutral Strips,	42NLK18	Use 30 ckt kit
30		42NLK30	42NLK30A
42		42NLK42	42NLK42A
54, 66		_	42NLK54A

- ① 400 amp kit is for main only not allowed for subfeed breaker.
- ② MBKBFA kit is available to mount BL/BQD/NGB 2-pole or 3-pole in unit space as a "Back-Fed Main". This occupies branch space and reduces circuit count by 2 or 3 positions. (includes Neutral Lug, "MAIN" label and instructions)".

  Although QR is rated 250A, it is limited to 225A in panelboard.
- @ Original P1 kits will not work with Next Gen P1 interiors if the chart shows different part numbers for each.





MBKFD3A



#### Miscellaneous Parts and Accessories

Catalogue			
Number	Description Oil LP4 P		
BK1	Bonding Kit for 400A max. Original P1 Panels		
BK1A	Bonding Kit for 400A max. Next Gen P1 Panels		
BK2	Bonding kit for S1/S2 400 & 600		
ВК3	Bonding kit for S3 Panel		
IMK1	Interior Adjusting Kit		
11-1824-01	Directory Card Holder		
LPDC01	Directory Card (Pack of 10; ref. 12-1110-01)		
MCHK	Metal Card Holder Kit		
NBK03	Number Strips 1–42. Stick-on type; Use w/ P1 series Panels		
NBK04	Number Strips 43–84. Stick-on type; Use w/ P1 series Panels		
NBK05	Number Strips 85–126. Stick-on type; Use w/ P1 series Panels		
NBK06	Number Strips 127–168. Stick-on type; Use w/ P1 series Panels		
EGK	AL Ground Bus 44 Connections		
ECGK	CU Ground Bus 44 Connections		
IGK	Insulated AL Ground Bus		
ICGK	Insulated CU Ground Bus		
EWK1	End Wall Kit with Knockouts (20" W x 5.75" DP)		
EWK2	End Wall Kit with Knockouts (24" W x 7.75" DP)		
P1SCRWS	Package of 42 breaker mounting screws for P1		
DFFP1	1" Branch circuit filler plate (suitable for replacing QF3 in P1 thru P5 Panelboards and Switchboards)		
P1CONBPHCU <sup>①</sup>	Connector kit – 6 pcs. B-phase Copper		
P1CONBPHAL®	Connector kit – 6 pcs. B-phase Aluminum		
P1CONACPHCU <sup>①</sup>	Connector kit – 6 pcs. A or C-phase Copper		
P1CONACPHAL <sup>①</sup>	Connector kit – 6 pcs. A or C-phase Aluminum		
MBKQRFK	P1/Next Gen P1 Filler for 1PH/3PH QR. Horizontal mount only.		
TPS9IKITP1	Original P1 mounting bracket for SPD TPS3 09		
TPS9IKITP1A	Next Gen P1 mounting bracket for SPD TPS3 09		

- ® Next Gen P1 kits will not work with Original P1 interiors if the chart shows different part numbers for each.
- ® Replacement parts only.
- @ PDF can be downloaded and printed at this location: http://www.nema.org/ standards/pages/Panelboards.aspx (ref. Material #11-1056-01)

## **Warehouse Stock – Type P1 Panelboards**

## Main Breaker Mounting Kits with Breakers for P1 Panels (250A and

lower can be used as subfeed kits also)

Nex Gen P1		Ratings	
Catalogue No.	Description	240V	600V
MBKED33100A	Kit w/3-pole ED6 100A breaker	65kA	18kA
MBKED33125A	Kit w/3-pole ED6 125A breaker	65kA	18kA
MBKQR12225A	Kit w/2-pole QR2 225A breaker	10kA	_
MBKQR33150A	Kit w/2-pole QR2 150A breaker	10kA	_
MBKQR33200A	Kit w/2-pole QR2 200A breaker	10kA	_
MBKQR33225A	Kit w/2-pole QR2 225A breaker	10kA	_
MBKFD33200A	Kit w/3-pole FXD6 200A breaker	65kA	22kA
MBKFD33225A	Kit w/3-pole FXD6 225A breaker	65kA	22kA
MBKFD33250A	Kit w/3-pole FXD6 250A breaker	65kA	22kA
MBKHF33250A	Kit with 3-Pole HFD6 250A Breaker	100kA	25kA
MBKJD33400A <sup>①</sup>	Kit w/2-pole JXD6 300A breaker	65kA	25kA

NOTE: "Next Gen P1" Kits above only work for interior numbers ending in "T" or "N". Use "Original P1" main connector kits and loose breaker for all others.

## **GFCI Personnel Protection (5MA)**

			Interrupting Ratings (kA) RMS Symmetrical Amperes		
Breaker	Ampere	Catalogue	Volts AC		
Туре	Rating	Number	120	120/240	240
BLF2 1-Pole	15 20 30	BF115A BF120A BF130A	10	_	_
BLFB 2-Pole	15 20 30 40 50 60	BF215A BF220A BF230A BF240A BF250A BF260A	_	10	-
BLHF2 1-Pole	15 20 30	BF115AH BF120AH BF130AH	22	_	-
BLHFB 2-Pole	15 20 30 40 50 60	BF215AH■ BF220AH BF230AH BF240AH■ BF250AH■ BF260AH	_	22	_
HBLF2 1-Pole	15 20 30	BF115AHH BF120AHH BF130AHH	65	_	_



**300A Main installed.**These Next Gen P1 kits can now be used as top or bottom feed.

## **AFCI – Combination Type Arc Fault Circuit Interrupter**

			Interrupting Ratings (kA) RMS Symmetrical Amperes		
Breaker	Ampere	Catalogue	Volts AC		
Туре	Rating	Number	120	120/240	240
BAF2	15	BA115AFC	10	_	_
1-pole	20	BA120AFC	10	_	_
BAFH2	15	BA115AFCH	22	_	_
1-pole	20	BA120AFCH	22	_	_
HBAF2	15	BA115AFCHH	65	-	_
1-pole	20	BA120AFCHH	65	_	_
BAF	15	B215AFC	_	10	_
2-pole	20	B20AFC	_	10	_
BAF2	15	B215AFCH	_	22	_
2-pole	20	B220AFCH	_	22	_

## **Dual Function AFCI/GFCI Circuit Breakers**

			Interrupting Ratings (kA) RMS Symmetrical Amperes		
Breaker	Ampere	Catalogue	Volts AC		
Туре	Rating	Number	120	120/240	240
BFGA2	15	B115DF	10	_	_
1-pole	20	B120DF	10	_	_
BFGAH2	15	B115DFH	22	_	_
1-pole	20	B120DFH	22	_	_
HBFGA2	15	B115DFHH	65	_	_
1-pole	20	B120DFHH	65	-	_

## **Warehouse Stock/Unassembled – Type P1 Panelboards**

Selection

Branch Breakers Selection for P1

## **Selection Guide**

- 1. Select breaker type.
- 2. Select required amperage.
- 3. Select number of poles.
- 4. Select branch breaker catalog numbers.
- 5. Select ground bar and filler plates. (See replacement parts & accessories on page 10-12.)

## BL Branch Breakers - 10,000A IR<sup>1</sup>

Amp	1-Pole	2-Pole	2-Pole	3-Pole
Rating	120/240V	120/240V	240V	240V
15	B115	B215	B215R	B315
20	B120	B220	B220R	B320
25	B125	B225	B225R	B325
30	B130	B230	B230R	B330
35	B135	B235	B235R	B335
40	B140	B240	B240R	B340
45	B145	B245	B245R	B345
50	B150	B250	B250R	B350
55	B155	_	_	_
60	B160	B260		B360
70	B170	B270	_	B370
80	—	B280		B380
90 100	_	B290 B2100	_	B390 B3100

## BLH Branch Breakers - 22,000A IR<sup>①</sup>

Amp	1-Pole	2-Pole	3-Pole
Rating	120/240V	120/240V	240V
15	B115H	B215H	B315H
20	B120H	B220H	B320H
25	B125H	B225H	B325H
30	B130H	B230H	B330H
35	B135H	B235H	B335H
40	B140H	B240H	B340H
45	B145H	B245H	B345H
50	B150H	B250H	B350H
55	B155H	_	_
60	B160H	B260H	В360Н
70	B170H	B270H	B370H
80	-	B280H	B380H
90		B290H	B390H
100		B2100H	B3100H

## HBI Branch Breakers - 65 0004 IR<sup>1</sup>

TIBL Branch Breakers 05,000A III				
Amp	1-Pole	2-Pole	3-Pole	
Rating	120/240V	120/240V	240V	
15	B115HH	B215HH	B315HH	
20	B120HH	B220HH	B320HH	
30	B130HH	B230HH	B330HH	
40	B140HH	B240HH	B340HH	
50	B150HH	B250HH	B350HH	
60	—	B260HH	B360HH	
70		B270HH	B370HH	
80		B280HH	B380HH	
90		B290HH	B390HH	
100		B2100HH	B3100HH	

## BQD Branch Breakers - 14,000A IR Max. @ 480/277 Vac / 65,000A IR max. @ 240 Vac<sup>2</sup>

Amp Rating	1-Pole 277V	2-Pole 480Y/277V	3-Pole 480Y/277V
15	BQD115	BQD215	BQD315
20	BQD120	BQD220	BQD320
25	BQD125	BQD225	BQD325
30	BQD130	BQD230	BQD330
35	BQD135	BQD235	BQD335
40	BQD140	BQD240	BQD340
45	BQD145	BQD245	BQD345
50	BQD150	BQD250	BQD350
55	BQD155	BQD255	BQD355
60	BQD160	BQD260	BQD360
70	BQD170	BQD270	BQD370
80	BQD180	BQD280	BQD380
90	BQD190	BQD290	BQD390
100	BQD1100	BQD2100	BQD3100

## BQD6 Branch Breakers - 10,000A IR max. @ 600/347 Vac

	Catalogue Number				
Ampere Rating	1-Pole 347V	2-Pole 600Y/347V	3-Pole 600Y/347V		
15	BQD6115	BQD6215	BQD6315		
20	BQD6120	BQD6220	BQD6320		
25	BQD6125	BQD6225	BQD6325		
30	BQD6130	BQD6230	BQD6330		
35	BQD6135	BQD6235	BQD6335		
40	BQD6140	BQD6240	BQD6340		
45	BQD6145	BQD6245	BQD6345		
50	BQD6150	BQD6250	BQD6350		
60	BQD6160	BQD6260	BQD6360		
70	BQD6170	BQD6270	BQD6370		

## **NGB Family Branch Breakers**

NGB - 14,000A IR Max. @ 600Y/347V AC / 100,000A IR @ 240V AC

Amp	1-pole	2-pole	3-pole
Rating	347V	600Y/347V	600Y/347V
15	NGB1B015B	NGB2B015B	NGB3B015B
20	NGB1B020B	NGB2B020B	NGB3B020B
25	NGB1B025B	NGB2B025B	NGB3B025B
30	NGB1B030B	NGB2B030B	NGB3B030B
35 40	NGB1B035B	NGB2B035B	NGB3B035B
45	NGB1B040B	NGB2B040B	NGB3B040B
	NGB1B045B	NGB2B045B	NGB3B045B
50	NGB1B043B NGB1B050B	NGB2B049B NGB2B050B	NGB3B043B
60	NGB1B060B	NGB2B060B	NGB3B060B
70	NGB1B070B	NGB2B070B	NGB3B070B
80	NGB1B080B	NGB2B080B	NGB3B080B
90	NGB1B090B	NGB2B090B	NGB3B090B
100	NGB1B100B	NGB2B100B	NGB3B100B
110	NGB1B110B	NGB2B110B	NGB3B110B
125	NGB1B125B	NGB2B125B	NGB3B125B

② To add shunt trip to BQD breakers, see Breaker Accessories.

## **Panelboard Replacement, Modification, and Additions**

Selection

S1/S2 Panels—All the original P1 panel kits for 250 amp and below panels will work for 250 amp maximum S1/S2 panels.

Note: Nex Gen P1 kits will not work with S1/S2

## 400/600 Amp S1/S2 and All SE Panels

## Lug Kits — Main or Feed Thru

Ampere Rating	Material	Wire Range	Service	Catalogue Number
125A/250A	Al/Cu	(2) 1/0–250 kcmil	1-Phase	MLKA1
125A/250A	Al/Cu	(2) 1/0–250 kcmil	3-Phase	MLKA3
400A/600A	Al/Cu	(2) #3/40—250 kcmil or (1) 3/0-500 kcmil	1-Phase	SMLKA1
400A/600A	Al/Cu	(2) #3/40—250 kcmil or (1) 3/0-500 kcmil	3-Phase	SMLKA3

## **Breaker Mounting Kits**

Ampere Rating	Breaker Types	Service	Catalogue Number
125A	ED2, ED4, ED6, HED4, HED6, HHED6	1-Phase	SMBKED1
225A	ED2, ED4, ED6, HED4, HED6, HHED6	3-Phase	SMBKED3
225A	QJ2, QJH2, QJH2 <sup>®</sup>	1-Phase	SMBKQJ1
225A	QJ2, QJH2, QJH2 <sup>①</sup>	3-Phase	SMBKQJ3
250A	FXD6, FD6, HFXD6, HFD6	1-Phase	SMBKFD1
250A	FXD6, FD6, HFXD6, HFD6	3-Phase	SMBKFD3
400A	JD6, JXD6, HJD6, HJXD6	1-Phase	SMBKJD1
400A	JD6, JXD6, HJD6, HJXD6	3-Phase	SMBKJD3
600A	LD6, LXD6, HLD6, HLXD6	1-Phase	SMBKLD1
600A	LD6, LXD6, HLD6, HLXD6	3-Phase	SMBKLD3

## **Neutral Kits**

Ampere Rating	Description	Catalogue Number
250A max.	30/42 circuit 200% neutral kit	2NLK2
400/600A max.	42 circuit 200% neutral kit	2NLK1

## For CDP-7 and S3

## **Breaker Mounting Kits**

Ampere Rating	Breaker Types	Material	Catalogue Number
70A	BQD6	Aluminum	7BQD6-2
70A	BQD6	Copper	7BQD6-2C
100A	BL	Aluminum	7BL-2
100A	BL	Copper	7BL-2C
100A	BQD	Aluminum	7BQ-2
100A	BQD	Copper	7BQ-2C
125A	ED2, ED4, ED6, HED4	Aluminum	7E6-2
125A	ED2, ED4, ED6, HED4	Copper	7E6-2C
225A	QJ2, QJH2, QJH2	Aluminum	7QJ3-2
225A	QJ2, QJH2, QJH2	Copper	7QJ3-2C

## For CDP-6, VB-6, SPP-6 and FPP6:

## **Breaker Mounting Kits**

Dicaker Woulding Kits							
Ampere Rating	Breaker Types	Material	Catalogue Number				
100A	BL	Copper	6BL2C				
125A	ED2, ED4, ED6, HED4	Copper	6E62C				
125A	CED6	Copper	6CLE2C				
225A	QJ2, QJH2, QJH2	Copper	6QJ2C				
250A	FD6, FXD6, HFD6	Copper	6F62C				
400A	JXD6, JD6, HJD6, SJD6	Copper	6JJ62C				

#### **Factory Assembled** Selection 2 0 **NGB** 5 Catalogue Numbering System **Type of Panel** P1, P2, P3, S5, F2 \_\_ Voltage and System\* -C = 208Y/12030/4W Wye AC - All R = 415/24030/4 W Wye AC - AllE = 480Y/277 3Ø 4 W Wye AC - All S = 440/250 3Ø 4 W Wye AC - All D = 240 3Ø 3 W Delta AC - All L = 600/34730/4 W Wye AC - AllF = 480 3Ø 3 W Delta AC - All T = 230 3Ø 3 W Delta AC - All **G** = 600 3Ø 3 W Delta AC - P2, P3, P4, P5 W = 380 3Ø 3 W Delta AC - P2, P3, P4, P5 I = 347 3Ø 3 W Delta AC P2, P3, P4, P5 1 = 24V DC 1-Pole Branch Only - P2, P3, P4, P5 **B** = 240/120 3Ø 4 W Delta BØ High Leg AC - P2, P3, P4, P5 **2** = 24V DC 2-Pole Branch Only - P2, P3, P4, P5 Q = 240/120 3Ø 4 W Delta CØ High Leg AC - P2, P3, P4, P5 3 = 48V DC 1-Pole Branch Only - P2, P3, P4, P5 **4** = 48V DC 2-Pole Branch Only - P2, P3, P4, P5 **A** = 120/240 1Ø 3 W Grounded Neutral AC - All H = 120 10/2 W Grounded Neutral AC - P2, P3, P4, P5 5 = 125V DC 1-Pole Branch Only - P2, P3, P4, P5 **N** = 125V DC 2-Pole Branch Only - P2, P3, P4, P5 $J = 240 \, 1\% \, 2 \, \text{W} \, \text{No Neutral AC - All}$ Y = 125 10 2 W Grounded Neutral AC - P2, P3, P4, P5 O = 125/250V DC 2-Pole Branch Only - P2, P3, P4, P5 P = 125/250V DC 2 & 3-Pole Branch - All**Z** = No Longer Available K = 220/127304 W Wye AC - AllU = 120V AC 3Ø3W - AIIM = 380/220 3Ø 4 W Wye AC - All V = 240V 3Ø3W Grounded B Phase - P2, P3, P4, P5 \*For any voltage system not listed, check with sales for availability. **Enclosure Height** Circuits P1 – 18, 30, 42, 54, 66 P2 – 18, 30, 42, 54, 66, 78, 90 P3 – 18, 30, 42, 54, 66, 78, 90 S5, F2 - 60, 75, 90 Main Lug (ML), Main Breaker (See Main Breaker Table coding below) Amperage -100-400A = P1400-800A = P3100-600A = P2400-1200A = S5, F2Bus Bus Bus Code<sup>o</sup> **P2** Р3 Material **Plating S5** F2 Tin-Plated Α Aluminum · Indicates default С Tin-Plated Copper optional optional optional n/a n/a for this bus type. Silver-Plated Copper optional optional optional **Feed Location** T = TopB = BottomMounting S = SurfaceF = Flush. Flush trims extend 1 1/2" beyond the base box dimensions on P1, P2 and P3. T = Subfeed Space Included N<sup>2</sup> = No Subfeed Space -Subfeed Space Indicator (for P1 only)

Branch Breaker Type

NONE = BL/BQD type NGB = NGB type only

## **Main Breaker Coding**

Code	Breaker Type	Code	Breaker	Code	Breaker	Code	Breaker Type	Code	Breaker Type	Code	Breaker Type	Code	Breaker Type	Code	Breaker Type
BL	BL	H2	HFXD6	J6	JD6	L6	LD6	MD	MD6	ND	ND6	L3	LLK	N8	HNG
	DL	-	ПГЛО	36	300		LD0			1	-		-	1	
BH	BLH	H1	HHFD6	JD	JXD2	LX	LXD6	MX	MXD6	NX	NXD6	J2	NJG	N2	HNX
BR	BLR	Н3	HHFXD6	JX	JXD6	LH	LXD6H	MH	MXD6H	NT	NXD6H	J1	NJX	N5	HNY
НВ	HBL	G2	HGB	JH	JXD6H	S1	SCLD6	SO	SCMD6	SR	SCND6	J4	NJY	N9	LNG
BQ	BQD	G3	LGB	SC	SCJD6	S2	SHLD6	SQ	SCMD6H	ST	SCND6H	L2	HLK	N3	LNX
B6	BQD6	NB	NGB	SX	SHJD6	SL	SLD6	S5	SHMD6	AD	SHND6	L7	NLK	N6	LNY
CE	CED6	G4	NGB2	SY	SHJD6H	QJ	QJ2	S6	SHMD6H	SD	SHND6H	M5	HMG	N7	NNG
E4	ED4	G5	HGB2	SJ	SJD6	Q2	QJ2H	SM	SMD6	SN	SND6	M2	HMX	N1	NNX
E6	ED6	G6	LGB2	SH	SJD6H	QH	QJH2	AX	SMD6H	AY	SND6H	M8	HMY	N4	NNY
H4	HED4	CJ	CJD6	CL	CLD6	C9	CMD6	CN	CND6	J6	HJG	M6	LMG	QR	QR2
НА	HHED6	6H	HHJD6	HH	HHLD6	СН	CMD6H	C6	CND6H	J7	HJX	M3	LMX	Q4	QRH2
CF	CFD6	H9	HHJXD6	XH	HHLXD6	HM	HMD6	HN	HND6	J5	HJY	M9	LMY	Q5	HQR2
FD	FD6	H6	HJD6	HL	HLD6	HR	HMXD6	HT	HNXD6	J9	LJG	M4	NMG	Q6	HQR2H
FX	FXD6	H5	HJXD6	НО	HLXD6	HS	HMXD6H	HX	HNXD6H	J3	LJX	M1	NMX	Q7	QR2-MCS
HF	HFD6	H7	HJXD6H	HP	HLXD6H	<u> </u>	_	_	_	J8	LJY	M7	NMY	<b> </b>	_

<sup>&</sup>lt;sup>®</sup> Standard bussing in P1, P2 and P3 panels is tin-plated for aluminum and copper.

② Not available for Next Gen P1 NGB interiors.

## Next Gen Type P1

600Y/ 347 Vac Maximum 400 Ampere Mains 400 Ampere Maximum Branch Short Circuit Rating — 200,000 A. @ 240 Vac / 100,000 A. @ 600Y/347 Vac. IR Maximum

**Circuit Breaker / Lighting and Distribution** 

## **Branch Breaker Symmetrical** Interrupting Capacity

**Based on CSA's Test Procedure** Feed thru and subfeed lugs may result in lower interrupting ratings if not protected

by a main device. Consult sales office.

#### **Panelboards**

Certified by CSA under file #165172 and listed by Underwriters' Laboratories, Inc., under "Panelboards" File #E2269 for interiors and #E4016 for boxes and fronts.

#### Service

1-phase 2-wire - 120 Vac, 240 Vac,

1-phase 3-wire - 120/240 Vac,

3-phase 3-wire - 480Y/277 (when derived from 3-phase 4-wire system), 240 Vac, 120 Vac

3-phase 4-wire - 208Y/120 Vac, 480Y/277 Vac, 600Y/347 Vac, 380/220 Vac.

#### **Panelboard Fronts and Doors**

Standard panelboards are furnished with trim featuring concealed fasteners and hinges with a flush door lock. All are factory-assembled for ease of installation. Fronts are fabricated from code gauge steel and finished ANSI-61. See page <?> for optional fronts.

## Main Breakers

BL, BLH, HBL, NGB, BQD, BQD6, ED4, ED6, HED4, QJ2, QJH2, QJ2H, QR2, QRH2, HQR2, HQR2H, FXD6, FD6, HFD6, HFXD6, JXD6, JD6, HJXD6, HJD6. (All main breakers except 400 amp frame are mounted horizontal.)

Note: All Next Gen P1 interiors with BL, BQD or GB Type Mains are Back-fed in unit space (GB Type = NGB).BQD, BQD6

#### **Main Breaker Panel Connectors**

Ampere Rating	Connectors Suitable for Cu or Al
100	(1)—#14 1/0 AWG
125	(1)—#4 1/0 AWG
225	(1)—#4 AWG-300 kcmil
250	(1)—#4/0 AWG-350 kcmil Al (1)—#6/0 AWG-350 kcmil Cu
400 <sup>①</sup>	(2)—#3/0 AWG-250 kcmil Al or (1)—#3/0 AWG-500 kcmil Al

Connector ranges indicated do not apply to all main breaker types. Refer to molded case circuit breaker standard pressure wire connector chart (Section 5) for the connector range of a specific frame.

#### **Main Lug Connectors**

125	(1)—#6 AWG-350 kcmil
250	(1)—#6 AWG–350 kcmil
400 std.	AL (2) 110-250 kcmil or (1) #2 AWG–600 kcmil
400 opt.	CU (2) 1/0–4/0 or (1) 110–600 kcmil
400 opt.	AL (1) AL 1/0-750 kcmil (2) AL/CU 250 kcmil max. [max. (1) 600 kcmil (1) wire]

#### **Boxes**

20" wide, 5.75" deep

- End walls are blank as standard.
- . End walls with knockouts will be supplied at no charge on 5.75" deep panels if requested at time of order.

#### Main Breaker **Gutter Dimensions - Inches**

	Side Gutter	Neutral Location	
	20"	24"	20"
Main Breaker	w/box	w/box	w/box
BL, BLH, HBL, BQD, BQD6	8.500	10.5	11.5
NGB	8.000	10	11.5
ED4, ED6, HED4	6.125	8.125	11.5
QJ2, QJH2, QJ2H	6.500	8.5	11.5
QR2, QRH2, HQR2,HQR2H	6.500	8.5	11.5
FD6, FXD6, HFD6, HFDX6	5.250	7.25	11.5
JD6 <sup>2</sup> , JXD6 <sup>2</sup>	15.000	15	26.75

## Main Lug End Gutter **Dimensions - Inches**

Amp Rating	End Gutter	Neutral Location
125	10.500	11.5
250	10.500	11.5
400 <sup>③</sup>	25.500	26.75
	125 250	Rating         Gutter           125         10.500           250         10.500

<sup>3</sup> Feed-thru lug wire bending space is 15.000" (381mm) and neutral wire bending space is 15.880" (413mm) on 400A panel.

## Side Gutter Wiring Space - Inches

Reference Letter	Panel Width 20"	Panel Width 24" (Optional)
Α	6.375	7.375
В	5.500	7.5
С	6.125	8.125
D	6.500	8.5
E@	5.250	7.25
F	5.000	7

#### **Branch Breaker Side Gutters**

	BL, BLH, HBL	BL, BLH, HBL				
' / '	BLF, BLHF	BLF, BLHF	. /\ .			
←B→	BQD, BQD6	BQD, BQD6	<b>←</b> B →			
<b>←</b> C→	ED, ED4, E	ED, ED4, ED6, HED4				
<b>←</b> D→	QJ2, QJH QR2, QRH2, H					
<b>←</b> E→	FXD6, FD6, F					
<b>←</b> F→	NGB	NGB	<b>←</b> F →			

## Weight - Approximate

Total panelboard weight when filled with a normal quantity of breakers and accessories is:

About 3 lbs. per inch of box height

## Gauge Steel Boxes (Type 1)

Width	Height	Gauge Steel		
20"	All	#14		

Fronts — Sui	face, Flush (T	ype 1)
20"	All	#14

#### Series Connected Short Circuit Ratings

The term "Series Connected Short Circuit Rating" refers to the application of series connected circuit breakers in a combination that allows some breakers to have lower individual interrupting ratings than the available fault current. This is permitted as long as the series combination has been tested and certified by CSA.

The table below lists specific main and branch breaker series combinations that are marked on all P1 panels. All combinations shown have been tested for use in P1 panelboards and are CSA listed. Other combinations are available. See Circuit Breaker Section, of this book.

These series ratings must be specified on order at time of entry.

PANELBOARDS

<sup>@</sup> P1 panel limited to (1) subfeed 250 amperes max. See Branch Breaker Side Gutter Chart for Nex Gen P1 Backfed Options.


<sup>1</sup> P1 400 amp main breaker panels have wire bending space available for 600 kcmil.

<sup>2 400</sup>A main breaker is vertical mounted.

## **Circuit Breaker / Lighting and Distribution**

## Table P1-3 - Main Breaker Panel Size Selector - Next Gen P1

					Dimens	ions in in	ches (mm)	
Max	Main		Max #	Max #	Unit Sp	ace	Box Height	
Ampere rating	Breaker Types	Connections suitable for Cu or Al	Poles FT <sup>①</sup>	Poles NFT	FT A	NFT A	B	Weight in Lbs. (kg)
			_	18	_	9	26 (661)	90 (41)
	DI ® DI II®	#8-#6 AWG Cu or Al	18	30	9	15	32 (813)	105 (48)
100	BL <sup>2</sup> , BLH <sup>2</sup> , HBL <sup>2</sup> , BQD <sup>2</sup> ,	#8-6 AWG Cu or #8-4 AWG AI	30	42	15	21	38 (965)	120 (55)
100	BOD6 <sup>©</sup>	#8-#1 AWG Cu or	42	54	21	27	44 (1118)	135 (61)
	Babo	#6-#1/0 AWG AI	54	66	27	33	50 (1270)	150 (67)
			66	-	33	-	56 (1423)	165 (73)
	NGB <sup>©</sup>	15-30 amp: #14-#6 Cu or #12-#6 Al 35-125 amp: #6-1/0 Cu #4-2/0 Al	-	18	-	9	26 (661)	95 (43)
125	ED2, ED4	#14-#10 AWG Cu or	18	30	9	15	32 (813)	110 (50)
.20		#12-10 AWG AI #3-3/0 Cu or #1-2/0 AI	30	42	15	21	38 (965)	125 (57)
	EDO LIEDA		42	54	21	27	44 (1118)	140 (64)
	ED6, HED4		54	66	27	33	50 (1270)	155 (71)
		#3-3/0 Cu or #1-2/0 Al	66	-	33	-	56 (1423)	170 (78)
	QJ2, QJH2,		_	18	-	9	26 (661)	95 (43)
225	QJ2H QR2, QRH2,	#6 AWG-300 Kcmil (Cu) or #4 AWG-300 Kcmil (AI)	18	30	9	15	32 (813)	110 (50)
	HQR2, HQR2H	,	30	42	15	21	38 (965)	125 (57)
			42	54	21	27	44 (1118)	140 (64)
250	FXD6, FD6, HFD6, HFXD6	#6 AWG-350 Kcmil (Cu) or #4 AWG-350 Kcmil (AI)	54	66	27	33	50 (1270)	155 (71)
	חרטט, חראטט	#4 AVVG-350 KCMII (AI)	66	-	33	-	56 (1423)	170 (78)
			_	30	l -	15	56 (1423)	172 (78)
400	JD6, JXD6,	3/0-500 Kcmil (Cu) or	30	42	15	21	62 (1575)	190 (86)
400	HJD6, HJXD6	4/0-500 Kcmil (AI)	42	54	21	27	68 (1728)	208 (95)
	1107120		54	66	27	33	74 (1880)	226 (104)



Note: Main breakers use breaker connectors. For sizes, see breaker connector chart. 400A MLO Panels have wire bend space for 600kcmil CU & AL wire when using standard lugs. With optional 750kcmil AL/CU connectors, wire bend space is available for up to 750kcmil AL wire, but is still limited to 600kcmil CU wire.

#### Table P1-4 - Main Breaker Selection

Ampere	Breaker	Max. Ir (kA)	at		Main	
Rating	Types	240 AC	480/277V AC	600Y/347V	Breaker Code	Additional Trip Values
70	BQD6	65	_	10	B6	15, 20, 25, 30, 35, 40, 45, 50, 60, 70
	BL (STD)	10	14	_	BL	15, 20, 25, 30, 35, 40, 45, 50, 60, 70, 80, 90, 100
100	BLH	22	_	-	BH	15, 20, 25, 30, 35, 40, 45, 50, 60, 70, 80, 90, 100
100	HBL	65	-	-	HB	15, 20, 25, 30, 35, 40, 45, 50, 60, 70, 80, 90, 100
	BQD	65	_	_	BQ	15, 20, 25, 30, 35, 40, 45, 50, 60, 70, 80, 90, 100
	NGB (STD)	100	25	14	NB <sup>®</sup>	50, 60, 70, 80, 90, 100, 110, 125
125	ED6 (STD)	65	25	18	E4	50, 60, 70, 80, 90, 100, 110, 125
	HED4	42	42	_	H4	50, 60, 70, 80, 90, 100, 110, 125
	QJ2 (STD)	10	-	-	QJ	60, 70, 80, 90, 100, 110, 125, 150, 175, 200, 225
225	QJH2	22	-	_	QH	60, 70, 80, 90, 100, 110, 125, 150, 175, 200, 225
	QJ2H	42	-	-	Q2	60, 70, 80, 90, 100, 110, 125, 150, 175, 200, 225
	QR2	10	_	_	QR	100, 110, 125, 150, 175, 200, 225
225	QRH2	25	-	_	Q4	100, 110, 125, 150, 175, 200, 225
223	HQR2	65	-	_	Q5	100, 110, 125, 150, 175, 200, 225
	HQR2H	100	-	-	Q6	100, 110, 125, 150, 175, 200, 225
	FXD6 (STD)	65	35	22	FX	70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250
250	FD6	65	35	22	FD	70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250
250	HFD6	100	65	25	HF	70, 80, 90, 100, 150, 175, 200, 225, 250
	HFXD6	100	65	25	H2	70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250
	JXD2	65	-	_	JD	300, 400
	JXD6 (STD)	65	35	25	JX	200, 225, 250, 300, 350, 400
400	JD6	65	35	25	J6	200, 225, 250, 300, 350, 400
	HJD6	100	65	35	H6	200, 225, 250, 300, 350, 400
	HJXD6	100	65	35	H5	200, 225, 250, 300, 350, 400

 <sup>400</sup>A 66 circuit only available with non-feed thru versions.
 BL, BLH, HBL, BQD, BQD6,, and xGB mount in unit space and count in max. # of poles.
 xGB interiors are not available as non-feed-thru without sub-feed space.

Table P1-5 - Main Lug Panel Size Selector - Next Gen P1

			Dimension	ns in inches	(mm)			
	Max #	Max #	/lax # Unit Space					
Maximum Ampere rating	Poles FT	Poles NFT	FT A	NFT A	Box Height B"	Weight in Lbs. (kg)	MLO Connectors Suitable for	
		18	-	9	26 (661)	90 (41)		
	18	30	9	15	32 (813)	105 (48)		
125	30	42	15	21	38 (965)	120 (55)	(1) #6 AWG - 350 kcmil	
(or) 250	42	54	21	27	44 (1118)	135 (61)	(CU or AL)	
	54	66	27	33	50 (1270)	150 (67)		
	66	-	33	_	56 (1423)	165 (73)		
	-	30	-	15	56 (1423)	120 (55)	AL (2) 1/0 - 250 kcmil or	
400	30	42	15	21	62 (1575)	135 (61)	(1) #2 AWG - 600 kcmil	
	42	54	21	27	68 (1728)	150 (68)	CU (2) 1/0 - 4/0 or	
	54	66	27	33	74 (1880)	165 (75)	(1) #2 AWG - 600 kcmil	

## **Table P1-6 – Branch Circuit Breakers**

Max.			Max. I	Interrup	ting Ra	ating (k	A)				
Amp Rating	Breaker Type	Number of Poles	120V	120/ 240V	240V	277V	480/ 277V	347V	600Y/ 347V	Available Trip Values	Connections Suitable for Cu or Al
70	BQD6	1 2 3	- - -	65 65 –	- - 65	1 1 1	- - -	10 - -	- 10 10	15, 20, 25, 30, 35, 40, 50, 60, 70 15, 20, 25, 30, 35, 40, 50, 60, 70 15, 20, 25, 30, 35, 40, 50, 60, 70	15-40A #14-#6 AWG Cu #12-#6 AWG AI 45-70A #8-#1 AWG Cu #6-#1/0 AWG AI
	BL	1 2 3	10 - -	- 10 -	- - 10		- - -	- - -	- - -	15, 20, 25, 30, 35, 40, 45, 50, 55, 60, 70 15, 20, 25, 30, 35, 40, 50, 60, 70, 80, 90, 100 15, 20, 25, 30, 35, 40, 50, 60, 70, 80, 90, 100	
	BLR	2	-	-	10	-	-	-	_	15, 20, 30, 40, 50, 60, 70, 90, 100	
	BL	1 2	10 -	- 10	- -	-	- -	- -	- -	15, 20, 30 15, 20, 30	
	BLH	1 2 3	- - -	22 22 -	- - 22	- - -	- - -	- - -	- - -	15, 20, 30, 40, 50, 55, 60, 70 15, 20, 30, 40, 50, 60, 70, 90, 100 15, 20, 30, 40, 50, 60, 70, 80, 90, 100	15-20A #14-#10 AWG Cu #12-#10 AWG AI
	HBL	1 2 3	- - -	65 65 -	- - 65	- - -	- - -	-	- - -	15, 20, 30, 40, 50 15, 20, 30, 40, 50, 60, 70 15, 20, 30, 40, 50, 60, 70, 80, 90, 100	25-35A #8-#6 AWG Cu #8-#6 AWG AI 40-50A #8-#6 AWG Cu
100	BLF2 BLFB	1 2	10 -	- 10	-	-	-	-	-	15, 20, 30 15, 20, 30, 40, 50, 60	#8-#4 AWG AI 55-70A #8-#4 AWG Cu
	BLHF2 BLHFB	1 2	22 -	- 22	-	-	-	-	-	15, 20, 30 15, 20, 30, 40, 50, 60	#8-#2 AWG AI 80-100A #4-#1/0 AWG Cu #2-#1/0 AWG AI
	HBLF2	1	65	-	-	-	-	-	-	15, 20, 30	
	BLE	1 2	10 -	- 10	_ _		- -	- -	- -	15, 20, 30 15, 20, 30, 40, 50, 60	
	BLEH	1 2	22 -	- 22	_ _	-	- -	- -	- -	15, 20, 30 15, 20, 30, 40, 50, 60	
	BAF	1	10	-	-	-	-	-	-	15, 20	
	BAFH	1	22	-	-	-	-	-	-	15, 20	
	BQD	1 2 3	- - -	65 65 –	- - 65	14 - -	- 14 14	- - -	- - -	15, 20, 25, 30, 35, 40, 50, 60, 70, 80, 90, 100 15, 20, 25, 30, 35, 40, 50, 60, 70, 80, 90, 100 15, 20, 25, 30, 35, 40, 50, 60, 70, 80, 90, 100	15-40A #14-#6 AWG Cu #12-#6 AWG AI 45-100A #8-#1 AWG Cu #6-#1/0 AWG AI
125	NGB <sup>2</sup> 3	1 2 3	100 - -	- 100 100	- 100 100	25 - -	- 25 25	14 - -	- 14 14	15, 20, 25, 30, 35, 40, 50, 60, 70, 80, 90, 100, 125 <sup>3</sup> 15, 20, 25, 30, 35, 40, 50, 60, 70, 80, 90, 100, 125 <sup>3</sup> 15, 20, 25, 30, 35, 40, 50, 60, 70, 80, 90, 100, 125 <sup>3</sup>	15-30A #14-#6 Cu #12-#6 Al 35-125 #6-1/0 Cu #4-2/0 Al

NOTE: BL, HBL and BQD breakers are mounted in common mountings in 3" or (6) pole increments.

① Two-pole breaker is one phase and neutral. Three-pole is two phases and neutral.

P1 panel with NGB branch devices will not accept BL or BQD frames in the same panel as branch devices.

The New Next Gen P1 (18 circuit 250A only) is limited to 100A per connection (200A per pair) when installing Branch Breakers across from one another. All other configurations allow 125A per connection max. (250A per pair max.)

## Table P1-7 - Subfeed Breakers

Breaker	Number	Max. Interrupting Rating (kA)			
Туре	of Poles	240V	480Y/277V	600Y/347V	Available Trip Values
QJ2	2, 3	10	_	_	60, 70, 80, 90, 100, 110, 125, 150, 175, 200, 225
QJH2	2, 3	22	_	-	60, 70, 80, 90, 100, 110, 125, 150, 175, 200, 225
QJ2H	2, 3	42	_	-	60, 70, 80, 90, 100, 110, 125, 150, 175, 200, 225
QR2	2, 3	10	_	-	100, 110, 125, 150, 175, 200, 225
QRH2	2, 3	25	-	-	100, 110, 125, 150, 175, 200, 225
HQR2	2, 3	65	_	-	100, 110, 125, 150, 175, 200, 225
HQR2H	2, 3	100	_	-	100, 110, 125, 150, 175, 200, 225
ED6	2, 3	65	18	18	15, 20, 25, 30, 35, 40, 45, 50, 55, 60, 70, 80, 90, 100, 110, 125
HED4	2, 3	100	42	-	15, 20, 25, 30, 35, 40, 45, 50, 55, 60, 70, 80, 90, 100, 110, 125
FXD6	2, 3	65	35	22	70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250
FD6	2, 3	65	35	22	70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250
HFD6	2, 3	100	65	22	70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250
HFXD6	2, 3	100	65	25	70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250

## Table P1-8 - Breaker Mounting Kit Main or Subfeed Strap Kit w/o Breaker

Amp Rating	Breaker Types	Service	Original P1 Cat. No.	Next Gen P1 Cat. No. <sup>2</sup>
100A	BL, BLH, HBL	1-Phase	MBKBL1	MBKBL1A
IOUA	DL, DLII, IIDL	3-Phase	MBKBL3	MBKBL3A
100A	BOD	1-Phase	_	MBKBC1NBA
100A	ВОО	3-Phase	_	MBKBC3NBA
125A	NGB	1-Phase	MBKNB1	MBKBC1NBA
125A	INGD	3-Phase	MBKNB3	MBKBC3NBA
125A	ED4 ED6 HED4 HED6	1-Phase	MBKED1	MBKED1A
125A	ED4, ED6, HED4, HED6	3-Phase	MBKED3	MBKED3A
225A	0.12 0.1112 0.1211	1-Phase	MBKQJ1	MBKQJ1A
225A	QJ2, QJH2, QJ2H	3-Phase	MBKQJ3	MBKQJ3A
225A <sup>3</sup>	QR2, QRH2, HQR2,	1-Phase	MBKQR1	MBKQR1A
225A®	HQR2H	3-Phase	MBKQR3	MBKQR3A
250A	FXD6, FD6, HFD, HFXD6	1-Phase	MBKFD1	MBKFD1A
250A		3-Phase	MBKFD3	MBKFD3A
400A <sup>①</sup>	JXD6, JD6,	1-Phase	MBKJD1	MBKJD1A
400A	HJD6, HJXD6	3-Phase	MBKJD3	MBKJD3A

- $\ensuremath{\texttt{0}}$  400 amp kit is for main—only, not allowed for subfeed breaker.
- ② MBKBFA kit is available to mount BL/BQD/NGB 2-pole or 3-pole in unit space as a "Back-Fed Main". This occupies branch space and reduces circuit count by 2 or 3 positions. (includes Neutral Lug, "MAIN" label and instructions)".

  Although QR is rated 250A, it is limited to 225A in panelboard.

#### Table P1-9 - Lug Kits (Main or Feed-Thru)

		<u> </u>		-	
Amp Rating	Matl.	Wire Range (includes Neutral)	Service	Original Catalogue Number	Nex Gen P1 Catalogue Number
	AL	(1) #6 AWG-	1 Phase	MLKA1	MLKA1A
250	AL	350 kcmil (CU or AL)	3 Phase	MLKA3	MLKA3A
250	CU	(1) #6 AWG-	1 Phase	MLKC1	MLKC1A
	CO	350 kcmil (CU or AL)	3 Phase	MLKC3	MLKC3A
		(2) 1/0 - 250 kcmil		4MLKA1	4MLKA1A
400	AL	or (1) #2 AWG-600 kcmil	3 Phase	4MLKA3	4MLKA3A
	CU	(2) 1/0 - 4/0	1 Phase	4MLKC1	4MLKC1A
	CU	or (1) 1/0 - 600 kcmil	3 Phase	4MLKC3	4MLKC3A
400	AL	(1) AL 1/0-750 kcmil (2) AL/CU 250kcmil max.	1 Phase	-	4MLKA1B
400	AL	[max.(1) 600 kcmil CU wire]	3 Phase	-	4MLKA3B

## Table P1-10 - Copper Neutral Lug Kits - 250A

No. of Circuits	Description	Original P1 Catalogue Number	Nex Gen P1 Catalogue Number
18		CNLK18	Use 30 ckt kit
30	2 or 4 Branch Neutral Strips,	CNLK30	CNLK30A
42	1 Main Neutral Lug, Hardware	CNLK42	CNLK42A
54, 66		_	CNLK54A

## Table P1-10A - 2/0 Neutral Lug Kits - 250A and 400A

No. of Circuits	Description	Original P1 Catalogue Number	Nex Gen P1 Catalogue Number
18	2 or 4 Branch Neutral Strips, Hardware	_	Use 30 ckt kit
30		_	LNLK30A
42		_	LNLK42A
54, 66		_	LNLK54A

## Table P1-11 - 200% Neutral Lug Kits - 250A

No. of Circuits	Description	Original P1 Catalogue Number	Nex Gen P1 Catalogue Number
18		2NLK18	Use 30 ckt kit
30	2 or 4 Branch Neutral Strips, 2 Main Neutral Lugs, Hardware	2NLK30	2NLK30A
42		2NLK42	2NLK42A
54, 66		_	2NLK54A

## Table P1-12 - 200% Neutral Lug Kits - 400A

No. of Circuits	Description	Original P1 Catalogue Number	Nex Gen P1 Catalogue Number
18	2 or 4 Branch Neutral Strips, 1 Main 600 kcmil Neutral Lug,	42NLK18	N/A
30		42NLK30	42NLK30A
42		42NLK42	42NLK42A
54, 66		_	42NLK54A

① Original P1 kits will not work with Next Gen P1 interiors if the chart shows different part numbers for each.

<sup>®</sup> Next Gen P1 kits will not work with Original P1 interiors if the chart shows different part numbers for each.

## **Type P1 Panelboards**

## Table P1-13 - Main Breaker Gutter Dimensions Inches (mm)

Main	Max. Interrupting F	Neutral Location	
Breaker	20" wide box	24" wide box	20" wide box
BL, BLH, HBL, BQD, BQD6 <sup>2</sup>	8.500 (216)3	10.500 (267)3	10.500 (267)
NGB	8.000 (203)3	10.000 (254) <sup>3</sup>	10.500 (267)
ED2, ED4, ED6, HED4	6.125 (156)	8.125 (206)	10.500 (267)
QJ2, QJH2, QJ2H	6.500 (165)	8.500 (216)	10.500 (267)
QR2, QRH2, HQR2, HQR2H	6.500 (165)	8.500 (216)	10.500 (267)
FD6, FXD6, HFD6, HFXD6	5.250 (133)	7.250 (184)	10.500 (267)
JD6, JXD6 <sup>®</sup>	15.000 (381)	15.000 (381)	26.500 (674)

① JD frame mounted vertically.

## Table P1-14 - Main Lug End Gutter Dimensions Inches (mm)

Amp	End Gutter		Neutral Location	
Rating	20" wide box	24" wide box	20" wide box	24" wide box
125	9.500 (242)	9.500 (242)	10.500 (267)	10.500 (267)
250	9.500 (242)	9.500 (242)	10.500 (267)	10.500 (267)
400	25.500 (648)	25.500 (648)	26.750 (680)	26.750 (680)

**NOTE:** Feed-thru lug and neutral wire bending space is 15.000" and 16.250" respectively on 400A panel.

Table P1-15 – Side Gutter Wiring Space Inches (mm) (Fig P1-1)

opace menes (mm, (rig r r r)				
Reference Letter	Panel Width 20"	Panel Width 24" Optional		
A <sup>②</sup>	6.375 (167)	8.375 (213)		
B <sup>②</sup>	5.500 (140)	7.500 (191)		
C2	5.000 (127)	7.000 (178)		
D	6.125 (156)	8.125 (206)		
E	6.500 (165)	8.500 (216)		
F	5.250 (133)	7.250 (184)		

Fig P1-1

_			_	
<b>←</b> A→	BL, BLH, HBL	BL, BLH, HBL	<b>←</b> A→	
~~~	BLF, BLHF	BLF, BLHF	~~~	
<b>←</b> B →	BQD, BQD6	BQD, BQD6	<b>←</b> B →	
<b>←</b> C→	NGB	NGB	<b>←</b> C→	
<b>←</b> D →	ED2, ED4, E	ED2, ED4, ED6, HED4		
<b>←</b> E →		QJ2, QJH2, QJ2H QR2, QRH2, HQR2, HQR2H		
<b>←</b> F →	FXD6, FD6			

Panel Width 20 in. (508 mm)



Feed-Thru (FT)



Non-Feed-Thru (NFT)

## **Miscellaneous Parts and Accessories**

Catalogue No.	Description	
BK1	Bonding Kit for 400A max. Original P1 Panels	
BK1A	Bonding Kit for 400A max. Next Gen P1 Panels	
BK2	Bonding kit for S1/S2 400 & 600	
BK3	Bonding kit	
IMK1	Interior Adjusting Kit	
11-1824-01	Directory Card Holder	
LPDC01	Directory Card (Pack of 10; ref. 12-1110-01)	
MCHK	Metal Card Holder Kit	
NBK03	Number Strips 1–42. Stick-on type; Use w/ P1 series Panels	
NBK04	Number Strips 43–84. Stick-on type; Use w/ P1 series Panels	
NBK05	Number Strips 85–126. Stick-on type; Use w/ P1 series Panels	
NBK06	Number Strips 127–168. Stick-on type; Use w/ P1 series Panels	
EGK	AL Ground Bus 44 Connections	
ECGK	CU Ground Bus 44 Connections	
IGK	Insulated AL Ground Bus	
ICGK	Insulated CU Ground Bus	
EWK1	End Wall Kit with Knockouts (20" W x 5.75" DP)	
P1SCRWS	Package of 42 breaker mounting screws for P1	
DFFP1	1" Branch circuit filler plate (suitable for replacing QF3 in P1 thru P5 Panelboards and Switchboards)	
P1CONBPHCU <sup>①</sup>	Connector kit – 6 pcs. B-phase Copper	
P1CONBPHAL®	Connector kit – 6 pcs. B-phase Aluminum	
P1CONACPHCU <sup>①</sup>	Connector kit – 6 pcs. A or C-phase Copper	
P1CONACPHAL®	Connector kit – 6 pcs. A or C-phase Aluminum	
MBKQRFK P1/Next Gen P1 Filler for 1PH/3PH QR. Horizontal mount only.		
TPS9IKITP1	Original P1 mounting bracket for SPD TPS3 09	
TPS9IKITP1A	Next Gen P1 mounting bracket for SPD TPS3 09	

① Replacement parts only.

## Table P1-18 - Standard Enclosures

Box	Catalogue Number				
Height	Type 1 Standard Trim			Type	Туре
(in.)	Box <sup>⑤</sup>	Surface <sup>®</sup>	Flush <sup>®</sup>	3R <sup>⑦</sup>	3R/12®
26	B26	S26B	F26B	NR26	WP26
32	B32	S32B	F32B	NR32	WP32
38	B38	S38B	F38B	NR38	WP38
44	B44	S44B	F44B	NR44	WP44
50	B50	S50B	F50B	NR50	WP50
56	B56	S56B	F56B	NR56	WP56
62	B62	S62B	F62B	NR62	WP62
68	B68	S68B	F68B	NR68	WP68
74	B74	S74B	F74B	NR74	WP74

- © 16 GA std., Optional 14 GA & 12 GA Enclosures only.
- 14 Gauge Steel only. 16 Gauge Can w/ 14 Gauge Front.



Example of Back-fed NGB Main breaker installed

<sup>&</sup>lt;sup>2</sup> For Next Gen P1, use Side Gutter Wiring Specs Table P1-15. These are back-fed main breakers.

<sup>&</sup>lt;sup>®</sup> These dimensions are for Original P1 as a reference only, not for Nex Gen P1.

Subfeed mounting limit per panel.
 For all Nex Gen P1 panels using BL/BQD or xGB breakers as mains in back-fed position, use this chart for wiring space.

## **Type P1 Panelboard Modifications and Additions**

Selection

## Panel Options

#### **Enclosures**

- Extra gutter to sides or ends of the can
- 24" wide boxes
- Hinged trims
- Door-in-door trims
- Screw to the box trims
- Piano hinge trims
- Painted boxes
- Custom colors
- Stainless steel trims and boxes
- Type 1 enclosures (Std 16 Gage)
- Type 3R/12 enclosures 16 Gauge Can w/ 14 Gauge front)
- Type 4 enclosures (14 Gauge only)
- Type 4X enclosures (14 Gauge only 304SS Std, 316SS Optional)
- Panel skirts
- Gaskets between trim and box

## **Surge Protection Devices**

- TPS3 02
  - Bus connected
- Internally mounted (30A breaker required to feed SPD)
- Externally mounted in a 15" high aux. enclosure (30A breaker required to feed SPD)
- TPS3 09
  - Internally mounted (20A breaker required to feed SPD)
  - Externally mounted (20A breaker required to feed SPD)
- TPS3 12
  - Externally mounted (40A breaker required to feed SPD)

## Panel Modifications

#### **Enclosures**

Main Bus

Standard main bus is tin-plated aluminum. For copper main bus, add from the table for each panel. Includes copper neutral cross bar. For copper neutral branch lugs, see miscellaneous.

- Compression lug for MLO<sup>②</sup>
- Contactor mains Mount in 23" enclosure ahead of panel.
- Asco 920 through 225 amps<sup>®</sup>
- Asco 911 through 150 amps<sup>®</sup>
- Siemens LEN through 30 amps<sup>®</sup>
- Branch and main breaker accessories
  - Handle blocks
  - Handle locks
- Feed-thru lugs<sup>①</sup>

Cannot be used in conjunction with SPD/TVSS or subfeed breakers. Do not add height to the panel.

Feed-thru Lugs Amp Rating	Туре	Connector CU/AL Range
	AL/CU Mechanical	(1)–#6 AWG- 350 kcmil
250	CU Mechanical	(1)–#6 AWG- 350 kcmil
	AL/CU Compression	(1)–#6 AWG- 350 kcmil
	AL/CU	(2)–#1/0 - 250 kcmil or
400	AWG Mechanical	(1)–#2 AWG- 600 kcmil
400	CU	(1)–1/0-600 kcmil (2)-1/0-4/0
	AL/CU Compression	(1) 400-600 kcmil AL (1) 400-500 kcmil CU

■ 200% neutral<sup>①</sup>

 $_{\bullet}$  Copper lugs, mechanical line and branch neutral  $^{\! \mathbb{O}}$ 

■ Bus mounted SPD/TVSS®

 Grounding of Panelboards
 Ground Bars except for brazed to box are shipped with the panel interior factory mounted.

- Non-Insulated Equipment Ground Bar Standard
- Copper Non-Insulated Ground Bar
- AL Insulated Equipment Ground Bar
- CU Insulated Equipment Ground Bar
- Shunt Trip on Main or Branch
   BL®, BLH®, HBL®, BQD®, NGB® as branch use
   1" unit space for shunt trip.

QJ2, QJ2H, QJH2, QR2, QRH2, HQR2, HQR2H, ED2, ED4, ED6, HED4, FD6, FXD6, HFD6

HFXD6, JXD6, JD6, HJD6, HJXD6

10

NELBOARDS

NOTE: Specify copper or aluminum cable.

- ① Do not increase panel or enclosure size.
- ② Accessories on 1" pole breakers (BL, BQD, xGB, ED) will take 1" unit space.
- 3 External to the panel, supplied in a separate enclosure

## Type P1 Panelboard Modifications and Additions

Reference

## Compression Lugs

## Table P1-19 - Lugs

Style	Amp Rating	Breaker Type	Compression Connectors	Box Height Addition
	125	N/A	(1) #6 AWG - 350 kcmil	None
MLO	250	IN/A	(1) #6 AVVG - 350 KCIIIII	None
IVIEO	400	N/A	(1) 400 - 600 kcmil AL (1) 400 - 500 kcmil CU	None
	125	ED4, ED6, HED4	(1) #14 AWG - 2/0	Box must go to 24" wide
Main Breaker	225	QJ2, QJH2, QJ2H, QR2, QRH2, HQR2, HQR2H	(1) #6 AWG - 350 kcmil CU or AL	Box must go to 24" wide for All breakers
	250	FXD6, HFD6	(1) #6 AWG - 350 kcmil CU or AL	Box must go to 24" wide for All breakers

NOTE: Standard compression lugs used for P1 panels are range taking lugs and require a particular crimping tool (tool is Hubbell/Anderson Versa Crimp VC6 -for 250A) to accommodate the range. Consult factory for information. 200% neutral not available with compression lugs. xGB breakers cannot accommodate compression lugs. (For 400A tool use Hubbell/Anderson Versa Crimp VC6FT/VC7FT - see instruction sheet for details.)

## **Enclosure Modifications**

## Type-4-Water Tight, Dust Tight, **Steel Enclosure**

(Actual Type-4 enclosure is larger than standard Type 1 enclosure. See chart below for reference to approximate actual size.)

#### Table P1-20

Standard Box Height	Actual NEMA 4 Enclosure Size		
(in inches)	Н	W	D
32	32	20	8
38	42	30	8
44	48	36	8
56	60	36	10

NOTE: Larger Type 4 enclosures are not

## Remote Switch Modifications

## **Table P1-22 - Control Power** Transformer

Size	VA Relay
0, 1	50
2	75
3	150
4	250

## Table P1-24 - Remote Control **Switch Modification**

Description
Auxiliary Contacts (mounted, not wired)
2-Wire Control

## Type-4X For Type P1

Water Tight, Dust Tight and Corrosion Resistant (consult plant to verify actual enclosure size)

#### Table P1-21

Catalogue	Enclosure – Stainless Steel Size (inches) (304SS is standard)					
Number	Н	W	D			
B4X26	26	20	5.75			
B4X32	32	20	5.75			
B4X38	38	20	5.75			
B4X44	44	20	5.75			
B4X50	50	20	5.75			
B4X56	56	20	5.75			
B4X62	62	20	5.75			
B4X68	68	20	5.75			
B4X74	74	20	5.75			

Enclosure Fiberglass Size (inches)				
Н	W	D		
36	30	8		
36	30	8		
48	36	12		
48	36	12		
60	36	12		
60	36	12		
	·	1		

NOTE: 316SS is available as an option – must be specified.

## Table P1-23 - Applications for a Remote Switch

Switch Type	Modification				
920	Mounts in 23" relay cabinet as a main only				
LEN	30A mounts in 23" relay cabinet as a main only				

#### Gauge Steel of Boxes/Fronts, Surface and Flush

Dimensions in Inches (mm)		Gauge Steel				
Н	W	Box Front/Door		Туре		
26-74 (660-1880)	20 (508)	16 <sup>①</sup>	14 <sup>③</sup>	Type 1		
26-74 (660-1880)	20 (508)	16 <sup>②</sup>	16/14 <sup>②</sup>	Type 3R/12		
32-60 (813-1524)	20-36 (508-914)	14 <sup>③</sup>	14 <sup>③</sup>	Type 4		
26-74 (660-1879)	20 (508)	14 <sup>④</sup>	14 <sup>@</sup>	Type 4X		
36-60 (914-1524)	30-36 (762-914)	N/A <sup>⑤</sup>	N/A <sup>⑤</sup>	Type 4X Non-Metallic		

① 16 Gauge is Standard (14 Gauge & 12 Gauge are optional)

<sup>2 15</sup> Gauge Steel Can with 14 Gauge Door or Similar Approved Construction


No Optional Gauge available304SS 14 Gauge Std., 316SS 14 Gauge optional

<sup>9</sup> Sizes do not match Standard Enclosure Sizes - See Table P1-21 - material is non-metallic - No Gauge Specified.

## **Type P1 Enclosure Details**


## Type 1 Box

Box is symmetrical



# Type 3R and 3R/12 Box

## Flush Mounting



① Dimensions are interior of the box. Add 5/8" to width for absolute dimension. Add 1/8" to height for absolute dimension.

Dimensions shown in inches and millimeters [].

**Type P2 Panelboards** *General* 

## Features

Flexibility is the hallmark of the P2 panel. This panel offers a wide array of factoryassembled options to meet almost all lighting panel applications. With this design, the ability to mix breaker frames in unit space up to 250 amps will also meet many distribution panel requirements in a much smaller package. Bussing options for the P2 vary from aluminum to copper. Standard bussing in the P2 panel is tin-plated. Silver-plated copper is also offered as an option. Subfeed lugs (up to 400 amp) are just a few of the options of this unique panel.

Like a lighting panel, P2 is set up around 18, 30, 42, 54, 66, 78, and 90 circuit configurations. It will also allow the user to configure the panel to the smallest possible size. The P2 panel starts with 9" of unit space (18 circuits of 1" pole breakers). Breakers mounted in unit space can be mixed and matched to meet customer requirements. All 1" pole breakers (BL, BQD, ED frames) are mounted in 3" or 6" pole increments. Breaker frames, above 125 amps, are mounted in 6" single breaker mountings. As an example of a minimum panel, (6) 20 amp 1-pole BL breakers (3" of unit space) and a 3-pole 225 amp QJ breaker (6" of unit space) equaling 9" of unit space can be configured in a P2 panel

without any extra provisions or space required. FD 250 amp and JD 400 amp breakers are mounted as subfeed breakers outside of unit space.

Another unique feature of the P2 panel is that blank unit space can be added to allow for future expansions or modifications. Any expansions or modifications must be in 3" increments. BL, BQD, and ED frame breakers have 3" or 6" pole kits, and can be mixed in unit space by these increments. Breakers of the same frame can cross from one mounting to another if contiguous. QR frame breakers are mounted in 6" increments for two- and three pole, single mounted units. Changes in the unit space length for BL, BQD, or ED frame breakers require an addition deadfront, center strip kit. Check with sales or the factory for additional unit space kits.

## Main Lug / Main Breaker

**Enclosure** – Standard Type 1 enclosure is 20" wide x 5.75" deep. Box Height is determined by main device and unit space. See charts for box height.

Voltage - 600V AC max. 250V DC max.

Amperage – 600 amp max.

Short circuit rating - 200 KAIC max. symmetrical or equal to the lowest rated device installed unless a series rating is indicated. Panels with subfeed or feed-thru lugs without a main device, circuit breaker or fusible unit, are limited to a three-cycle rating. The three-cycle rating for the P2 panel is limited to 22 KAIC. Note that the main device may be mounted remote from the panel.

**Bussing** – The P2 panel has more options to meet market requirements. The standard bussing is temperature rated aluminum. The rating is per the requirements of CSA C22.2 No.29 - the standard for panelboards. All aluminum bussing is tin-plated. Optional bussing for the P2 panel is copper. The copper bus option for this panel is tin-plated as standard or silver.

## Weight – Approximate


Total panelboard weight when filled with a normal quantity of breakers and accessories is about 3 lbs. (1 kg) per inch (54g per mm) of box height.

## Gauge Steel of Boxes/Fronts, Surface and Flush

Dimensions in Inches (mm)		Gauge Steel	Gauge Steel			
Width	Height	Box	Front/Door	Туре		
20 (508)	26-74 (660-1880)	14	14	Type 1		
20 (508)	26-74 (660-1880)	16 <sup>②</sup>	16/14 <sup>②</sup>	Type 3R/12		
20-36 (508-914)	32-60 (813-1524)	14	14	Type 4		
20 (508)	26-74 (660-1879)	14 <sup>3</sup>	14 <sup>3</sup>	Type 4X		

## Interior Numbering System

Type P2 unassembled panelboards are available as main lug only and come with provisions for the branch breaker type selected.



## **Branch Breakers**

Panel Type	Voltage (Max.)	Breaker Type	Power Product Catalogue Page
P2	240	BL, BLH, HBL, BQD	See section 5
12	600/347	BQD6, ED6	See Section 5

## **Distributor Stock - Type P2 Main Lug Only**

Selection

Interior, Box and Trim Selection 600A Max. — 20" Wide x 5.75" Deep

- Determine voltage, system, amperage and type of branch breaker connectors to select the appropriate Interior from the table below.
- 2. Select the type of box and trim needed.
- 3. List required branch circuit breakers: Type BL, BQD or ED breakers.

## Type P2 Unassembled Panelboards

Interiors On	ly - Less Branc	h Breakers		Boxes	Boxes			Trim		
Amperes Rating Mains	Max. No. of Circuits	Provision Type	Main Lug + provisions	Height - Inches (mm)	Type 1	Type 3R/12 <sup>①</sup>	Surface	Flush <sup>®</sup>		
1-Phase, 3-Wire							120/240V			
250	66 78	BL/BQD	I2A66ML250A-BL I2A78ML250A-BL	56 (1422) 62 (1575)	B56 B62	WP56 WP62	S56B S62B	F56B F62B		
400	42 66	BL/BQD	I2A42ML400A-BL I2A66ML400A-BL	50 (1270) 62 (1575)	B50 B62	WP50 WP62	S50B S62B	F50B F62B		
3-Phase,	1-Wire							208Y/120V		
250	42 66 78	BL/BQD	I2C42ML250A-BL I2C66ML250A-BL I2C78ML250A-BL	44 (1118) 56 (1422) 62 (1575)	B44 B56 B62	WP44 WP56 WP62	S44B S56B S62B	F44B F56B F62B		
400	42 66 78 90	BL/BQD	I2C42ML400A-BL I2C66ML400A-BL I2C78ML400A-BL I2C90ML400A-BL	50 (1270) 62 (1575) 68 (1727) 74 (1880)	B50 B62 B68 B74	WP50 WP62 WP68 WP74	S50B S62B S68B S74B	F50B F62B F68B F74B		
600	66	BL/BQD	I2C66ML600A-BL	62 (1575)	B62	WP62	S62B	F62B		
3-Phase,	1-Wire							600Y/347V		
	30	ED	I2L30ML250A-ED	38 (965)	B38	WP38	S38B	F38B		
	42	ED	I2L42ML250A-ED	44 (1118)	B44	WP44	S44B	F44B		
250	66	BQD6 ED	I2L66ML250A-BQD I2L66ML250A-ED	56 (1422) 56 (1422)	B56 B56	WP56 WP56	S56B S56B	F56B F56B		
	78	BQD6 ED	I2L78ML250A-BQD I2L78ML250A-ED	62 (1575) 62 (1575)	B62 B62	WP62 WP62	S62B S62B	F62B F62B		
	42	BQD6 ED	I2L42ML400A-BQD I2L42ML400A-ED	50 (1270) 50 (1270)	B50 B50	WP50 WP50	S50B S50B	F50B F50B		
	66	BQD6 ED	I2L66ML400A-BQD I2L66ML400A-ED	62 (1575) 62 (1575)	B62 B62	WP62 WP62	S62B S62B	F62B F62B		
400	78	BQD6 ED	I2L78ML400A-BQD I2L78ML400A-ED	68 (1727) 68 (1727)	B68 B68	WP68 WP68	S68B S68B	F68B F68B		
	90	BQD6 ED	I2L90ML400A-BQD I2L90ML400A-ED	74 (1880) 74 (1880)	B74 B74	WP74 WP74	S74B S74B	F74B F74B		
600	66	BQD6 ED	I2L66ML600A-BQD I2L66ML600A-ED	62 (1575) 62 (1575)	B62 B62	WP62 WP62	S62B S62B	F62B F62B		

① Hinged door included with type 3R/12 enclosures.

<sup>©</sup> Flush trims extend 3/4" beyond each side of the base box dimensions.

## Standard Circuit P2 Panels


Base Box Size Requirements for P2 Panels with Standard Line Lugs. Unit Spaces range from 9" to 45" (in 6" increments). Boxes range from 26" to 74" high (in 6" increments). Inclusion of optional modifications may require size increases that must be added to these base values to calculate the final box size for the panel (see pages 6-28, 10-31). Values in brackets [], at the bottom of each column, indicate the maximum allowable 1" module branch poles for each main type.

	P2 Panels with Standard Line Lugs. Unit Space (starting with 9" and adding 6" increments) "A" Dimension														
"B"	Main Lug	gs		Main Breaker	n Breakers										
Dimen- sion Box Height	125A	250A	400A 600A	125A Horiz. BL, BQD, ED	125A Vert. ED <sup>①</sup>	125A Horiz. CED	225A Horiz. QJ/QR	225A Vert. QJ/QR <sup>①</sup>	250A Horiz. FD	250A Vert. FD <sup>①</sup>	250A CFD	400A JD	400A CJD	600A LD	600A CLD
26	9	_	_	9	_	_	l –	_	_	_	_	_	<u> </u>	1-	T-
32	15	9	_	15	9	9	9	_	_	_	_	_	<u> </u>	1-	1-
38	21	15	9	21	15	15	15	9	9	_	_	_	<u> </u>	1-	1-
44	27	21	15	27	21	21	21	15	15	9	_	_	<u> </u>	<u> </u>	1-
50	27	27	21	33	27	27	27	21	21	15	9	9	<u> </u>	<u> </u>	1-
56	39	27	27	39	33	33	33	27	27	21	15	15	l –	9	T -
62	45	39	33	45	39	39	39	33	33	27	21	21	9	15	9
68	51	45	39	51	45	45	45	39	39	33	27	27	15	21	15
74	57	51	45	57	54	54	54	45	45	39	33	33	21	27	21
	[114p]	[102p]	[q0e]	[114p]	[102p]	[102p]	[102p]	[q0e]	[q0e]	[78p]	[66p]	[66p]	[42p]	[54p]	[42p]

# Main breaker wire bending space diagram

# Vertical Main Breaker Horizontal Main Breaker Neutral Neutral See Table C See Table C See Table A B Box depth = 5.75 in. (146 mm) Box width - 20 in. (508 mm) for 100-600A

# Main lug wire bending space diagram



# Type P2 Panelboards

## Standard Circuit P2 Panels

## Main Breaker Wire Bending

Standard Circuits (up to 54 1" module branch poles)						
Panel Amps	Breaker Frames	C <sub>①</sub>	<b>D</b> ①			
100	BL	5.75	8.00			
100	BQD	5.13	8.00			
125	ED (horiz.)	4.00	8.00			
125	ED (vert.)	6.56	11.13			
225	QJ/QR (horiz.)	5.00	7.00			
225	QJ/QR (vert.)	10.06	16.69			
250	FD (horiz.)	5.00	7.00			
250	FD (vert.)	13.25	22.72			
400	JD	15.38	25.00			
600	LD	15.38	23.00			

## **Branch Breaker Side Gutters Inches (mm)**

Reference Letter	Panel Width 20" (508)
Α	5.750 (146)
В	5.125 (130)
С	4.000 (102)
D2	5.000 (127)
E	4.625 (117)

## **Main Lug Connectors**

Standard Circuits (up to 54 1" module branch poles)							
Panel Amps	Standard Connectors	tandard Connectors C <sup>①</sup> D <sup>①</sup>					
125	(1) #14-2/0	6.62	8.19				
250	(1) #6 AWG - 350 MCM	11.75	10.72				
400	(1) #4 AWG - 600 MCM or (2) #6 - 250 MCM	14.00	13.09				
600	(2) #4 AWG - 500 MCM	14.00	11.00				

<b>←</b> A →	BL, BLH, HBL	BL, BLH, HBL,	<b>←</b> A →
	HBLF2, BLFB, BLHFB	HBLF2, BLFB, BLHFB	
<b>←</b> B →	BQD, BQD6	BQD, BQD6	<b>←</b> B →
<b>←</b> C →	ED, ED4, ED6, HED4	ED, ED4, ED6, HED4	_ ← C →
<b>←</b> D →	QJ2,QJH: QR2, QRH2, H(	<b>←</b> D →	
	(Single M		
			<del>-</del>



① Refer to diagrams at the bottom of page 10-26.② Single branch mounting construction.

## **Type P2 Panelboards**

## Main Breaker Selection<sup>①</sup>

Ampere	Breaker	Max. Inte	errupting F	Rating (kA)	Ref.	
Rating	Туре	240V	480V	600V	Catalogue No.	Available Trip Values
70	BQD6	65	_	10	B6	15, 20, 25, 30, 35, 40, 45, 50, 60, 70
100	BL HBL BQD BLH	10 65 65 22	- - 14 -	_ _ _ _	BL HB BQ BH	15, 20, 25, 30, 35, 40, 50, 60, 70, 80, 90, 100 15, 20, 25, 30, 35, 40, 50, 60, 70, 80, 90, 100 15, 20, 25, 30, 35, 40, 50, 60, 70, 80, 90, 100 15, 20, 25, 30, 35, 40, 50, 60, 70, 80, 90, 100
125	ED4 ED6 HED4	65 100 100	18 25 42	_ 14 _	E4 E6 H4	15, 20, 25, 30, 35, 40, 50, 60, 70, 80, 90, 100, 110, 125 15, 20, 25, 30, 35, 40, 50, 60, 70, 80, 90, 100, 110, 125 15, 20, 25, 30, 35, 40, 50, 60, 70, 80, 90, 100, 110, 125
	QJ2 QJH2 QJ2H	10 22 42	_ _ _	_ _ _	QJ QH Q2	60, 70, 80, 90, 100, 110, 125, 150, 175, 200, 225 60, 70, 80, 90, 100, 110, 125, 150, 175, 200, 225 60, 70, 80, 90, 100, 110, 125, 150, 175, 200, 225
225	QR2 QRH2 HQR2 HQR2H	10 25 65 100	- - -	_ _ _ _	QR Q4 Q5 Q6	100, 110, 125, 150, 175, 200, 225 100, 110, 125, 150, 175, 200, 225 100, 110, 125, 150, 175, 200, 225 100, 110, 125, 150, 175, 200, 225
	FD6 FXD6 HFD6 HFXD6 CFD6 <sup>2</sup>	65 65 100 100 200	35 35 65 65 200	18 18 25 25 100		70, 80, 90, 100, 110, 125, 150, 175, 200, 225 70, 80, 90, 100, 110, 125, 150, 175, 200, 225 70, 80, 90, 100, 110, 125, 150, 175, 200, 225 70, 80, 90, 100, 110, 125, 150, 175, 200, 225 70, 80, 90, 100, 110, 125, 150, 175, 200, 225 70, 80, 90, 100, 110, 125, 150, 175, 200, 225
250	FD6 FXD6 HFD6 HFXD6	65 65 100 65	35 35 65 35	18 18 35 25	HF	70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250 70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250 70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250 70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250
400	JXD6 <sup>2</sup> JD6 <sup>2</sup> HJXD6 <sup>2</sup> SJD6 <sup>2</sup> SHJD6 <sup>2</sup> CJD6 <sup>2</sup> SCJD6 <sup>2</sup>	65 100 100 65 100 200 200	35 35 65 65 35 65 200 200	25 35 35 35 25 35 100 100	JX J6 H6 H5 SJ S2 CJ SC	200, 225, 250, 300, 350, 400 200, 300, 400 200, 300, 400 200, 300, 400 200, 300, 400 200, 300, 400
600	LXD6 <sup>2</sup> LD6 <sup>2</sup> HLXD6 <sup>2</sup> HLD6 <sup>2</sup> SLD6 <sup>2</sup> SHLD6 <sup>2</sup> CLD6 <sup>2</sup> SCLD6	65 100 100 65 100 200 200	35 35 65 65 35 65 150	25 25 35 35 25 35 100 100	HL	450, 500, 600 250, 300, 350, 400, 450, 500, 600 250, 300, 350, 400, 450, 500, 600 250, 300, 350, 400, 450, 500, 600 300, 400, 500, 600 300, 400, 500, 600 300, 400, 500, 600 300, 400, 500, 600

## Vertically Mounted Main Breaker (available in 2-pole or 3-pole)

_			
	Ampere Rating	Breaker Type(s)	Unit Space (in.)
	100	ED4, ED6, HED4	6
		QJ2, QJH2, QJ2H, FXD6, FD6, HFD6 QR2, QRH2, HQR2, HQR2H	6

## Subfeed Breakers (available in 2-pole or 3-pole)

Breaker	Mounting Position When Used as Subfeed Breaker	Ampere Ratings	Maximum I (kA) Symm	nterrupting   etrical	Rating
Туре	Vertical	For Load	240V AC	480V AC	600V AC
FD6®, FXD6	Twin	70-250	65	35	22
HFD6®,HFXD6	Twin	70-250	100	65	25
JD6⊚, JXD6	Single	200-400	65	35	25
HJD6®, HJXD6	Single	200-400	100	65	35

① Interchangeable trip main breakers are mounted at top of panel only.

② Vertically mounted.

③Twin mounted subfeed breakers are mounted at the bottom of panelboard only and adds 24" to the panel height.

<sup>@</sup>Subfeed breaker is mounted at bottom of panelboard only. 400 amp subfeed breaker adds 24" to the panel height. (Only for use with MLO)

## Type P2 Panelboard Standard Modifications and Additions

## Selection

#### **Branch Circuit Breakers**

Max. Amp	Bolt-On Breaker		Availabil	ity		Maximum Interrupting Rating (kA)						
Rating	Туре	Amps	1-Pole	2-Pole	3-Pole	120V AC	120/240V AC	240V AC	277V AC	480V AC	600V AC	250V DC
70	BQD6	15-70	/	/	/	65	65	65	_	_	10	_
		15–60	√	/	/	10	_	_	_	_	_	_
	BL	70	√	√,	√,	_	10	_	_	_	_	-
		80–100 15–60	_	√   /	/	_		10	_	_	_	_
	BLH	70	\frac{1}{2}	//	/	_	22	_	_	_	_	_
		80–100	<u> </u>	V	V	_	_	22	_	_	_	_
		15–55	√	√,	√,	_	65	_	_	_	_	-
	HBL BLR (240V)	60–100 15–60	_	<b> </b> √	<b>√</b>	_	65	_ 10	_	_	_	_
	DEIT (240V)	70–100	_	\\ /			_	10	_	_	_	_
	DIE (CECI)	15–30	/	/	1-	10	_	_	_	_	_	_
100	BLE (GFCI)	40–60	<u> </u>	V	_	_	10	_	_	_	_	_
	BLEH	20–30	√,	<del>-</del>	-	22	_	_	_	_	_	_
		15–60 15–30	/	/	+-	10	22		_	_	_	<del>-</del>
	BLF (GFCI)	40–60	\frac{1}{3}	/	_	10	10	_	_	_	_	
	DI LIE (CECI)	15–30	/	/	<b> </b> -	22	_	_	_	_	_	_
	BLHF (GFCI)	40–60	,	V	_	_	22	_	_	_	_	_
	HBLF2 (GFCI)	15–30	√	-	-	65	_	_	_	_	_	_
	BAF BAFH	15–20 15–20	<b>\</b>	<b>\</b>	_	10 22	_	_	_	_	_	_
		15–20	/	/			65	_	14	_	_	14
	BQD	70–100	√ √	V V	√ √	_	65	_		14	_	14
		15–60	√.	√.	√.	100	100	100	25	25	14	144
	NGB2	70–100 110–125	<u> </u>	<b> </b>	\ \ /	100 100	100 100	100 100	25 25	25 25	14 14	14 <sup>4</sup> 14 <sup>4</sup>
		15–60		/	/	100	100	100	35	35	22	144
	HGB2	70–100	V	V V	V	100	100	100	35	35	22	144
		110–125	_	√	√	100	100	100	35	35	22	144
	LGB2	15–60 70–100	<b>\</b>	<b>\</b>	\_/	100 100	100 100	100 100	65 65	65 65	25 25	14 <sup>4</sup> 14 <sup>3</sup>
	LOBZ	110–125	_	\\ \/	\frac{1}{\sqrt{1}}	100	100	100	65	65	25	143
125		15–60	√	/	/	65	_	_	22	_	_	_
123	ED4	70–100	√	<b>√</b> ,	<b>√</b> ,	_	_	65 65	_	18	_	30
		110–125 15–60	<del>-</del>   -	/	/	_	_	65		18 25		30
	ED6	70–100	_	\\ \/	\frac{1}{\sqrt{1}}	_	_	65	_	25	18	-
		110–125	_	V	, /	_	_	65	_	25	18	_
	HED4 <sup>①</sup>	15–60	√,	√,	<b>√</b> ,	_	_	65 65	_	42	18 18	30
	HED4⊍	70–100 110–125	<u> </u>	//	\\ /		_	65	_	42 42	18	_
	CED6 <sup>4</sup>	15	_	T _	- /	_	_	200	_	_	100	_
		20-125	_	√	·/	_	_	200	_	_	100	_
	QJ2	60–225	-	$\sqrt{}$	<b>√</b> ,	_	_	10	_	_	_	_
	QJH2 QJ2H	60-225 60-225	_	1/	\\ \/	_	_	22 42	_	_	_	_
225	QR2	100–225	_	1./	./	_	_	10	_	_	_	_
	QRH2	100–225	-	V.	V	_	_	25	_	_	_	_
	HQR2 HQR2H	100-225	_	\ \ /	\\ /	_	_	65 100	_	_	_	_
	Inunzn	100–225			. √		_	100				<u> </u>

## **Branch Neutral Connections**

Wire Range	Max. Number of Connections	Max. Amp <sup>②</sup>
#14-#6	26	65
#14-1/0	28	125
#6-350 kcmil	3	250
(1) #4-600 kcmil or (2) #6-250 kcmil	1	400

① 1-Pole HED 4 15–30A Rated 65kA 35 through 100A Rated 25kA.

Based on 75 degree copper.
 2-pole only (or) two outer poles of 3-pole breaker.
 CED6 breaker can be used in 400A panel with copper bussing only. Panel enclosure required is 24" (610mm) wide.

## **Enclosure Modifications**

Description
Type 1 with gasket
Type 1 with dripshield
Type 3R - Waterproof and silicone free
Type 3R/12 - Dustproof
Type 4/4X - Standard type 304 Stainless Steel
Type 4/4X - Type 316 Stainless Steel
Wider enclosure - 24", 30" or 36" wide
Hinged trim

Hinged trim
Piano hinged trim
Trim with padlock
Door-in-door trim
Screw to the box trim
Trim with gasketed door
Stainless steel trim

Trim mounted devices

(Devices mounted into a 10" minimum box extension)

- Pilot lights
- Toggle switches
- Push buttons

Painted boxes Custom colors Increase gauge trims and boxes Stainless steel trims and boxes, Type 1

#### Meters

(Contact sales for pricing and application engineering for space requirements)

## **Panel Skirts**

See page 10-64

## Panel Bus Modifications

#### **Bus Material**

Represented by "A", "C" or "E" in the 11th digit of the catalogue number.

Standard bussing is tin plated Al, alternate bus bar material can be selected:

- Tin plated copper
- Silver plated copper optional

Subfeed and Feed-Thru (for 2-pole or 3-pole)

		Unit Space (inches)
--	--	---------------------------

## **Subfeed (Double) Lugs** for Main Lug Panelboards Only

100/125	(2)-#12 AWG - 2/0 AWG	6
225/250	(2)—#6 AWG-350 kcmil	6
400	(4)—250 kcmil (2)—600 kcmil	6

**Feed-Thru Lugs** — Cannot be used in conjonction with SPD or Subfeed Breakers (200% Neutral not available)

Amp Rating	Туре	Connector Wire Range
	Al Mechanical	(1) #6 AWG - 2/0 AWG Al/Cu
125	Cu Mechanical	(1) #6 AWG - 350 kcmil Cu
	Compression	(1) #6 AWG - 350 kcmil Al/Cu
	Al Mechanical	(1) #6 AWG - 350 kcmil Al/Cu
250	Cu Mechanical	(1) #6 AWG - 350 kcmil Cu
	Compression	(1) #6 AWG - 350 kcmil Al/Cu
	Al Mechanical	(1) #2 AWG - 600 kcmil Al/Cu and (1) 1/0 AWG - 250 kcmil Al/Cu
400	Cu Mechanical  Compression	(1) 1/0 AWG - 600 kcmil or (2) 1/0 AWG - 4/0 AWG
		(1) 250 kcmil - 600 kcmil Cu or (2) #6 AWG - 350 kcmil Al/Cu
	Al Mechanical	(2) #2 AWG - 600 kcmil Al/Cu
	Cu Mechanical	(2) #2 AWG - 600 kcmil Cu
600	Compression	(2) #6 AWG - 350 kcmil Al/Cu (2) 400 kcmil - 600 kcmil Al or (2) 400 kcmil - 500 kcmil Cu

# Increase Capacity Neutral up to 200% (N/A on FeedThru Lugs & Subfeed Lugs)

Main Bus Amps						
125						
250						
400						
600						

See page 10-31 for unit space adders and compatibility with other options.

(Devices mounted and wired to the trim should also have hinged trim specified)

## **Bus mounted SPD**

See Section 9

- TPS3 01
  - Bus connected
  - Internally mounted (30A breaker required to feed SPD)
  - Externally mounted in a 15" high aux. enclosure (30A breaker required to feed SPD)
- TPS3 0
  - Internally mounted (20A breaker required to feed SPD)
  - Externally mounted (20A breaker required to feed SPD)
- TPS3 12
- Externally mounted (40A breaker required to feed SPD)

#### **Service Entrance Label**

Type P2 Panelboards are factory labeled "SUITABLE FOR USE AS SERVICE ENTRANCE EQUIPMENT" when identified as "Service Entrance" at the time of order entry. For regulations governing this feature, please consult CEC, CSA or local electrical authorities.

## **Grounding of Panelboards**

Ground Bars except for brazed to box are shipped with the panel interior factory mounted.

- Non-Insulated Equipment Ground Bar
- Copper Non-Insulated Ground Bar
- Al Insulated Equipment Ground Bar
- Cu Insulated Equipment Ground Bar

## **Shunt Trip on Main or Branch**

BL, BLH, HBL, NGB, xGB2, ED6, HED4, uses 1" unit space for shunt trip. All others may be used on mains or subfeeds.

#### Contactor Mains or Submain\*

- Asco 920 through 225 amps adds 12" unit space as main, 15" unit space as submain
- External with manufacture supplied enclosure
- Siemens LEN through 30 amps adds 6" as main; 18" for up to 100A submain and 21" for 200A. 7.75" depth cans for up to 100A and 10" depth cans for 200A.

## **Branch and Main Breaker Accessories**

See breaker section of this catalog.

- Handle blocks
- Handle locks
- Aux. Contacts
- UVR®

## **Embedded Micro Metering Module™ (Type P2 Panelboard)**

Selection

## SEM3 System configured in Panelboards

The Siemens SEM3 system can be configured for factory installation in branch circuit monitoring applications. This option can lower the installation time of the system for the installer while providing a factory warrantied solution.

The SEM3 system can be factory installed in unit space in type P2 & S5 Siemens panel boards and in Siemens switch-boards. Please note P1 and P3 configurations are not available at this time and the amount of unit space needed varies depending upon the application. Please note that lead time adders will apply and may vary depending upon the configuration of the system.

## SEM3 for use in Siemens Panelboards



## Type P2: Enclosure

- Available in a Type 1 rated enclosure.
- Minimum width & depth: 30" width x 7.75" depth
- Height: Up to 74" depending on branch breaker selection
  - Addition of monitoring on some mains (primary and subfeed) may require additional box length. In these cases the box will be increased to the next size available as a standard design. The option of monitoring on mains is not available for equipment rated for service entrance.
  - In cases where enclosure size is increased all multi-section panels will be increased to match the largest section.



## Controller

SEM3 controller is mounted in a separate enclosure (relay cabinet) opposite of the feed location (i.e., bottom mount for top feed) with a height of 24". Each controller will be powered by direct tap connection to the panel section or through a 150VA potential transformer for systems above 480V. the direct tap connection will use 2 circuits from the distribution section (i.e., 42 circuits panel will have 40 circuits usable for distribution. Each controller can monitor up to 45 circuits. Applications that require monitoring more than 45 circuits will require additional P2 panel complete with SEM3.



#### **Current Transformers (CTs)**

Five sizes of CTs are available for use in the P2 panel: 50, 125, 250, 400 & 600 amp. All CTs are pre-mounted to a support bracket that attaches to the base rail of the interior of the panel board. Each bracket supports a maximum of 3 CTs and is designed for the breaker selected (brackets are not interchangeable between breaker frames). Each CT will be attached to a data module that is placed in the meter racks.



## **Meter Racks**

All meter racks will be installed next to the SEM3 controller in the relay cabinet. NOTE: Monitoring of 45 circuits will require: two 21 position racks and one 3 position rack

## **Embedded Micro Metering Module™ (Type P2 Panelboard)**


Selection

P2 Devices Enclosure sizes

## Example P2 Panel with SEM3 Type 1 Enclosure (36" Wide x 7.75" Deep)

Enclosure heights are in 6" increments from 26" thru 74". Enclosure heights: 26", 32", 38", 44", 50", 56", 62", 68", 74"

Example below is largest standard P2 enclosure for factory assembled panel with all small (1") branch breakers installed.



## **Type P2 Panelboard Standard Modifications and Additions**

Selection

## **Box Size Additions for Optional Features**

Main Lugs			Main Breakers													
Options	125A	250A	400A	600A	125A Horiz. BL, BQD,ED, xGB	125A Horiz. CED	125A Vert. ED	225A Horiz. QJ QR	225A Vert. QJ QR	225A Horiz. FD	250A Vert. FD	250A Vert. CFD	400A JD	400A CJD	600A LD	600A CLD
*Min. Box Size	26"	32"	38"	38"	26"	32"	32"	32"	38"	38"	44"	50"	50"	62"	56"	62"
200% Neutral (lug type)	0	0	6 (all)	6 (all)	0	0	0	N/A	0	N/A	0	0	0	0	0	0
Std. Lugs (100% Neut. PNL)	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
CU Lugs (100% Neut. PNL)	6	6	6	0	N/A	N/A	0	N/A	0	N/A	0	0	0	0	0	0
Comp Lugs (100% Neut. PNL)	6	6	6	6	N/A	N/A	0	N/A	0	N/A	0	0	0	0	0	0
Feed-thru Standard Lugs	6	6	12	12	6	6	6	N/A	6	N/A	6	6	12	12	12	12
Feed-thru Cu Lugs Feed-thru	6	6	12	N/A	N/A	N/A	6	N/A	6	N/A	6	6	12	12	N/A	N/A
Comp Lugs	6	12	12	N/A	N/A	N/A	6	N/A	6	N/A	12	12	12	12	N/A	N/A
Subfeed Standard Lugs	0	6	6	N/A	-	_	_	_	_	_	_	_	N/A	_	_	_
(1) FD Subfeed (Horizontal Mtg.)	N/A	12	12	12	N/A	N/A	N/A	N/A	N/A	12	12	12	12	12	12	12
(2) FD Subfeed (Vertical Mtg.)	N/A	24	24	24	N/A	N/A	N/A	N/A	N/A	24	24	24	24	N/A	N/A	N/A
SPD	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12	12

**NOTE**: N/A = OPTION NOT AVAILABLE

## **Compression Lugs**

Style	Amp Rating	Breaker Type	Compression Connectors	Box Height Addition - Inches (mm)
	125	N/A	(1)#6 - 350 kcmil Al/Cu	6 (152)
	250	N/A	(1)#6 - 350 kcmil Al/Cu	6 (152)
	400	N/A	(1) 400 - 600 kcmil Cu or (2)#6 - 350 kcmil Al/Cu	6 (152)
	600	N/A	(2)#6 - 350 kcmil Cu or Cu/Al or 400 - 600 kcmil Al/Cu	6 (152)
	100	ED4, ED6, HED4, CED6 <sup>①</sup>	(1)#14-2/0 AWG Cu or Al	Box must go to 24" wide on CED6 breaker only Add 6" to box height for NØ
	225	QJ2, QJH2, QJ2H QR2, QRH2, HQR2, HQR2H	(1)#6 AWG - 350 kcmil Cu or Al	Box must go to 24" wide
Main	250	FXD6, HFD6, CFD6	(1)#6 AWG - 350 kcmil Cu or Al	Box must go to 24" wide for all breakers Requires an additional 6.0" box height
Breaker	400	JD6, JXD6, HJD6, CJD6, SJD6, SHJD6, SCJD6	(2)#1/0 AWG - 500 kcmil Cu or Al	9 (229)
	600	LD6, LXD6, HLD6, CJD6, SLD6, SHLD6, SCLD6	(2)#2/0 AWG - 500 kcmil Cu or Al	6 (152)

## **Alternate Lugs**

Style	Amp Rating	Breaker Type	Standard AL Connectors	Box Height Addition - Inches (mm)			
MLO	400	N/A	(1) 250 - 750 kcmil or (2)#3/0 AWG - 250 kcmil Cu or Al	6 (152)			
Main Breaker	400	JD6, JXD6, HJD6, CJD6, SJD6, SHJD6, SCJD6	(1)#4/0 AWG - 750 kcmil Cu or Al	6 (152)			

<sup>\*</sup>Min. Box Size, corresponding to 9" of Unit Space.

## **Type P2 Panelboard Connector Modifications**

## **Enclosure Modifications**

## Description

Wider enclosure - 24" wide

Type 1 with gasket

Type 1 with dripshield

Type 2 enclosures

Type 3R enclosures

Type 3R/12 enclosures

## Type 4—Water Tight, Dust Tight, Steel Enclosure® (Actual NEMA-4

enclosure is larger than standard

Type 1 enclosure. See chart below for reference to approximate actual size.)

Standard Box Height	Actual NEMA 4 Enclosure Size®				
(in inches)	Н	W	D		
32	32	20	8		
38	42	30	8		
44	48	36	8		
56	60	36	10		

NOTE: Larger Type 4 enclosures are not available.

## Type 4X—Water Tight, Dust Tight and Corrosion Resistant®

(consult plant for actual enclosure size)

Catalogue	Enclosure – Stainless Steel Size (inches) (304SS is standard)				
Number	Н	w	D		
B4X26	26	20	5.75		
B4X32	32	20	5.75		
B4X38	38	20	5.75		
B4X44	44	20	5.75		
B4X50	50	20	5.75		
B4X56	56	20	5.75		
B4X62	62	20	5.75		
B4X68	68	20	5.75		
B4X74	74	20	5.75		

Enclosure – Fiberglass Size (inches)					
Н	D	W			
36	30	8			
36	30	8			
48	36	12			
48	36	12			
60	36	12			
60	36	12			

NOTE: 316SS is available as an option - must be specified.

- ① 16 Gauge Cans w/ 14 Gauge Front)
- ② 14 Gauge only ③ 14 Gauge only 304SS Std, 316SS Optional)

## Gauge Steel of Boxes/Fronts, Surface and Flush

Dimensions in Inch	es (mm)	Gauge Steel			
Width Height		Вох	Front/Door	Туре	
20 (508)	26-74 (660-1880)	14	14 <sup>3</sup>	Type 1	
20 (508)	26-74 (660-1880)	16 <sup>②</sup>	16/14 <sup>②</sup>	Type 3R/12	
20-36 (508-914)	32-60 (813-1524)	14 <sup>3</sup>	14 <sup>3</sup>	Type 4	
20 (508)	26-74 (660-1879)	14 <sup>④</sup>	14 <sup>4</sup>	Type 4X	
30-36 (762-914)	36-60 (914-1524)	N/A <sup>⑤</sup>	N/A <sup>⑤</sup>	Type 4X Non-Metallic	

- ② 15 Gauge Steel Can with 14 Gauge Door or Similar Approved Construction

- No Optional Gauge available
   304SS 14 Gauge Std., 316SS 14 Gauge optional
   Sizes do not match Standard Enclosure Sizes See Table P1-21 material is non-metallic No Gauge Specified.

## **Type P2 Panelboard Kits and Accessories**

#### **Standard Enclosures**

Box	Catalogue Number								
Height	Type 1 Sta	ndard Trim							
Inches	Box	Surface Flush		Type 3R	Type 3R/12 ①				
26	B26	S26B	F26B	NR26	WP26				
32	B32	S32B	F32B	NR32	WP32				
38	B38	S38B	F38B	NR38	WP38				
44	B44	S44B	F44B	NR44	WP44				
50	B50	S50B	F50B	NR50	WP50				
56	B56	S56B	F56B	NR56	WP56				
62	B62	S62B	F62B	NR62	WP62				
68	B68	S68B	F68B	NR68	WP68				
74	B74	S74B	F74B	NR74	WP74				

① Same as Type 3R with Gasket added for Type 12 Spec.

#### **Options For Type 1 Trims**

Items must be ordered as manual line item on Spartanburg Hinged trim - Replace "B" suffix with "H" Door-in-door - Replace "B" suffix with "D" Screw to Box - Replace "B" suffix with "C" Metal card holder - Add "M" suffix on all trims

Selection

#### Option For 24" Wide Enclosures with Equal Gutter on Both Sides (Excludes Type 3R)

24" wide with equal gutter on both sides - Add "24" as prefix

#### **Breaker Kits and Accessories**

Kit Number	Description	Contents
BBKB32	BL/BQD 6-pole 3" branch breaker kit Cu/Tin	
BBKB32AT	BL/BQD 6-pole 3" branch breaker kit Al/Tin	Kit contains top barrier, (3) A/C connectors, (1) B connector, hardware
BBKB32CS	BL/BQD 6-pole 3" branch breaker kit Cu/Silver	
BBKCED32	CED branch breacker kit Cu/Tin	Vit contains composter lift for P2 400A 24" wide only
BBKCED32CS	CED branch breacker kit Cu/Silver	Kit contains connector kit for P2 400A, 24" wide only
BBKED32	ED 6-pole 3" branch breaker kit Cu/Tin	Kit contains busiless support inter whose beggins (2) A/C composters
BBKED32AT	ED 6-pole 3" branch breaker kit Al/Tin	Kit contains breaker support, inter-phase barrier, (3) A/C connectors, (1) B connector, hardware
BBKED32CS	ED 6-pole 3" branch breaker kit Cu/Silver	(1) B connector, nardware
BBKNB32 (P2/P3)	NGB 6-pole 3" branch breaker kit	Kit contains top barrier, (3) A/C connectors, (1) B connector, hardware
BBKGB32	NGB2/HGB2/LGB2 6-pole	Kit contains top barrier, (3) A/C connectors, (1) B connector, hardware
BBKQ1 (P2)	QJ branch breaker kit for 2 and 3-pole single mount	Kit to contain all connectors and cover plates necessary to mount both 2 and 3-pole breakers
BBKQR1 ①	QR branch breaker kit for 2 and 3-pole single mount in P2 panel	Kit to contain all connectors and cover plates necessary to mount both 2 and 3-pole breakers
DFK1	BL, BQD, ED deadfront kit for 1" pole breakers	Center strips 3", 6", 9", 15", 21" plus mounting hardware
DFFP3	Deadfront filler 3"	3" empty space filler and hardware
DFFP6	Deadfront filler 6"	6" empty space filler and hardware
BNK2	Branch neutral (P2)	Three tier lug with mounting hardware to increase neutral capacity
P2BK1	P2 250A max. Bonding Kit	Bonding strap and hardware
P2BK2	P2 400A max. Bonding Kit	Bonding strap and hardware
P2BK3	P2 600A max. Bonding Kit	Bonding strap and hardware
BBKQRP1FK	P2 Filler for QR. Horizontal or vertical mount. 1-phase/3-phase.	Kit contains all cover plates necessary to change from QJ to QR both 2 and 3-pole breakers.

① Although QR is rated 250A, it is limited to 225A in panelboard.

#### Type P2 Panelboards


#### Miscellaneous Parts and Accessories

Catalogue Number			Description		
EGK	Al Ground Bus 44 Connections	NBK6	Number Strips 86-168 (snap-in type, P2/P3 panels)		
P2BK1	P2 250A Bonding Kit	NBK7	Number Strips 169-210 (snap-in type, P2/P3 panels)		
P2BK2	P2 400A Bonding Kit	NBK8	Number Strips 211-252 (snap-in type, P2/P3 panels)		
P2BK3	P2 600A Bonding Kit	ECGK	Cu Ground Bus 44 Connections		
IMK1	Interior Adjusting Kit	IGK	Insulated Al Ground Bus		
11-1824-01	Plastic directory card holder	ICGK	Insulated Cu Ground Bus		
LPDC01	Directory Card (Pack of 10; ref. 12-1110-01)	EWK1	End Wall Kit with Knockouts (20" W x 5.75" DP)		
SDKN	Drip shield 20''W x 5.75''D	EWK2	End Wall Kit with Knockouts (24" W x 7.75" DP)		
NBK3	Number Strips 1-42 (snap-in type, P2/P3 panels)	DFFP1	1" Filler Plate – (suitable for replacing QF3-UL in P1 thru S5 Panelboards and Switchboards)		
NBK4	Number Strips 43-84 (snap-in type, P2/P3 panels)	МСНК	Metallic directory card holder		
NBK5	Number Strips 85-126 (snap-in type, P2/P3 panels)	EBF1	NEB/HEB Filler Plate		


# **Type P2 Panelboards**

#### Type 1 Box

Box is symmetrical



Type 3R and 3R/12 Box



① Dimensions are interior of the box. Add 5/8" to width for absolute dimension. Add 1/8" to height for absolute dimension.

Dimensions shown in inches and millimeters [].

## **Type P3 Panelboards**

#### **Features**

Another innovation from Siemens is the P3 panel. It is a smaller, footprint distribution panel to fit a large number of applications that require more (or larger) branch devices than the lighting panel class offer. This panel offers a wide array of factory-assembled options, and has the ability to mix breaker frames in unit space up to 250 amps. Bussing options for the P3 vary from the standard aluminum to copper designs. All bussing in the P3 panel is tin-plated as a standard. Silver-plated copper is offered as an option on a copper bus. Subfeed lugs (up to 400 amp) are just a few of the options of this unique panel.

The P3 panel configurations, defined by the unit space, allow for a given amperage, main device, and box height. The P3 panel starts with a 56" high box. Breaker unit space can be mixed and matched to meet customer requirements. All 1" pole breakers (BL, BQD. ED. xGB frames) are mounted in 3" or 6" pole increments. Breakers frames, above 125 amps, are mounted in 6" single or twin breaker mountings. As an example panel, FD 250 amp and JD 400 amp breakers are mounted as subfeed breakers outside of unit space. Like other distribution panels, the P3 panel can have blank space added into the panel to allow for future expansions or modifications. Any expansions or modifications must be in 3" increments. BL, BQD and ED frame breakers have 3" or 6-pole kits and can be mixed in unit space by these increments. Breakers of the same frame can cross from one mounting to another if contiguous. xGB frame breakers cannot be mixed with other frame types. Any expansion or modification must be in 3" increments also. QJ/QR frame breakers are mounted in 6" increments for two and three pole single and twin mounted units. Changes in the unit space length for BL, BQD, xGB, or ED frame breakers require an additional deadfront center strip kit. Check with sales or the factory for additional unit space kits.

#### Main Lug/Main Breaker

Enclosure - Standard Type 1 enclosure is 24" wide x 7.75" deep. X Box Height is determined by main device and unit space. See charts for box height.

Voltage - 600V AC max. 250V DC max.

Amperage - 800 amp max.

**Short Circuit Rating -**200,000 A @ 480 Vac

100.000 A @ 600 Vac IR max. symmetrical or equal to the lowest rated device installed unless a series rating is indicated. Panels with subfeed or feed-thru lugs without a main device, circuit breaker or fusible unit, are limited to a three-cycle rating. The three-cycle rating for the P3 panel is limited to 22 Kaic. Note that the main device may be mounted remote from the panel.

Bussing - The P3 panel has more options to meet market requirements. The standard bussing is aluminum. The rating is per the requirements of CSA C22.2 No.29 – the standard for panelboards. All aluminum bussing is tin-plated. Optional bussing for the P3 panel is copper. The copper bus option for this panel is tin-plated.

#### Weight - Approximate

Total panelboard weight when filled with a normal quantity of breakers and accessories is about 5 lbs. (1 kg) per inch (54g per mm) of box height.

#### Gauge Steel of Boxes Fronts, Surface & Flush

Dimensions	Gauge Steel		
Width	Height	Box	Front
24" (610)	56 - 80" (1422, 2032)	#14	#14

#### Type I o I ancincatus

Panel Unit	Space	То	Box	( He	ight	t R	equi	rem	ents
					<u> </u>				

	P3 Panels Wit	P3 Panels With Standard Line Lugs. Unit Space (starting with 9" and adding 6" increments) "A" Dimension								
"B"	Main Lugs			Main Breakers	s					
Dimension Box Height	400A	600A	800A	400A JD	600A LD					
56	21	21	21	9	9					
62	27	27	27	15	15					
68	33	33	33	21	21					
74	39	39	39	27	27					
80	45	45	45	33	33					


#### Main Lug Wire Bending

Panel Amps	Standard Connectors	С	D
400	(2) #3/0 AWG - 250 kcmil or (1) 600 kcmil	16.00	17.88
600 800	(2) #3/0 AWG - 500 kcmil (2) 600 kcmil	16.00 16.00	17.88 17.88

#### Main Breaker Wire Bending - Inches (mm)


Panel Amps	С	E	F
JD	_	15.63 (397)	29.38 (746)
LD	_	14.75 (375)	29.38 (746)

#### Main Breaker Wire Bending Diagram



Main Breaker Wire Bending

#### Main Lug Wire Bending Diagram




Main Lug Wire Bending

#### Branch Breaker Side Gutters Inches (mm)

Reference Letter	Panel Width 24" (609)
А	7.750 (197)
В	7.125 (181)
C	6.000 (152)
D <sub>®</sub>	7.000 (178)
E	5.000 (127)
F	6.625 (168)

① Single branch mounting construction.

#### **Branch Breaker Wire Bending Diagram**



24 in. (610 mm)

**Branch Breaker Side Gutters** 

① This lug is removable.

# Type P3 Panelboards Selection

#### **Alternate Main Breakers**

Ampere	Breaker	Maximur Rating (k	n Interrup A)	ting	Ref. Catalogue	Available Configurations <sup>②</sup>			
Rating	Туре	240V	480V	600V	Number	240V AC	480V AC	600V AC	Available Trip Values
	JXD6 <sup>①</sup>	65	35	25	JX	STD	STD	STD	200, 225, 250, 300, 350, 400
	JD6 <sup>①</sup>	65	35	25	J6	STD	STD	STD	200, 225, 250, 300, 350, 400
400	HJXD6 <sup>①</sup>	100	65	35	H6	ADD	ADD	ADD	200, 225, 250, 300, 350, 400
400	HJD6 <sup>①</sup>	100	65	35	H5	ADD	ADD	ADD	200, 225, 250, 300, 350, 400
	SJD6 <sup>①</sup>	65	35	25	SJ	ADD	ADD	ADD	200, 300, 400
	SHJD6 <sup>①</sup>	100	65	35	S2	ADD	ADD	ADD	200, 300, 400
	LXD6 <sup>①</sup>	65	35	25	LX	STD	STD	STD	450, 500, 600
	LD6 <sup>①</sup>	65	35	25	L6	STD	STD	STD	250, 300, 350, 400, 450, 500, 600
600	HLXD6 <sup>①</sup>	100	65	35	HL	ADD	ADD	ADD	250, 300, 350, 400, 450, 500, 600
600	HLD6 <sup>①</sup>	100	65	35	НО	ADD	ADD	ADD	250, 300, 350, 400, 450, 500, 600
	SLD6 <sup>①</sup>	65	35	25	SL	ADD	ADD	ADD	300, 400, 500, 600
	SHLD6 <sup>①</sup>	100	65	35	S6	ADD	ADD	ADD	300, 400, 500, 600

# EI BOADDE

# Type P3 Panelboards

#### **Branch Circuit Breakers**

Max. Amp	Bolt-On		Provisions for Maximum Interrupting Rating (kA)							
Rating	Breaker Type	Amps	120V AC	120/240V AC	240V AC	277V AC	480V AC	600V AC	250V DC	
70	BQD6	15-70	_	65	65	_	_	10	14	
	BL	15–60 70 80–100	10 _ _	_ 10 _	_ _ 10	_ _ _	_ _ _		_ _ _	
	BLH	15–60 70 80–100	_ _ _	22 22 —	- - 22	_ _ _	_ _ _	_ _ _	- - -	
	HBL	15–55 60–100	_	65 —	- 65	_	_	_	_	
	BLR (240V)	15–60 70–100	_	_	10 10	_ _	_	_	_ _	
100	BLE (GFCI)	15–30 40–60	10 —	_ 10						
	BLEH (GFCI)	15–30 15–60	22 —	_ 22	_ _	_ _	_ _	_ _	_ _	
	BLF (GFCI)	15–30 40–60	10 —	_ 10	_	_ _	_		_	
	BLHF (GFCI)	15–30 40–60	22 -	_ 22	_	_	_	_	_	
	HBLF2 (GFCI)	15–30	65	_	_	_	_	_	_	
	BAF BAFH	15–20 15–20	10 22			_	_		_	
	BQD	15–60 70–100	_	65 —	- 65	_	14 14	_	14 14	
	NGB2	15-125	100	100	100	25	25	14	14 <sup>4</sup>	
	HGB2	15-125	100	100	100	35	35	22	14 <sup>4</sup>	
	LGB2	15-125	100	100	100	65	65	25	14 <sup>4</sup>	
125	ED4	15–60 70–100 110–125	65 — —	_ _ _	- 65 65	22 _ _	- 18 18	_ _ _	- 30 -	
123	ED6	15–60 70–100 110–125	- - 100	_ _ _	65 65 —	_ _ _	25 25 —	18 18 —	30 _ _	
	HED4	15–60 70–100 110–125	100 _ _	_ _ _	_ _ _	- 65 65	_ _ _	_ _ _	_ _ _	
	QJ2 QJH2 QJ2H	60–225 60–225 60–225	_ _ _	_ _ _	10 22 42	_ _ _	_ _ _	_ _ _	_ _ _	
225	QR2 QRH2 HQR2	100–225 100–225 100–225	_ _ _	_ _ _	10 25 65	_ _ _	_ _ _	_ _ _	_ _ _	
	HQR2H	100–225	_	_	100	_	_	_	_	

#### Subfeed Breakers (available in 2-pole or 3-pole)

Subject Breakers (available in 2 pole of 6 pole)									
Breaker	Mounting Position When Used as Subfeed Breaker	Ampere Ratings	Maximum Interrupting Rating (kA) Symmetrical						
Туре	Vertical	For Load	240V AC	480V AC	600V AC				
FD6 <sup>①</sup> , FXD6	Twin	70-250	65	35	18				
HFD6 <sup>①</sup> , HFXD6	Twin	70-250	100	65	25				
JD6 <sup>2</sup> , JXD6	Single	200-400	65	35	25				
HJD6 <sup>2</sup> , HJXD6	Single	200-400	100	65	35				

#### **Neutral Connectors**

recutiui comicet	013	
Wire Range	Max. Number of Connections	Max. Amps
#14-#1/0	44	125
#4 - 350 kcmil	6	250
(1)#4 - 600 kcmil or (2)#6 - 250 kcmil	1	400

NOTE: QJ/QR Breakers are twin mounted in unit space and take 6" of unit space. Limited to (6) per panel max. BL, HBL, BLH and BQD breakers are mounted in common mountings in 3" or 4) pole increments. ED2, ED4, ED6 and HED4 breakers are mounted in common mountings in 3" or (6) pole increments.

① Twin mounted subfeed breakers are mounted at bottom of panelboard only and adds 24" to the panel height.

② Subfeed breaker is mounted at bottom of panelboard only. 400 amp subfeed breaker adds 30" to the panel height.

<sup>@ 2-</sup>pole only (or) two outer poles of 3-pole breaker.

#### Enclosures

# Extra Gutter to Sides or Ends of the Can (Type 1 Only)

Description
6" end gutter
2" side gutter
Barrier in gutter (add to extra gutter price – min 4" required)
Hinged trims
Piano hinged trims Door-in-door trims
Screw to the box trims
Trim mounted devices
Pilot lights     Toggle switches
Push buttons
Painted boxes
Custom colours
Increase gauge trims
and boxes
Stainless steel trims,
Type 1

#### Meters

(Contact sales for pricing and application engineering for space requirements)

#### **Panel Skirts**

See page 10-64

# Panel Bus Modifications Represented by "A," "C" or "E" in the 11th digit of the catalogue number

Standard bussing is tin plated AI, alternate bus bar material can be selected:

- Tin plated copper
- Silver plated copper optional

# Subfeed and Feed-Thru (for 2-pole or 3-pole)

	1	
		Unit
Ampere	Connector	Space
Rating	Cu/Al Wire Range	(innches)

# **Subfeed (Double) Lugs** for Main Lug Panelboards Only

225/250	(2)-#6 AWG-350 kcmil	6
400	(2)—250 kcmil (1)—600 kcmil	6

# **Feed-Thru Lugs** — Cannot Be Used in Conjunction with SPD or Subfeed Breakers

See page <?> for unit space adders and compatibility with other options.

225/250	50 (1)—#6 AWG-350 kcmil		
400	0 (2)—250 kcmil (1)—600 kcmil		
600	(2)-250-500 kcmil	9	
800	(2)-600 kcmil	12	

#### **Branch and Main Breaker Accessories**

See page 10-44 and Breaker Section

- Handle blocks
- Handle locks
- Aux. Contacts®
- UVR®

#### Increase capacity neutral up to 200%

Main Bus Ar	nps	
125		
250		
400		
600		

See page 10-44 for unit space adders and compatibility with other options.

#### **Copper MLO Only**

Main Bus Amps	
125	
250	
400	
600	

(Devices mounted and wired to the trim should also have hinged trim specified)

#### **Surge Protection Device**

See Section 10

#### **Service Entrance Label**

Type P3 Panelboards are factory labeled "SUITABLE FOR USE AS SERVICE ENTRANCE EQUIPMENT" when identified as "Service Entrance" at the time of order entry. For regulations governing this feature, please consult CEC, CSA or local electrical authorities.

P3 service entrance panels are available in type 1 enclosure only (indoor application) and come standard with plated copper.

#### **Grounding of Panelboards**

Ground Bars are shipped with the panel interior factory mounted.

- Non-Insulated Equipment Ground Bar
   Ground Bar
- Copper Non-Insulated Ground Bar
- Al Insulated Equipment Ground Bar
- Cu Insulated Equipment Ground Bar

#### **Shunt Trip on Main or Branch**

BL, BLH, HBL, BQD, ED4, HED4, ED6, HED6, QJ2, QJ2H, QJH2, QR2, QRH2, HQR2, HQR2H as branch only. BL, BLH, HBL, NGB2, HGB2, LGB2, ED2, ED4, HED4, ED6, uses 1" unit space for shunt trip. All others may be used on mains or subfeeds.

# **Type P3 Panelboard Standard Modifications**

#### Selection

#### **Option Combinations**

Amps	Incoming	Subfeed Lugs	Feed-thru Lugs	FDa Subfeed	JD <sup>①</sup> Subfeed	FD <sup>②</sup> Subfeed	200% Neutral	Min. Box Size (in.)	Unit Space (in)
		•	_	_	_	_	•	56	21
		_	•	_	_	_	•	56	15
	Main Lug Only	_	_	•	_	_	•	56	9
		_	_	_	•	_	•	56	9
40023		_	_	_	_	•	•	62	9
400			_	_	_	_	•	56	9
			•	_	_	_	•	62	9
	Main Breaker (JD)	None Std.	_	•	_	_	•	68	9
			_	_	•	_	•	68	9
			_	_	_	•	•	74	9
		_	_	_	_	_	•	56	21
			•	_	_	_	•	56	15
	Main Lug Only		_	•	_	_	•	56	9
	,		_	_	•	_	_	56	9
60023			_	_	_	•	•	62	9
60000			_	_	_	_	•	56	9
			•	_	_	_	•	62	9
	Main Breaker LD	_	_	•	_	_	•	68	9
			_	_	•	_	_	68	9
			_	_	_	•	•	74	9
			_	_	_	_	•	56	21
	Main Lug Only	Main Lug Only – – –	•	_	_	_	•	56	9
800@3			_	•	_	_	•	56	9
			_	_	•	_	_	56	9
			_	_	_	•	•	62	9

① Subfed lugs are currently not offered as standard with

main circuit breakers.

② Subfed lugs on panels above 400A are not standard.

③ 200% neutral cannot be provided along with a 400A subfeed breaker because the breaker blocks the 4th lug site.

# **Type P3 Panelboard Modifications and Additions**

#### **Compression Lugs**

Style	Amp Rating	Breaker Type	Compression Connectors	Box Height Addition
	400	N/A	(1) 250 - 500 kcmil or (2)# 1/0 AWG - 250 kcmil	
MLO	600	N/A	(2)#3/0 AWG - 500 kcmil	_
	800	N/A	(2) 400-750 kcmil Cu only	_
Main	400	JD6, JXD6, HJD6, SJD6, SHJD6	(2)#1/0 AWG - 500 kcmil Cu or Al	_
Breaker	600	LD6, LXD6, HLD6, SLD6, SHLD6	(2)#2/0 AWG - 500 kcmil Cu or Al	_

#### **Alternate Lugs**

Style	Amp Rating	Breaker Type	Standard AL Connectors	Box Height Addition
	400	N/A	(1) 250 - 750 kcmil or (2)#3/0 AWG - 250 kcmil Cu or Al	6
MLO	800	N/A	(3) 500 kcmil	6
	800	N/A	(4) 1/0-750 kcmil Cu or Al	6
Main Breaker	400	JD6, JXD6, HJD6, SJD6, SHJD6	(1)#4/0 AWG - 750 kcmil Cu or Al	6

#### **Enclosure Modifications**

24" Panel Width Description			
Type 3R enclosures			
Type 3R/12 enclosures <sup>①</sup>			
Gasket between trim and box (Type 1)			

# Type 4X For Type P3<sup>®</sup> Water Tight, Dust Tight and Corrosion Resistant (consult plant for actual enclosure size and for

Type 4<sup>2</sup> enclosures)

Box Height	Enclosure – Stainless Steel			
Inches	Н	W	D	
56	56	24	7.75	
62	62	24	7.75	
68	68	24	7.75	
74	74	24	7.75	
80	80	24	7.75	

② 14 Gauge only - 304SS Std, 316SS Optional)

## **Type P3 Panelboard Kits and Accessories**

#### **Standard Enclosures**

Box	Catalog Number								
Height	Type 1 Stan	dard Trim							
(in.)	Box	Surface	Flush	Type 3R	Type 3R/12				
56	24WD56	P3S56	P3F56	24NRD56	24WPD56				
62	24WD62	P3S62	P3F62	24NRD62	24WPD62				
68	24WD68	P3S68	P3F68	24NRD68	24WPD68				
74	24WD74	P3S74	P3F74	24NRD74	24WPD74				
80	24WD80	P3S80	P3F80	24NRD80	24WPD80				

#### **Options For Type 1 Trims**

Items must be ordered as manual line item on factory Hinged trim – Add "H" suffix Door-in-door - Add "D" suffix Metal card holder - Add "M" suffix Provision for padlock - Add "-PL" suffix Service entrance application - Add "SE" suffix

#### **Breaker Kits and Accessories**

Kit Number	Description	Contents		
BBKGB32 (P2/P3)	NGB2, HGB2, LGB2 3" branch breaker kit	Kit contains top barrier, (3) A/C connectors, (1) B connector, hardware		
BBKB32 (P2/P3) BL/BQD 6-pole 3" branch breaker kit		Kit contains top barrier, (3) A/C connectors, (1) B connector, hardware		
BBKNB32 (P2/P3)	NGB, 6-pole 3" branch breaker kit	Kit contains top barrier, (3) A/C connectors, (1) B connector, hardware		
<b>BBKEB32</b> (P3)	HEB 6-pole 3" branch breaker kit	Kit contains top barrier, (3) A/C connectors, (1) B connector, hardware		
<b>BBKED32</b> (P2/P3)	ED 6-pole 3" branch breaker kit	Kit contains breaker support, inter-phase barriers, (3) A/C connectors, (1) B connector, hardware		
BBKQ2 (P3) Branch breaker kit for 2 and 3-pole QJ twin mount		Kit contains all connectors and cover plates necessary to mount both 2 and 3-pole breakers		
BBKQR2 <sup>①</sup> P3 twin BKR mounting kit for 1-phase/3-phase.		Kit contains all connectors and cover plates necessary to mount both 2 and 3-pole breakers		
DFK1	BL, BQD, ED deadfront kit for 1" pole breakers	Center strips 3", 6", 9", 15", 21" plus mounting hardware		
DFFP3	Deadfront filler 3"	3" empty space filler and hardware		
DFFP6	Deadfront filler 6"	6" empty space filler and hardware		
P3BK1	P3 bonding kit	Bonding strap and hardware		
EBF1	HEB/NEB Filler Plate	Filler Plate		
BBKQRP2FK	P3 Filler for QR. Dual mount horizontal. 1-phase/3-phase.	Kit contains all cover plates necessary to change from QJ to QR both 2 and 3-pole breakers. For 1-phase panel, both breakers must change from QJ to QR, cannot have one of each installed.		

① Although QR is rated 250A, it is limited to 225A in panelboard.


#### Type P3 Panelboards

#### **Miscellaneous Parts and Accessories**


	Description			
Catalogue Number	Description			
EGK	Al Ground Bus 44 Connections			
BK1	Bonding kit for 250A max. and all P1 panels			
IMK1	Interior Adjusting Kit			
11-1824-01	Directory Card Holder			
LPDC01	Directory Card			
NBK3	1 Numbering Button Kit "Snap-in" type 1 @ 42			
NBK4	1 Numbering Button Kit "Snap-in" type 43 @ 84			
NBK5	1 Numbering Button Kit "Snap-in" type 85 @ 126			
NBK6	Number Strips 127-168.			
NBK7	Number Strips 169-210.			
NBK8	Number Strips 211-252.			
ECGK	Cu Ground Bus 44 Connections			
IGK	Insulated AI Ground Bus			
ICGK	Insulated Cu Ground Bus			
EWK2	End Wall Kit with Knockouts (24" W x 7.75" D)			
DFFP1	1" Filler Plate (Suitable for replacing QF3 in P1 thru S5 Panelboards and Switchboards)			
P3BK1	P3 Bonding Kit			
JCK24	24 trim screws and 24 trim clips			
DFK1	BL, BQD, ED deadfront kit for 1" (include 7 different length centre strips)			
12-1110-01	1 Directory card for 1-42 circuits			
MCHK	1 Metallic directory card holder			
FPLK2	2 Spare Fas-latch trim locks with 2 keys			
DSK724	1 Dripshield 24"W x 7.75"D			

## Type P3 Panelboards

Type 1 Box Box is symmetrical



## Type 3R and 3R/12 Box



①Dimensions are interior of the box. Add 5/8" to width for absolute dimension. Add 1/8" to height for absolute dimension.

Dimensions shown in inches and millimeters [ ].

#### **Power and Disribution**

Type S5 (SPP6)

600 Volts AC, 250 Volts DC Maximum 1200 Ampere Mains 1200 Ampere Maximum Branch UL & CSA Short Circuit Rating -200,000A IR Maximum

**Branch Breaker Symmetrical Interrupting Capacity** 

#### Based on Underwriters' Test **Procedure**

Meets 1996 NEC wire bending requirement, section 373-6. CSA - C22.2 No. 0.12

#### **Panelboards**

Listed by Underwriters' Laboratories, Inc., under "Panelboards" File #E2269 for interiors and #E4016 for boxes and fronts. Meet Federal Specification W-C375B/Gen. & CSA File #LR93833.

600 Volts AC, 250 Volts DC, Maximum. 1 Phase, 3 Wire; 3 Phase, 3 Wire; or or 3 Phase, 4 Wire.

#### **Panelboard Fronts and Doors**

Standard panelboards are furnished with 4 piece trim with ventilation. Fronts are fabricated from code gauge steel and finished ASA61.

#### **Main Breakers**

All 400A and 1200A frame main breakers are mounted horizontally.

#### **Main Lug Connectors**

Ampere Rating	Connectors Suitable for Cu or Al
400	(1)–#3/0 AWG-500kcmil
400	(2)-#3/0 AWG-250kcmil
600	(2)-#3/0 AWG-500kcmil
800	(3)–#3/0 AWG-500kcmil
1200	(4)–#3/0 AWG-500kcmil

#### **End Gutters**

Ampere Rating	Main Lug (inches)	Main Breaker (inches)
400/600	15.967	13.0
800/1200	15.967	13.0

#### **Boxes**

38" wide, 12.75" deep (Type 1, 2) 38" wide, 14.25" deep (Type 3R/12)

#### **Panelboard Specifications**

Max Pand Amp	-	Unit Space (MLO)	Box Height				
400 600 800 120	)A )A	30" 45" 60" 60"	60" 75" 90" 90"	120/240Volts 1 Phase, 3 Wire	120/208 Volts 3 Phase, 4 Wire	600 Volts 3 Phase, 3 Wire	347/600 Volts 3 Phase, 4 Wire

#### **Integrated Equipment Short Circuit Ratings**

The term "Integrated Equipment Short Circuit Rating" refers to the application of series connected circuit breakers in a combination that allows some breakers to have lower individual interrupting ratings than the available fault current. This is permitted as long as the series combination has been tested and certified by UL & CSA.


Series ratings must be specified on order at time of entry.

#### **Main Breaker Selection**

			Maximum Interrupting Rating (kA)			
Amperage Rating	Breaker Type	Trip Type	240V	480V	600V	Available Trip Values
	JXD6		65	35	25	200, 225, 250, 300, 350, 400
	JD6	Thermal	65	35	25	200, 225, 250, 300, 350, 400
	HJD6	Magnetic	100	65	35	200, 225, 250, 300, 350, 400
400	HHJD6		200	100	50	200, 225, 250, 300, 350, 400
	CJD6		200	150	100	200, 225, 250, 300, 350, 400
	SJD6	Electronic	65	35	25	200, 300, 400
	SHJD6	(Solid State)	100	65	35	200, 300, 400
	SCJD6	State)	200	150	100	200, 300, 400
	LXD6		65	35	25	450, 500, 600
	LD6	Thermal	65	35	25	250, 300, 350, 400, 450, 500, 600
	HLD6	Magnetic	100	65	35	250, 300, 350, 400, 450, 500, 600
600	HHLD6 CLD6		200	100 150	50	250, 300, 350, 400, 450, 500, 600
	SLD6				100	450, 500, 600
	SHLD6	Electronic (Solid	65 100	35 65	25 35	300, 400, 500, 600 300, 400, 500, 600
	SCLD6	State)	200	150	100	300, 400, 500, 600
	MXD6	,	65	50	25	500, 600, 700, 800
	MD6	Thermal	65	50	25	500, 600, 700, 800
	HMD6	Magnetic	100	65	50	500, 600, 700, 800
800	CMD6		200	100	65	500, 600, 700, 800
	SMD6	Electronic	65	50	25	600, 700, 800
	SHMD6	(Solid	100	65	50	600, 700, 800
	SCMD6	State)	200	100	65	600, 700, 800
	NXD6		65	50	25	800, 900, 1000, 1200
	ND6	Thermal	65	50	25	800, 900, 1000, 1200
	HND6	Magnetic	100	65	50	800, 900, 1000, 1200
1200	CND6		200	100	65	800, 900, 1000, 1200
	SND6	Electronic	65	50	25	800, 1000, 1200
	SHND6	(Solid	100	65	50	800, 1000, 1200
	SCND6	State)	200	100	65	800, 1000, 1200

#### **Branch Breaker Gutter Dimensions** For 38"W Distribution Section (Table 5) Α Α

Selection



#### **Power and Disribution**

**Branch Circuit Breaker Selection**<sup>①</sup>

Selection

Breaker	Tuin				Mounting H	eight Inches (	mm	)	Max IC Rating (kA)			
Frame Rating	Trip Type	Breaker Type	Poles	Trip Amperage	Single	Twin	Gu	tter <sup>©</sup>	240V	480V	600	
_ · · · <u>J</u>	71	BL	1, 2, 3	15, 20, 25, 30, 40, 50, 60, 70, 80, 90, 100	_	3.75" (95)@3	Α	14" (356)	10	1	/	
	Thermal	BLH	1, 2, 3	15, 20, 25, 30, 40, 50, 60, 70, 80, 90, 100	_	3.75" (95)@3	Α	14" (356)	22	/	/	
	Magnetic	HBL	1, 2, 3	15, 20, 25, 30, 40, 50, 60, 70, 80, 90, 100	_	3.75" (95)@3	Α	14" (356)	65	/	/	
		BQD6 <sup>⑤</sup>	1, 2, 3	15, 20, 30, 40, 50, 60, 70	_	3.75" (95)23	Α	14" (356)	65	/	10	
100	Cround Foult	BLE (GFCI)	1, 2	15, 20, 30, 40, 50, 60	_	3.75" (95) <sup>2</sup>	Α	14" (356)	10	/	/	
	Ground Fault Circuit Interrupter	BLF (GFCI)	1, 2	15, 20, 30, 40, 50, 60	_	3.75" (95) <sup>②</sup>	Α	14" (356)	10	/	/	
		BLHF (GFCI)	1, 2	15, 20, 30, 40, 50, 60		3.75" (95) <sup>2</sup>	Α	14" (356)	22	/	/	
	Arc Fault Circuit	BAF (AFCI)	1	15, 20		3.75" (95)©	Α	14" (356)	10	/	/	
	Interrupter	BAFH (AFCI)	1	15, 20	_	3.75" (95) <sup>2</sup>	Α	14" (356)	22	/	/	
		ED2	1, 2, 3	15, 20, 30, 40, 50, 60, 70, 80, 90, 100	3.75" (95)23	3.75" (95)23	D	10" (254)	10	/	1	
		ED4	1, 2, 3	15, 20, 30, 40, 50, 60, 70, 80, 90, 100, 110, 125	3.75" (95)23	3.75" (95)23	D	10" (254)	65	18	10	
		ED6 HED4	1, 2, 3	15, 20, 30, 40, 50, 60, 70, 80, 90, 100, 110, 125 15, 20, 30, 40, 50, 60, 70, 80, 90, 100, 110, 125	3.75" (95) <sup>2</sup> 3 3.75" (95) <sup>2</sup> 3	3.75" (95) <sup>23</sup> 3.75" (95) <sup>23</sup>	D	10" (254) 10" (254)	100	18 65	18 30	
	Thermal	CED6	2, 3	15, 20, 30, 40, 50, 60, 70, 80, 90, 100, 110, 125	3.75" (95)3	3.75" (95)®	E	7.61" (193)	200	200	100	
125	Magnetic	HEB	2, 3	15, 20, 30, 40, 50, 60, 70, 80, 90, 100, 110, 125	- -	3.75" (95)@3	C	11.62 (295)	100	65	25	
	Widgilotto	NGB	1, 2, 3	15, 20, 25, 30, 40, 50, 60, 70, 80, 90, 100, 110, 125		3.75" (95)@3	В	13.98" (355)	100	25	14	
		NGB2	1, 2, 3	15, 20, 25, 30, 40, 50, 60, 70, 80, 90, 100, 110, 125		3.75" (95)23	В	13.98" (355)	100	25	14	
		HGB2	1, 2, 3	15, 20, 25, 30, 40, 50, 60, 70, 80, 90, 100, 110, 125	_	3.75" (95)23	В	13.98" (355)	100	35	22	
		LGB2	1, 2, 3	15, 20, 25, 30, 40, 50 ,60, 70, 80, 90, 100, 110, 125	_	3.75" (95)@3	В	13.98" (355)	100	65	25	
	Electronic	NDG	3	60, 100, 150	_	5" (127)	Н	10.9" (276)	65	35	18	
150	(Solid State)	LDG	3	60, 100, 150	_	5" (127)	Н	10.9" (276)	200	100	18	
		QJ2	2, 3	60, 70, 80 ,90, 100, 110, 125, 150, 175, 200, 225	5" (127)	5" (127)	F	8.75" (222)	10	/	/	
		QJH2	2, 3	60, 70, 80 ,90, 100, 110, 125, 150, 175, 200, 225	5" (127)	5" (127)	F	8.75" (222)	22	/	/	
	Thormal	QJ2H	2, 3	60, 70, 80 ,90, 100, 110, 125, 150, 175, 200, 225	5" (127)	5" (127)	F	8.75" (222)	42	/	/	
225	Thermal Magnetic	QR2	2, 3	100, 110, 125, 150, 175, 200, 225	5" (127)	5" (127)	F	8.75" (222)	10	/	/	
		QRH2	2, 3	100, 110, 125, 150, 175, 200, 225	5" (127)	5" (127)	F	8.75" (222)	25	/	/	
		HQR2	2, 3	100, 110, 125, 150, 175, 200, 225	5" (127)	5" (127)	F	8.75" (222)	65	/	/	
		HQR2H	2, 3	100, 110, 125, 150, 175, 200, 225	5" (127)	5" (127)	F	8.75" (222)	100	/	/	
250	Thermal	FXD6, FD6	2, 3	70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250	5" (127)	5" (127)	G	8.25" (210)	65	35	22	
	Magnetic	HFD6	2, 3	70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250	5" (127)	5" (127)	G	8.25" (210)	100	65	25	
		CFD6	2, 3	70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250		5" (127)	J	11.76" (299)	200	200	100	
	Electronic	NFG	3	100, 150, 250	_	5" (127)	Н	10.9" (276)	65	35	18	
	(Solid State)	LFG	3	100, 150, 250	— 0.75" (222)	5" (127)	Н	10.9" (276)	200	100	25	
	Thermal	JXD6, JD6 HJD6	2, 3	200, 225, 250, 300, 350, 400	8.75" (222) 8.75" (222)	8.75" (222)	K	7.92" (201) 7.92" (201)	65 100	35 65	25 35	
	Magnetic	HHJD6	2, 3	200, 225, 250, 300, 350, 400 200, 225, 250, 300, 350, 400	8.75" (222)	8.75" (222) 8.75" (222)	K	7.92 (201)	200	100	50	
	Magnetic	CJD6	2, 3	200, 225, 250, 300, 350, 400	8.75" (222)	-	N	12" (305)	200	150	100	
400		SJD6	3	200, 300, 400	8.75" (222)	_	M		65	35	25	
400		SHJD6	3	200, 300, 400	8.75" (222)	_	M	13.42" (341)	100	65	35	
	Electronic	SCJD6	3	200, 300, 400	8.75" (222)	_	N	12" (305)	200	150	100	
	(Solid State)	NJG	3	250, 400	6.25" (159)	6.25" (159)	L	8" (203)	65	35	25	
		LJG	3	250, 400	6.25" (159)	6.25" (159)	L	8" (203)	200	100	25	
		LXD6	2, 3	450, 500, 600	8.75" (222)	_	М	13.42" (341)	65	35	25	
	Therman	LD6	2, 3	250, 300, 350, 400, 450, 500, 600	8.75" (222)	_	M	13.42" (341)	65	35	25	
	Thermal Magnetic	HLD6	2, 3	250, 300, 350, 400, 450, 500, 600	8.75" (222)	_	M	13.42" (341)	100	65	35	
600	Magnetic	HHLD6	2, 3	250, 300, 350, 400, 450, 500, 600	8.75" (222)	_	M	13.42" (341)	200	100	50	
000		CLD6	2, 3	450, 500, 600	8.75" (222)	_	N	12" (305)	200	150	100	
	Electronic	SLD6	3	300, 400, 500, 600	8.75" (222)	_		13.42" (341)	65	35	25	
	(Solid State)	SHLD6	3	300, 400, 500, 600	8.75" (222)	_	-	13.42" (341)	100	65	35	
	, ,	SCLD6	3	300, 400, 500, 600	8.75" (222)	_	N	12" (305)	200	150	100	
		LMXD6, LMD6	2, 3	500, 600, 700, 800	8.75" (222)	_	R	13" (330)	65	50	25	
	Th	HLMXD6, HLMD6		500, 600, 700, 800	8.75" (222)	_	R	13" (330)	100	65	50	
	Thermal	MXD6	2, 3	500, 600, 700, 800	10" (254)	_	P	13" (330)	65	50	25	
000	Magnetic	MD6	2, 3	500, 600, 700, 800	10" (254)	_	P	13" (330) 13" (330)	65	50	25	
800		HMD6 CMD6	2, 3	500, 600, 700, 800 500, 600, 700, 800	10" (254) 10" (254)	_	P	13" (330)	100 200	65 100	50 65	
		SMD6	3	600, 700, 800	10 (254)	_	Q	12" (305)	65	50	25	
	Electronic	SHMD6	3	600, 700, 800	10" (254)		Q	12" (305)	100	65	50	
	(Solid State)	SCMD6	3	600, 700, 800	10" (254)	_	Q	12" (305)	200	100	65	
		NXD6	2, 3	800, 900, 1000, 1200	10" (254)	_	P	13" (330)	65	50	25	
	Thermal	ND6	2, 3	800, 900, 1000, 1200	10" (254)	_	P	13" (330)	65	50	25	
	Magnetic	HND6	2, 3	800, 900, 1000, 1200	10" (254)	_	P	13" (330)	100	65	50	
1200	.5	CND6	2, 3	800, 900, 1000, 1200	10" (254)	_	P	13" (330)	200	100	65	
		SND6	3	800, 1000, 1200	10" (254)	_	0	12" (305)	65	50	25	
	Electronic	SHND6	3	800, 1000, 1200	10" (254)	_	Q		100	65	50	
	(Solid State)	SCND6	3	800, 1000, 1200	10" (254)	_		12" (305)	200	100	65	

Space includes housing frame plate with blank cover plate. Provision includes all necessary mounting hardware, less circuit breaker, and includes housing frame cover plate with breaker handle opening.
 1 to 6 poles may be mounted in 3.75" (95) of unit space.
 Accessories such as shunt trips on three pole breakers require 6.25" (159) of unit space.

⑤ Also 10KA at 600Y/347 Volts.⑥ Refer to Table 5 for layout dimensions.

#### **Modifications and Additions**

#### Type S5

When required, special constructions or additions to standard panelboards may be specified for all factoryassembled Power and Distribution Panelboards. Below and on the next page are listed many of those available for Type S5 panelboards. In no case do these apply to Narrow (Column) Width Lighting Panelboards or Unassembled Panelboards.

#### 1. Miscellaneous

NEMA TYPE	
Type1 Type 2 (Drip-proof) Type 3R Type 12	

#### 2. Painted Finish

Touch-Up Paint (ASA61, Light Gray) 12 oz. aerosol can, Catalog Number TUP61

#### 3. Miscellaneous Accessories

Nameplate — laminated, engraved
Tamper-Resistant Screws

#### 4. Devices Mounted on Gutter Cover Includes Device, Mounting — Wired or Unwired

Toggle Switch — SPST or 3-way; 15A	
Pilot Light — General Purpose, Neon or Incandescent	
Pushbutton	

#### 5. Feed-Thru Lugs<sup>①</sup> (One Set Per Panel)

Ampere			Unit Space (Additional inches)
Rating	3-Pole	2-Pole	MLO
400			10
600	Consult	Consult	10
800	Sales	Sales	17.5
1200			17.5

®For use on main lug, main breaker or main switch panels without subfeed breakers.

3 For short circuit ratings with remote control switches,

Available in 90" high enclosure only. Unit space is 42 1/2" with Test and Monitor Panel; 45" without Test

<sup>2</sup> Ground bar not installed in box.

consult sales office.

and Monitor Panel.

#### 6. MLO Compression Lugs -

Available as main lugs and neutral lug.

Ampere Rating	Aluminum (Specify Size )	Copper (Specify Size)	Deduct From Available Unit Space (inches)
400 600	Consult	Consult Sales	5 5

#### 7. Grounding of Panelboards<sup>2</sup>

Non-Insulated Equipment Ground Bus Including Ground Lug Insulated Equipment Ground Bus Including Ground Lug

#### 8. Remote Control Switches 34

600V AC	ASCO 920 Mechanically Held <sup>@3</sup>		Siemens CLH Electrically Held <sup>®</sup>	
Rating	2-Pole	3-Pole	2-Pole	3-Pole
30	Unit space 20"		Unit space 20"	
60				
75				
100	٥ ٥١	20	0 0	400 20
150 <sup>④</sup>				
200 <sup>4</sup>				
225				

#### 9. Increased Capacity Neutral

Ampere Ra	nting Neutral	Unit Space (inches)
400	600	None
400	800	None
600	1200	None
800	1200	None

#### 10. Circuit Breaker Accessories **Handle Blocking Device** Blocks handle in either the "ON" or "OFF" position. Available for:

Breaker Type	Cat. Number
BL, BLH, HBL, BQ, BQH, HBQ	ECQL1
All BQD, GB	BQDHBD
All QJ	QJHS1
All QR	HPLQR
AII BQD, NGB, NGB2, HGB2, LGB2	BQDPLD
All ED	E2HBL
All FD	FD6HB1
All JD, LD, LMD	JD6HBL
All MD, ND, PD	MN6BL

#### Not available on Sensitrip III.

#### Padlocking Device - Padlocks in "OFF" position. Available for:

Breaker Type	Cat. Number
BQ, BQH, BL, BLH, HBL	ECGTD3
One Pole BL, BLF, BE, BAF	ECPLD1
Two-Pole BL, BLF, BE	ECPLD2
All QJ	HL9419
All QR	HPLQR
All BQD, NGB, NGB2, HGB2, LGB2	BQDPLD
All ED	ED2HPL
All FD	FD6PL1
All JD, LD, LMD	JD6HPL
All MD, ND, PD	MN6PLD

#### 11. Ground Fault Sensing Relay Kit<sup>®</sup> **Equipment Protection (30 ma)**

For Use with Breaker Types		Description
ED4, ED6, HED4	1, 2, 3	Basic kit Basic kit with bell alarm

#### 12. Main Bus

Standard main bus and ground bus are tin plated aluminum. For copper main bus, neutral bus and ground bus change prefix 'A' to 'C' on catalog number and contact your sales office for pricing.

#### 13. Copper Lugs — For Main Lug Only Panels

Standard main lugs and neutral lugs are tin plated aluminum, UL & CSA listed for use with aluminum/copper cables. For copper lugs in the mains and neutral for use with copper cables only, contact sales.

#### 14. Shunt Trip on Main 56789 and Branches

Description	Cat. Number
"BL, BQD6 (branch only) QJ2, QJ2H, QJH2, QR2, QRH2, HQR2, HQR2H, ED2, ED4, HED4 (branch only) All others through 1200A"	See breaker portion of this catalogue

#### 15. Sentron TPS (TVSS Modules)

100kA, 150kA, 200kA, 250kA, 300kA
Options
Surge Counter
Remote Indicator

#### 16. Customer Metering

Siemens Digital Metering with Remote Display SEM3 Embedded Metering

10 Not CSA approved.

 $<sup>\</sup>ensuremath{\mathfrak{G}}$  For required unit space — consult local sales office.

<sup>©</sup> Price does not include control power transformer.

® Price 600 Volt 7½" high units.

Mounting height increases to 6.25" when shunt trip is required.

Shunt Trip on 100A frame breakers increases mounting height to 6.25" for twin mounting.

# **Modifications and Additions Replacements for Circuit Breakers**

#### Selection

#### **Replacement Connecting Strap Guide**

The following table may be used to obtain the proper connector kit by measuring the exterior dimensions of the panel. Every attempt has been made to make this table complete and accurate. The table is based on panels produced by ITE, Bulldog and Siemens from 1958 to present. Should any questions arise please contact your Siemens sales office for replacements.

Panelboard	nelboard			
Tub Width	Depth	Panel Type	Replacement Max Amps	Note
30" - 36" - 42"	9″	OLD CDP	400	MCCB only.
	9.75"	OLD CDP	600	MCCB only.
32" - 38"	13.75"	CDP/VB6	1200A	MCCB series 6 connectors
	10.75	CDI/VDO	600A	"VB" style units only (*)
38"	12.75"	SPP/FPP6	1200A	MCCB series 6 connectors
	.2.70	0.17	600A	"VK" or "VB" style (*)

<sup>\*</sup> If switch unit width is 17" it is a vacubreak. If switch unit width is 23" or 28" it is a "VK" switch.

#### Connecting Strap For Use With SPP/FPP, S5<sup>3</sup>

Max Amp Rating	Breaker Family	Breaker Type	Catalogue Number	Unit Height	Mounting
100	General	BQ, BQH, HB BL, BLH, HBL, BQD6	6BL2C <sup>②③</sup>	3.75" (95)	Twin
		NGB	SNBD	3.75" (95)	
	General	NGB2, HGB2, LGB2	SGB2D	3.75" (95)	
125		HEB	SEBD	3.75" (95)	Twin
	Sentron	ED2, ED4, ED6, HED4	6E62 <sup>①②</sup>	3.75" (95)	
	Sentron	CED6	6CLE2 <sup>①</sup>	3.75" (95)	
150	VL	NDG, LDG	SDGD	5" (127)	Twin
225	General Purpose	QJ2, QJH2, QJ2H	6QJ2 <sup>①</sup>	5" (127)	Twin
		QR2, QR2H, HQR2, HQR2H	6QR2 <sup>①@</sup>	5" (127)	
	Sentron	FXD6, FD6, HFD6, HHFD6	6F62 <sup>①</sup>	5" (127)	Twin
250	VL	NFG, LFG	SFGD	5" (127)	
	Sentron	CFD6	6CLF1C	5" (127)	Single
	Sentron	JXD6, JD6, HJD6, HHJD6	6JJ62 <sup>①</sup>	8.75" (222)	Twin
400	VI	NJG, LJG	SJG1D	6.25" (159)	Single
400	\ \L	NJG, LJG	SJG2D	6.25" (159)	Twin
	Sentron	CJD6	6CLJ1C	8.75" (222)	Single
	Sentron	LXD6, LD6, HLD6, HHLD6, SLD6, SHLD6	6LL61C	8.75" (222)	
600		CLD6	6CLL1C	8.75" (222)	Single
		SCLD6	6SCL61C	8.75" (222)	
800	Sentron	MXD6, MD6, HMD6, CMD6, SHMD6, SCMD6	6M61C	10" (254)	Single
1200	Sentron	NXD6, ND6, HND6, CND6, SHND6, SCND6	6N61C	10" (254)	Single

# Blank Filler Plates (No Breaker Cutout)

	For use with Series 6 CDP Panelboards, S5, F2 SMP, FCI and FCII Switchboards.		
Height	SPP/FPP/CDP/VB		
	•		
1.25"	6FPB01		
2.50"	6FPB02		
3.75"	6FPB03		
5.00"	6FPB05		
10.00"	6FPB10		
15.00"	6FPB15		

#### Connecting Strap Kits and Front-Filler Plates<sup>①</sup> For use with NDP-CDP-7, S3

Breakers	Catalogue Number
BQD6 (S3 only)	7 BQD6-2
BL, BLH, HBL,	7 BL-2
QJ2, QJH2, 2 Pole	7 QJ2-1
QJ2, QJH2 3 Pole Single unit, Panel Mount	7 QJ3-1
QJ2, QJH2 3 Pole Double unit, Panel Mount	7 QJ3-2
ED2, ED4, ED6,HED4	7 E6-2
Filler 1 Pole	DFFP1

These are aluminum connectors. If copper is required please add suffix **C**.

please add suffix **C**.
② 3.75" (95) plate accommodates six 1-pole breakers.
③ Connecting strap kits include connecting straps, hardwares, and cover plates for switchboards and power panels. Breakers to be ordered separately.

<sup>4</sup> QR filler plate only, use p/n: 6QR2FK.

#### Type F2

600 Volts AC, 250 Volts DC Maximum 600 Ampere Main Switch, 1200 Ampere Main Lugs Only 600 Ampere Maximum Branch UL & CSA Short Circuit Rating -200,000A IR Maximum

**Fusible/Power and Distribution** 

Meets 1996 NEC wire bending requirement, section 373-6. CSA - C22.2 No. 0.12

#### **Panelboards**

Listed by Underwriters' Laboratories, Inc., under "Panelboards" File #E2269 for interiors and #E4016 for boxes and fronts & CSA File #LR93833.

#### **Service**

600 Volts AC, 250 Volts DC, Maximum. 1 Phase, 3 Wire; 3 Phase, 3 Wire; or 3 Phase, 4 Wire.

#### **Boxes**

38" wide, 12.75" deep, Type 1

#### **Panelboard Fronts and Doors**

Standard panelboards are furnished with 4 piece trim. Fronts are fabricated from code gauge steel and finished ASA61.

The Proper Fuse Type for the Application is Selected Using the Following Parameters:

- Voltage Requirements
- Conductor Ampacity
- Horsepower Requirements
- Maximum Available RMS Fault Current
- UL & CSA Fuse Class

#### **Main Switch Panel Connectors**

Ampere Rating	Connectors Suitable for Cu or Al
400	(1) - 750 kcmil OR (2) - 250 kcmil (Cu or Al)
600	(2) - 750 kcmil OR (4) - 250 kcmil (Cu or Al)
800	(3)—#3/0 AWG–500 kcmil
1200	(4)—#3/0 AWG-500 kcmil

#### **Branch Switch Connectors**

Switch Ampere Rating	Wire and Cable Range
30	(1)-#14-#2 AWG (Cu or Al)
60	(1)-#14-#2 AWG (Cu or AI)
100	(1)-#14-#1/0 AWG (Cu or AI)
200	(1)—#6 AWG-350 kcmil (Cu or AI)
400	(1) - 750 kcmil OR (2) - 250 kcmil (Cu or Al)
600	(2) - 750 kcmil OR (4) - 250 kcmil (Cu or Al)

#### **Main Lug Panels**

Ampere Rating	Connectors Suitable for Cu or Al
400 <sup>①</sup>	(1)—#3/0 AWG–500 kcmil (2)—#3/0 AWG–250 kcmil
600	(2)-#3/0 AWG-500 kcmil
800	(3)—#3/0 AWG–500 kcmil
1200	(4)—#3/0 AWG–500 kcmil

#### **Gutters**

Ampere Rating	End Gutters (Minimum inches)	Side Gutters (Minimum inches)
400	12	7.9
600	12	7.9
800	12	7.9
1200	12	7.9

#### **Maximum VB HP Ratings**

		3 Phase		Single Phase	DC
Amp		Volts		Volts	Volts
Rating	240	480	600	240	250
30	7.5	15	20	3	5
60	15	30	50	10	10
100	30	60	50	15	20
200	60	125	50	_	40
400	50	50	50	_	50
600	50	50	-	_	_

#### **Maximum VK HP Ratings**

	3 Phase			Single Phase	DC
Amp		Volts		Volts	Volts
Rating	240	480	600	240	250
30	7.5	15	20	3	5
60	1.5	30	50	10	10
100	30	50	75	15	20
200	60	125	150	15	40

#### **UL & CSA Fuse Classes**

Class	Amperes	Volts	Interrupting Ratings	l <sup>2</sup> t, l <sub>p</sub>	Circuits
H (code)	1-600A	250 and 600V or less AC	10,000A		Less than 10,000A available
K <sup>®</sup>	1-600A	250 and 600V or less AC	50,000A	_	Feeder circuits
J	1-600A	600V or less	To 200,000A	I <sup>2</sup> t-Low Ip-Low	Feeder circuits (motor load small %)
RK1	1/10-600A	600V or less 250V or less	To 200,000A	I <sup>2</sup> t-Slightly > J Ip-Slightly > J	Feeder circuits (motor load small %)
RK5	1/10-600A	600V or less 250V or less	To 200,000A	I <sup>2</sup> t- > RK-1 Ip- > RK-1	Motor starting currents a factor
Т	1-600A	300 and 600V or less AC	To 200,000A	I <sup>2</sup> t-Low I <sub>p</sub> -Low	Non-motor loads
L	601-5000A	600V or less	To 200,000A	I <sup>2</sup> t-Low I <sub>p</sub> -Low	Feeder circuits motor loads

#### **Power and Disribution** Selection

Type F2

Maximum Panel Ampere	Unit Space (MLO)	Box Height				
400A	30"	60"	120/240Volts	120/208 Volts	600 Volts	347/600 Volts
600A	45"	75"	1 Phase, 3 Wire	3 Phase, 4 Wire	3 Phase, 3 Wire	3 Phase, 4 Wire
800A	60"	90"				
1200A	60"	90"				

#### **Branch Switches 600V Maximum**<sup>①</sup>

Rating Ampere	Maximum Voltage	Fusing (1)	Mounting Height F2 38" W
30/30A (VK)		J, C	6.25(159)
60/60A (VK)		J, C	6.25(159)
100/100A (VK)		J, C	7.5(190)
200A (VB)	600V	J, Code, R	10(254)
200/200A (VK)		J	10(254)
400A (VB)		J, Code, R,T	15(381)
600A (VB)		J, Code, R,T	15(381)

#### Fuse Clip provisions per unit

Class R	ClassT
Rating Ampere	Rating Ampere
30	30
60	60
100	100
200	200
400	400
600	600

Single or twin units as listed and are valid for class C or J fuses. If class R orT fuse provisions are required add per table above.
 Not applicable to VB style units 400A and 600A.

Use of auxiliary switch kit will require the use of a 7.5" (190) high unit for 30 and 60 Amp. switches.
 Refer to Siemens for single phase and DC horsepower requirements.

Ratings are based on UL test procedure. CSA will not recognize ratings above 100Hp.

# **Modifications and Additions**

#### Type F2

When required, special constructions or additions to standard panelboards may be specified for all factory-assembled Power and Distribution Panelboards. Below and on the next page are listed many of those available, for Type F2 panelboards. In no case do these apply to Narrow (Column) Width Lighting Panelboards.

#### 1. Miscellaneous

NEMA TYPE	
Type 1 Type 2 (Drip-proof) Type 3R Type 12	

#### 2. Painted Finish

Description
Touch-Up Paint (ASA61, Light Gray) 12 oz. aerosol can,
Catalog Number TUP-61

#### 3. Miscellaneous Accessories

Nameplate - laminated, engraved Tamper-Proof Screws

#### 4. Devices Mounted on Gutter Cover Includes Device, Mounting — Wired or Unwired

#### Description

Toggle Switch - SPST or 3-way; 15A

Pilot Light - General Purpose, Neon or Incandescent

Pushbutton

#### 5. Grounding of Panelboards<sup>3</sup>

Non-Insulated Equipment Ground **Bus Including Ground Lug** Insulated Equipment Ground Bus Including Ground Lug

#### 6. Remote Control Switches<sup>4</sup> 600V AC

600V AC	ASCO 920 Mechanically Held <sup>®®</sup>		Siemens CLH Electrically Held <sup>©</sup>	
Rating	2-Pole	3-Pole	2-Pole	3-Pole
30				
60				
75				
100	Unit space 20"		Unit space 20"	
150 <sup>©</sup>				
200 <sup>⑤</sup>				
225				

#### 7. Increased Capacity Neutral

Ampere Phase	Ampere Rating Phase Neutral	
400	600	None
400	800	None
600	1200	None
800	1200	None

#### 8. Main Bus

Standard main bus and ground bus is tin plated aluminum. For copper main bus, neutral bus and ground bus change prefix 'A' to 'C' on catalog number and contact your sales office for pricing.

#### 9. Copper Lugs -For Main Lug Only Panels

Standard main lugs and neutral lugs are tin plated aluminum, UL & CSA listed for use with aluminum/copper cables. For copper Lugs in the mains and neutral for use with copper cables only, contact sales.

#### 10. Feed-Through Lugs <sup>1</sup> (One Set Per Panel)

Ampere			Unit Space (Additional inches)
Rating	3-Pole	2-Pole	MLO
400	Consult		10
600		Consult	10
800	Sales Office	Sales	17.5
1200	Office	Office	17.5

#### 11. MLO Compression Lugs

Available as main lugs and neutral lug.

	Aluminum (Specify Size )	Copper (Specify Size)	Deduct From Available Unit Space (inches)	
400			5	
600			5	
000			_	
800			5	
1200			5 5	

#### 12. VK Switch Accessories

Item	Cat. No.
Fuse Pullers (2) 30/60 mp	FP2
100 amp	FP3
200 amp	FP4

#### 13. Sentron TPS (SPD Modules)

100 KA	200 KA	300 KA
150 KA	250 KA	
Options Surge Counter Remote Indicator		

#### 14. Customer Metering

Siemens Digital Metering with Remote Display SEM3 Embedded Metering

① For use on main lug, main breaker or main switch panels without subfeed breakers.

 $<sup>\</sup>begin{tabular}{ll} \hline \end{tabular}$  For increase in panelboard height — Consult local sales office.

<sup>3</sup> Ground bar is not installed in box.

<sup>4</sup> For required unit space — consult local sales office. Price includes increased enclosure height if required.

Devices listed by Underwriters' Laboratories, Inc.
 When 2 wire control is required. Relay and Terminal Block (9" of unit space required).

<sup>®</sup> For short circuit ratings with remote control switches consult sales office.

② Panelboard short circuit rating is limited to 5,000 RMS symmetrical.

# NEI BOARDS 10

# **Modifications, Additions Replacements for Fusible Switches**

#### Type F2 Replacement Units 12

	600 Volts		
Amperes	J Fuses	Height	
Rating	Cat. No.	in (mm)	

#### VK Switch For Use With FPP6 Panelboardscd3459

30/30	VK23611JP	6.25 (159)
60/60	VK23622JP	6.25 (159)
100/100	VK33633JP	7.5 (90)
200/200	VK73644JP	10 (254)

#### **VB Switch For Use With VB6 Panelboards** 9

30/30	V7E3611JP	7.5(190)
60/60	V7E3622JP	7.5(190)
100/100	V7E3633JP	7.5(190)
200	V7F3604JP	10(254)
400	V7H3605JP	15(381)
600	V7H3606JP	15(381)

#### Connecting Strap Kits®

Rating Amperes	VB Switch VB6 <sup>®</sup> Cat. No.	VK Switch Series 6 Cat. No.
30/30 60/60 100/100	VB6-71	VK6-57 VK6-57 VK6-58
100 200/200 200 400-600	VB6-71 N/A VB6-71 VB6-150	N/A VK6-72 VK6-71 <sup>©</sup> N/A

#### Blank Filler Plates®

For use with Series 6 CDP Panelboards, S5, F2, FCI and FCII Switchboards.		
	SPP/FPP/CDP/VB	
Height	6	
1.25"	6FPB01	
2.50"	6FPB02	
3.75"	6FPB03	
5.00"	6FPB05	
10.00"	6FPB10	
15.00"	6FPB15	

Panelboard				
Tub Width	Depth	Panel Type	Replacement Max Amps	Note
	9″	OLD CDP	400	MCCB only.
30" - 36" - 42"	9.75"	OLD CDP	600	MCCB only.
32" - 38"	13.75"	CDP6/VB6	1200A 600A	MCCB series 6 connectors "VB" style units only (*)
38"	12.75″	SPP6/FPP6	1200A 600A	MCCB series 6 connectors "VK" or "VB" style (*)

<sup>©</sup> For Series 6 Main Devices above 200A, add suffix MS to Catalog Number when ordering.

When 2-Pole units are required, use 3-Pole.
 Series 6 (VB6, CDP6) replacement units and connector kits also accommodates FCI and FCII distributions interiors. Units installed after October 1991 will be FPP6 type.
 Refer to Siemens for units equipped with auxiliary switches.

<sup>®</sup> Price is for two brackets – to be included with filler plates. ® To be used in tubs with 30-200A, VB units or fillers in  $12^5/8''$  deep tub.

② Can be used as fillers or in place of circuit breakers, VK or VB Switches.

<sup>®</sup> Fusible switch kits include fusible switches and cover plates for switchboards and power panels. Connecting strap kits to be ordered separately.

<sup>©</sup> Connecting strap kits include connecting straps and hardware. See Note 9 for cover plates.

## **Embedded Micro Metering Module™**

Selection

#### SEM3 System Configured in Panelboards

The Siemens SEM3 system can be configured for factory installation in branch circuit monitoring application. This option can lower the installation time of the system for the installer while providing a factory warrantied solution.

The SEM3 system can be factory installed in unit space in type P2 & S5 Siemens panel boards. Please note P1 and P3 configurations are not available at this time and the amount of unit space needed varies depending upon the application. Please note that lead time adders will apply and may vary depending upon the configuration of the system.

#### SEM3 for use in Siemens Panelboards

#### Available in a Type 1 and 2 rated enclosure



#### Controller

Each SEM3 Controller can monitor up to 45 circuits. Applications that require monitoring more than 45 circuits will require additional controllers.



#### **Current Transformers (CTs)**

Five sizes of CTs are available for use in the S5 panel: 50, 125, 250, 400, 600, 800 & 1200 amp. Each bracket supports a maximum of 3 CTs and is designed for the breaker selected (brackets are not interchangeable between breaker frames). Each CT will be attached to a data module that is placed in the meter racks.



#### **Meter Racks**

All meter racks will be installed next to the SEM3 controller unit space. The 21 space meter rack is used as a default option where possible.

**NOTE**: Monitoring of 45 circuits will require: two 21 position racks and one 3 position rack

#### **Other Considerations**

**Configuration**: Data modules from CTs monitoring a circuit breaker must be mounted adjacent to one another in the meter rack. Any field changes to the factory configuration must take this into account.

**Start-up & Commissioning:** Siemens can provide these services. Contact your local Siemens sales office for more details.


# Panel Skirts/System Types, AC & DC Voltages

#### Conduit Enclosing Shield (Panel Skirts)

Sheet metal to cover conduits above or below a standard panelboard box.


Skirt Length	Width	Depth
8, 9, 11, 12	20.00	5.75
14, 17, 18, 23, 25	20.00	5.75
26, 27, 28, 29, 30, 31, 32, 33, 34, 35, 36	20.00	5.75
37, 38, 39, 40, 41, 42, 43, 44	20.00	5.75
8, 9, 11, 12	24.00	7.75
14, 17, 18, 23, 25	24.00	7.75
26, 27, 28, 29, 30, 31, 32, 33, 34, 35, 36	24.00	7.75
37, 38, 39, 40, 41, 42, 43, 44	24.00	7.75


#### **Panel Skirts Standard Length**



8, 9, 10,11, 12, 14, 17, 18, 23, 24, 25, 26, 27, 28, 29, 30, 31, 32, 33, 34, 35, 36, 37, 38, 39, 40, 41, 42, 43, 44

#### **Busing**





Single-phase

Three-phase

#### **AC Voltages**

#### 1 phase, 2 wire

- 120V 1 phase, 2 wire
- 240V 1 phase, 2 wire



#### 1 phase, 3 wire

■ 120/240V 1 phase, 3 wire




#### 1 phase, 2 wire, Wye

277V 1 phase, 2 wire




#### 1 phase, 2 wire, Delta

480V 1 phase, 2 wire



#### 1 phase, 3 wire, Delta

240/480V 1 phase, 3 wire




#### 3 phase, 4 wire, Wye

- 208Y/120V 3 phase, 4 wire
- 480Y/277V 3 phase, 4 wire
- 600Y/347V 3 phase, 4 wire




- 240/120V 3 phase, 4 wire
- 480/240V 3 phase, 4 wire



#### 3 phase, 3 wire, Delta

- 240V, 3 phase, 3 wire
- 480V, 3 phase, 3 wire
- 600V, 3 phase, 3 wire240V, 3 phase, 3 wire, arounded B



• 600V, 3 phase, 3 wire, grounded B



- 1 phase, 3 wire, Wye
- 208Y/120V 1 phase, 3 wire
- 480Y/277V 1 phase, 3 wire



С

#### DC voltage

#### 1 phase, 2 wire

125Vdc, 2 wire

(Up to 125Vdc, MLO option only.)



# Type HCP Switchboard and Power Panel Units, Accessories

#### **Features**

- CSA certified under file #24563 and UL Listed under file #E6849 Vol 1, Sect. 8
- 400-1200A ratings
- Visible contacts
- Field installable shunt trip and auxiliary switch accessory kits
- Installs in existing Siemens switchboards
- Suitable for use on systems with up to 200,000A available fault current, RMS symmetrical when equipped with Class J or Class L fuses
- Group mounts with other 30A through 600A switches, and 100 through 1200 amp frame breakers
- Allows 800A and 1200A switches in standard 38" wide distribution sections in either main or branch configurations
- 16¼" mounting height is the smallest 1200A design in the industry, allowing up to 4 units in one vertical section
- Field reversible horizontal mounting design for left or right hand cabling
- Handle can be padlocked in the OFF position with up to three padlocks with 5/16" hasps. A cover padlocking provision is also supplied

#### Selection



#### 3-Pole, Horizontal Mount<sup>①</sup>

	B4	B4					Horse	power R	ating				
Catalogue	Maximum Ampere	Maximum AC Voltage	Fuse	Dimen	sions (in	ches*)	240V		480V		600V		250V
Number	Rating	Rating <sup>®</sup>	Class	Н	w	D	Std	Max	Std	Max	Std	Max	DC
HCP367HJ400	400	600	J	16.25	17.22	7.38	50	125	100	250	125	350	40
HCP367HJ600	600	600	J	16.25	17.22	7.38	75	200	150	400	200	400	40
HCP327HT	800	240	Т	16.25	17.22	7.38	100	250	_	_	_	_	50
HCP367H	800	600	L	16.25	17.22	7.38	100	250	200	500	250	500	50
HCP328HT	1200	240	Т	16.25	17.22	7.38	100	250	_	_	_	_	50
HCP368H	1200	600	L	16.25	17.22	7.38	100	250	200	500	250	500	50

#### 3-Pole, Vertical Mount

o : 0:0, : 0:0:00													
HCP367VJ400	400	600	J	17.00	16.25	7.38	50	125	100	250	125	350	40
HCP367VJ600▲	600	600	J	17.00	16.25	7.38	75	200	150	400	200	400	40
HCP327VT	800	240	Т	17.00	16.25	7.38	100	250	_	_	_	_	50
HCP367V	800	600	L	17.00	16.25	7.38	100	250	200	500	250	500	50
HCP328VT	1200	240	Т	17.00	16.25	7.38	100	250	_	_	_	_	50
HCP368V	1200	600	L	17.00	16.25	7.38	100	250	200	500	250	500	50

#### Accessories

#### Terminal Connectors (one lug per kit)

Ampere Rating	Catalogue Number	Connector Wire Range
400-600A	TA2K500	(2) #1 AWG-500 kcmil (Cu or Al)
400-600A	TC2K500	(2) #1 AWG-500 kcmil (Cu only)
400-800A	TA3K500	(3) #1 AWG-500 kcmil (Cu or AI)
400-800A	TC3K350	(3) #1 AWG-350 kcmil (Cu only)
800-1200A	TA4H500	(4) #2 AWG-500 kcmil (Cu or Al)
800-1200A	TA3H750	(3) 500-750 kcmil (Cu or Al)

#### **Auxiliary Switch Kits**

Contact	Maximum Vol	tage	Switch		Catalogue
Ampere Rating	AC	DC	Mounting	Contacts	Number
15A	480	125	Left Pole	1NO/1NC	A01HCPL4▲
15A	480	125	Right Pole	1NO/1NC	A01HCPR4

#### **Shunt Trip Kit**

Control Volta		
AC	DC	Catalogue Number
120	_	HCPST120
240	_	HCPST240▲
277	_	HCPST277
480	_	HCPST480▲

<sup>\*</sup>For inches / millimeters conversion, multiply inches by

#### **Switchboard Connection Strap Kit** ①

	•
Switch	
Ampere Rating	Catalogue Number
400-1200A	F6162DCAN

# ▲ Built to order. Allow 6–8 weeks for delivery. ① For horizontal mounting only in either 38" wide min switchboards or S5/F2 power panelboards.

#### T Fuse Adapter Kits (one per pole)

Catalogue	
Number	Description
TFAK72	800A, 300V AC
TFAK75	800A, 600V AC
TFAK82	1200A, 300V AC

#### HCP Replacement Handle Kit

(For use on all HCP switches)

SW Ampere Rating	Catalogue Number
400-1200A	НСРНК

#### **Compression Lug Adapter Kit**


The use of this kit provides for the mounting of up to four lugs per phase. Each kit accepts lugs with (2) 3/8" diameter mounting holes on 1" centers. One kit per pole line or load is required. Lugs are not provided.


Ampere Rating	Catalog Number
400-1200A	HCPCLP


<sup>&</sup>lt;sup>®</sup> Both 240 and 600V AC switches are also rated 250V DC


## **Type HCP Switchboard Units**


#### Horizontal Mount Drawing












# Group Mounting Assembly (Horizontal Mount Only)



Note: Right exit shown, rotate 180° for left exit Note: Items 26 & 27 are used to ground the switch enclosure (Route bonding wire along flange)

Item	Parts Supplied in Connection Strap Kit Cat. No. F6162D	Qty.
1-2	A/CØ Strap (Short)	1ea.
3-4	BØ Strap	1ea.
5-6	A/C Ø Strap (Long)	1ea.
7-8	Switch Mounting Bracket	1ea.
9	Insulation	1
10	1-3/8" Insulator	3
11	3/8-16 X 3/4" HHMS	3
12	3/8" Lock Washer	3
13	3/8" Flat Washer	3
14	3/8-16 X 3/4" RHSNB	3
15	Strap Bus Hardware Kit	2
16	1/4-28 X 3/8" SHWHSW	4
17	5/16-18 Insert	6
18	5/16-18 X 1" SRHMS	6
19	5/16 Flat Washer	6
20	5/16 Lock Washer	6
21	1/4-20 X 1" SRHMS	2
26	Ground Bracket	1
27	10-32 X 1/4" SHWHSW	2

## **Circuit Breaker / Column Type**

#### Type C1

240 Volts AC Maximum 250 Ampere Mains 250 Ampere Maximum Branch UL Short Circuit Rating -200,000 IR Maximum

**Branch Breaker Symmetrical Interrupting Rating** 

Based on Underwriters' Test Procedure

Type C2

480Y/277 Volts AC Maximum 250 Ampere Mains 250 Ampere Maximum Branch UL Short Circuit Rating -100,000 IR Maximum

Meets NEC wire bending requirement, section 312-6.

#### **Panelboards**

Listed by Underwriter's Laboratories, Inc., under "Panelboards" File #E2269.

Meets Federal Specification W-C375B/Gen.

#### **Service**

240 Volts Maximum, 1-Phase, 3-Wire, or 3-Phase, 4-Wire.

#### **Panelboards Fronts and Doors**

Standard panelboards are furnished with trim with a flush door lock. All are factory assembled for ease of installation. Fronts are fabricated from code gauge steel and finished ANSI-61.

#### Main Breakers C1

BL, BLH and HBL frame breakers are mounted horizontally. All other frames are mounted vertically.

#### Main Breakers C2

BQD frame breakers are mounted horizontally. All other frames are mounted vertically.

#### **Boxes**

C1 — 7%" wide, 5%" deep. C2 — 8½" wide, 5¾" deep.

#### **Branch Breaker Side Gutters**

Туре	Circuit Breaker	Side Gutter (inches)
C1	BL, BLH, HBL	3.505
C2	BQD	3.5

#### Weight-Approximate

Total panelboard weight when filled with a normal quantity of breakers and accessories is:

\*About 3 lbs. per inch of box height.

#### **Gauge Steel Boxes**

Туре	Width	Height	Gauge Steel
C1	7%"	48", 73", 85"	#14
C2	8½"	48", 73", 85"	#14

#### **Fronts**

C1	7%"	48", 73", 85"*	#14
C2	8½"	48", 73", 85"*	#14

<sup>\*</sup>Note: Feed thru lugs and subfeed breaker not available for this height.

#### **Main Breaker Connectors**

Ampere Rating	Connectors suitable for Cu or Al
100	(1) #14–1/0 AWG
125	(1) #4–1/0 AWG
225	(1) #6 AWG–300 kcmil
250	(1) #4 AWG-350 kcmil Al (1) #6 AWG-350 kcmil Cu

#### Main Lugs

125	(1) #6 AWG-350 kcmil
250	(1) #6 AWG-350 kcmil

# VFI ROARIIS

## **Circuit Breaker / Column Type**

#### **Branch Breaker Selection C1**

Breaker	Available aker Ampere Availability				Maximum Interrupting Rating (kA)			
Туре	Rating	1-Pole	2-Pole	3-Pole	120V	120/240V	240V	
	15, 20, 30, 40, 50, 60				_	10	_	
BL (120V)	70	/	/		_	10	_	
	70, 80, 90, 100	_	/	/	_	10	_	
BLF (GFCI)	15, 20, 30	/	/	_	10	_	_	
BLF (GFCI)	40, 50, 60	_	/	_	10	_	_	
BLE (EQGFI)	15, 20, 30			_	10	_	_	
BGL (SWN)	15, 20, 30	_			10	_	_	
BLR (240V)	15, 20, 30, 40, 50, 60	_		_	_	_	10	
DLN (240V)	70, 80, 90, 100	_	/	_	_	_	10	
	15, 20, 30, 40, 50, 60				_	22	_	
BLH (120V)	70		/		_	22	_	
	70, 80, 90, 100	_	/	/	_	22	_	
BLHF (GFCI)	15, 20, 30	/	/	_	_	22	_	
	40, 50, 60	_	/	_	_	22	_	
LIDI	15, 20, 30, 40, 50				_	65	65	
HBL	60, 70, 80, 90, 100	_	/		_	65	65	

**Subfeed Breakers** — Limit One Per Panel o C1 (Not available for 42 circuit panels)

ED4	15, 20, 30, 40, 50, 60, 70, 80, 90, 100	_	/	/	_	_	65
ED4	110, 125	_	/	_	_	_	65
HED4	15, 20, 30, 40, 50, 60, 70, 80, 90, 100	_	/	/	_	_	65
пер4	110, 125	_	/	$\checkmark$	_	_	100
QJ2	60, 70, 80, 90, 100, 110, 125, 150, 175, 200, 225	_	/		_	_	10
QJH2	60, 70, 80, 90, 100, 110, 125, 150, 175, 200, 225	_	/	_	_	_	22
QJ2H	60, 70, 80, 90, 100, 110, 125, 150, 175, 200, 225	_		/	_	_	42
QR2	100, 110, 125, 150, 175, 200, 225	_	/	/	_	_	10
FXD6	70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250	_	/		_	_	65
HFD6®	70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250	_	/		_	_	100

#### Alternate Main Breaker Selection OSS C2

Ampere Rating	Breaker Type	IR	Catalogue Number	Available Trip Values
100	BQD	14	BD	50, 60, 70, 80, 90, 100
	ED4	18	E4	50, 60, 70, 80, 90, 100
	ED6	25	E6	50, 60, 70, 80, 90, 100
	HED4	42	H4	50, 60, 70, 80, 90, 100
	HHED6	65	H6	50, 60, 70, 80, 90, 100
125	ED4	18	E4	110, 125
	ED6	25	E6	110, 125
	HED4	42	H4	110, 125
	HHED6	65	H6	110, 125
225	FXD6	35	FX	70, 80, 90, 100, 110, 125, 150, 175, 200, 225
	HFD6	65	HF	170, 80, 90, 100, 110, 125, 150, 175, 200, 225
250	FXD6	35	FX	250
	HFD6	65	HF	250

#### **Branch Circuit Breakers C2**

Breaker	Available Breaker Ampere		Availability			Maximum Interrupting Rating (kA)		
Туре	Rating	1-Pole	2-Pole	3-Pole	277V	480/277V	480V	
BQD	15, 20, 30, 40, 50, 60		/	/	14	14	_	
BOD	70, 80, 90, 100	\ \ \	/		14	14	_	

#### Subfeed Breakers — Limit One Per Panel<sup>∞</sup> C2 (Not available for 42 circuit panels)

ED4	15, 20, 30, 40, 50, 60, 70, 80, 90, 100	_	✓	/	_	18	18
ED4	110, 125	_	✓	/	_	18	18
ED6	15, 20, 30, 40, 50, 60, 70, 80, 90, 100	_	/	/	_	_	25
EDO	110, 125	_			_	_	25
HED4	15, 20, 30, 40, 50, 60, 70, 80, 90, 100	_	/	/	_	_	42
ПЕД4	110, 125	_	\ \ \		_	_	42
FXD6	70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250	_	/	/	_	_	35
HFD6	70, 80, 90, 100, 110, 125, 150, 175, 200, 225, 250	_	/	/	_	_	65

① No increase in box height. Space is already built into C1 panel.

③ Interchangeable trip breakers such as FD6 and HFD6 cannot be back fed. Must be top feed only.

C1 panel.

® BL, BLH, HBL and BQD are horizontally mounted.
All others vertically mounted.

#### Type C1/C2

When required, special constructions or additions to standard panelboards may be specified for factory-assembled column panelboards.

#### **Box Modifications**

Description
Gasketed
Metal Card Holder
Welded Metal Card Holder
Nameplate
Al Ground Bar
Cu Ground Bar
Insulated Al Ground Bar
Insulated Cu Ground Bar

#### Interior Modifications

Description
Feed-Thru Lugs Cu Neutral Lugs Cu main Lugs 125A Cu main Lugs 250A

#### **Box Sizing Chart**

Certain modifications such as subfeed breakers and feed-thru lugs require additional unit space. Use this chart to determine proper enclosure size.

Panel Configuration	Box Height (inches)
All MLO 18 Circuit	48
All MLO 30 Circuit	73
All MLO 42 Circuit	85
All MLO 18 Circuit with feed-thru lugs	73
All MLO 30 Circuit with feed-thru lugs	85
All MLO 18 Circuit with subfeed breaker	73
All MLO 30 Circuit with subfeed breaker	85
All Main Breaker 18 Circuit	48
All Main Breaker 30 Circuit	73
All Main Breaker 42 Circuit	85
All Main Breaker 18 Circuit with feed-thru lugs	73
All Main Breaker 30 Circuit with feed-thru lugs	85
All Main Breaker 18 Circuit with subfeed breaker	73
All Main Breaker 30 Circuit with subfeed breaker	85

#### **Column Extension**

Available in various standard lengths, extensions are 5½ inches deep and 7 inches wide.

Height (inches)	Catalogue Number <sup>①</sup>
14	LXX-14
20	LXX-20
26	LXX-26
32	LXX-32
38	LXX-38
41	LXX-41
44	LXX-44
53	LXX-53
56	LXX-56
62	LXX-62
65	LXX-65
68	LXX-68
74	LXX-74
80	LXX-80
86	LXX-86

#### **Pull Boxes**

Two styles of pull boxes are available, top and front mounted. When the panel and its extensions are mounted in a structural WF beam a front mounted pull box is required. When the panels are surface mounted, a top mounted pull box may be used. Provisions are made so that the neutral bar may be mounted in the pull box when required. (Front mounted pull box dimensions are 14" H. X 20" W.)

Description	Catalogue Number <sup>①</sup>
Top Mount Front Mount <sup>2</sup>	LXXP-T LXX50-F
1 TOTIL WIGHTIE	LAASU-I

#### **Breaker Kits and Accessories**

Kit Number	Description	Contents
MBKQRC1FK	C1 Filler for QR in Main position 1PH or 3PH	Kit contains all cover plates necessary to change from QJ to QR both 2 and 3-pole breakers.


# **Circuit Breaker / Column Type**

## Conduit Enclosing Shield (Panel Skirts)

Sheet metal to cover conduits above or below a standard panelboard box.

Skirt Length	Width	Depth
8, 9, 11, 12	20.00	5.75
14, 17, 18, 23, 25	20.00	5.75
26, 27, 28, 29, 30, 31, 32, 33, 34, 35, 36	20.00	5.75
37, 38, 39, 40, 41, 42, 43, 44	20.00	5.75
8, 9, 11, 12	24.00	7.75
14, 17, 18, 23, 25	24.00	7.75
26, 27, 28, 29, 30, 31, 32, 33, 34, 35, 36	24.00	7.75
37, 38, 39, 40, 41, 42, 43, 44	24.00	7.75

#### **Panel Skirts Standard Length**



① Available only as a main switch for non-service equipment applications. Not available for branch devices.

## **Enclosure/System Types, AC & DC Voltages**


#### Type 1

- Flush or surface mount.
- Galvanized steel with removable end walls -blank or with knockouts to order.
- Box sizes: 20" W x 5.75" D x 33", 50", 59" or 69" H (510 W x 145 D x 838, 1270, 1500 or 1753mm H). Box can be rotated 180° to accommodate conduit feed.
- Enclosure and chassis mounting instructions are found in supplied literature.
- Chassis mounts directly onto studs in the enclosure.
- Trim finished with gray powder coat paint over phosphatized steel (ANSI 61).
- Door and door-in-door configurations with locks.
- Door locks use key #2A1910-2.
- Circuit directory card is located on the inside of the door.
- Trim screws are concealed.


#### Type 3R

- Surface mount only.
- Finished with gray powder coat paint over phosphatized steel (ANSI 61).
- Bottom feed only, no knockouts
- Box sizes: 20" W x 7.7" D x 34.5" 51.5", 60.5" or 70.5 H (510 W x 195 D x 876, 1310, 1535 or 1791mm H).
- Enclosure and chassis mounting instructions are found in supplied literature
- Chassis mounts directly onto studs in the enclosure.
- Gasketed door has vault handle with lock.
- Door locks use key #2A1910-1.
- Circuit directory card is located on the inside of the door.

#### **Busing**



Single-phase



Three-phase

#### **AC Voltages**

- 1 phase, 2 wire
- 120V 1 phase, 2 wire
- 240V 1 phase, 2 wire



- 1 phase, 3 wire
- 120/240V 1 phase, 3 wire




Selection


- 1 phase, 2 wire, Wye
- 277V 1 phase, 2 wire



- 1 phase, 2 wire, Delta
- 480V 1 phase, 2 wire



- 1 phase, 3 wire, Delta
- 240/480V 1 phase, 3 wire



- 3 phase, 4 wire, Wye
- 208Y/120V 3 phase, 4 wire
- 480Y/277V 3 phase, 4 wire
- 600Y/347V 3 phase, 4 wire



- 3 phase, 4 wire, Delta
- 240/120V 3 phase, 4 wire
- 480/240V 3 phase, 4 wire



- 3 phase, 3 wire, Delta
- 240V, 3 phase, 3 wire
- 480V, 3 phase, 3 wire
- 600V, 3 phase, 3 wire
- 240V, 3 phase, 3 wire, grounded B
- 480V, 3 phase, 3 wire, grounded B
- 600V, 3 phase, 3 wire, grounded B



- 1 phase, 3 wire, Wye ■ 208Y/120V 1 phase, 3 wire
- 480Y/277V 1 phase, 3 wire



#### DC voltage

- 1 phase, 2 wire ■ 125Vdc, 2 wire

(Up to 125Vdc, MLO option only, SCCPB 40A or less.)



# **Dimensions and Panelboard Configurations**

Selection


#### NEMA 1 and 3R Enclosure Dimensions


Encl. Type	Encl. Height	Dimensions H	(inches) HC	МН	СН	DH	RH	SH	DW	D
NEMA 1	33	33.0	N/A	29.0	26.0	28.9	25.0	2.0	20.0	5.7
	50	50.0	N/A	43.0	40.0	37.9	39.0	3.5	20.0	5.7
	59	59.0	N/A	52.0	49.0	46.9	48.0	3.5	20.0	5.7
	69	69.0	N/A	62.0	59.0	56.9	58.0	3.5	20.0	5.7
NEMA 3R	33	33.0	34.5	35.5	26.0	28.9	25.0	2.0	20.0	6.3
	50	50.0	51.5	52.5	40.0	37.9	39.0	2.0	20.0	6.3
	59	59.0	60.5	61.5	49.0	46.9	48.0	2.0	20.0	6.3
	69	69.0	70.5	71.5	59.0	56.9	58.0	2.0	20.0	6.3

Available panelboard configurations
Based on enclosure height, panel amp rating and number of branch circuit positions


Encl. height (inches)	Panel amp rating	Branch positions	Available configurations
33" 30–200	18	Main lug only, with or without feed-through lugs     Non-fused disconnect, no loadside options	
	30	· Main lug only, no loadside options	
30-60		18	· 30 through 60A fused main disconnect with or without feed-through lugs or TVSS device
	30–60	30	· 30 through 60A fused main disconnect with or without feed-through lugs or TVSS device
		42	· 30 through 60A fused main disconnect with or without feed-through lugs or TVSS device
	70–200	18	$\cdot$ 70 through 200A fused main disconnect with or without feed-through lugs or TVSS device
	70-200	30	· 70 through 200A fused disconnect with or without feed-through lugs
50"		18	Main lug only with TVSS device     Non-fused disconnect, with feed-through lugs or TVSS device
30–200 225–400A	30–200	30	Main lugs only, with feed-through lugs or TVSS device     Non-fused disconnect, with or without feed through lugs
		42	Main lug only, with or without feed-through lugs or TVSS device     Non-fused disconnect, with or without feed-through lugs
	225-400A	18	Main lug only, with ot without feed through lugs or TVSS device     Non-fused disconnect, with or without feed-through lugs
		30	· Main lug only, with or without feed-through lugs
70,000	70–200	30	· 70 through 200A fused main disconnect, with TVSS device
	30–200	42	· 70 through 200A fused main disconnect with or without feed-through lugs or TVSS device
59"		42	· Non-fused disconnect with TVSS device
	225–400A	18	<ul> <li>Main lug only with loadside disconnect</li> <li>Non-fused disconnect, with TVSS device</li> <li>225 through 400A fused disconnect with or without feed-through lugs or TVSS device</li> </ul>
		30	Main lug only, with TVSS device     225 through 400A fused disconnect, with no loadside options
		42	Main lug only, with or without feed-through lugs or TVSS device     Non-fused disconnect, with no loadside options
69" 225	225-400A	18	· Non-fused disconnect, with loadside disconnect
		30	Main lug only with loadside disconnect     225 through 400A fused disconnect with feed-through lugs or TVSS device
		42	Non-fused disconnect, with or without feed through lugs or TVSS device     225 through 400A fused main disconnect, with or without feed-through lugs or TVSS device

#### NEMA 1 and NEMA 3R Dimensions





Fuse Curves Selection



Time-Current Characteristic Curves– Average Melt

Current Limitation Curves

