

Pipe straps, pipe and conduit clamps and hangers

Design loads


Where design loads are indicated, they provide for a safety factor of 3 in conformance with the American Standard Code for Pressure Piping.

Hanger design

Pipe hangers are of advanced design to be user friendly.

Finishes and special materials

The standard finish is electrogalvanized (EGC) or GoldGalv®. Some products are offered in aluminum and stainless steel where noted.



701 O.D. Pipe and conduit clamp

Machine screw and nut included.

Standard finishes and materials


PG	Pregalvanized (i.e. 701-045PG)
AL	Aluminum (i.e. 701-045AL) with zinc-plated hardware
SS6	Stainless steel type 316 (i.e. 701-045SS6)



Cat. no.	O.D. of pipe		Rigid conduit (in.)	EMT conduit (in.)	Wt./C (lb)	Std. Pack
	(in.)	(mm)				
701-045PG	0.36-0.45	9-11.5	-	-	9	10
701-055PG	0.46-0.55	11.5-14	-	-	10	10
701-065PG	0.56-0.65	14-17	-	-	11	10
701-075PG	0.66-0.75	17-19.5	-	½	13	10
701-088PG	0.76-0.88	19.5-22.5	½	-	15	10
701-100PG	0.89-1.00	22.5-25.4	-	¾	16	10
701-113PG	1.01-1.13	25.5-29	¾	-	17	10
701-126PG	1.14-1.26	29-32	-	1	18	10
701-140PG	1.27-1.40	32-36	1	-	18	10
701-153PG	1.41-1.53	36-39	-	1¼	19	10
701-167PG	1.54-1.67	39-42.5	1¼	-	20	10
701-180PG	1.68-1.80	42.5-46	-	1½	23	10
701-193PG	1.81-1.93	46-49	1½	-	26	10
701-204PG	1.93-2.04	49-52	-	-	30	10
701-225PG	2.10-2.25	53-57.5	-	2	32	10
701-237PG	2.26-2.37	57.5-60	2	-	34	10
701-245PG	2.33-2.45	59.95-62.5	-	-	36	10
701-257PG	2.46-2.57	62.5-65.5	-	-	38	10
701-287PG	2.75-2.87	70-73	2½	2½	40	10
701-294PG	2.88-2.94	73-75	-	-	42	10
701-306PG	2.95-3.06	75-78	-	-	42.5	10
701-319PG	3.07-3.19	78-81	-	-	43	10
701-350PG	3.36-3.50	85.5-89	3	3	45	10
701-356PG	3.51-3.56	89-90	-	-	46	10
701-379PG	3.70-3.79	94-96.5	-	-	48	10
701-400PG	3.80-4.00	96.5-101.5	3½	3½	49	10
701-450PG	4.25-4.50	108-114	4	4	70	10
701-556PG	5.25-5.56	121-141	5	5	75	5
701-665PG	6.25-6.65	146-170	6	6	80	5
701-876PG	8.50-8.75	197-222	8	8	85	5

Pipe straps, pipe and conduit clamps and hangers


Conduit and cable clamps



703 Universal clamp

Cat. no.	EMT/rigid (in.)	Conduit O.D.	Material thickness (gauge)	Wt./C lb	Std. ctn.
703-1/2EG	1/2	0.706–0.840	16	13	100
703-3/4EG	3/4	0.932–1.050	14	14	100
703-1EG	1	1.163–1.315	14	15	100
703-1-1/4EG	1 1/4	1.508–1.660	14	18	50
703-1-1/2EG	1 1/2	1.738–1.900	14	28	50
703-2EG	2	2.195–2.375	14	29	50

Diagram



Standard finishes – GoldGalv® (i.e.) 703-1/2
Electrogalvanized (EG suffix) (i.e.) 703-1-1/2EG
One size fits both rigid and electric metal tubing (EMT).
Individually assembled with screw and nut.





Quik Clamp II™



Cat. no.	Dimension A EMT in. (mm)	Dimension A rigid conduit in. (mm)	Quantity per box	Wt./C lb	Design load 1 static load limit lb (kg)	Design load 2 lb (kg)	Design load 3 lb (kg)
TBQC050	1 5/16 (33.5)	1 1/4 (31.5)	100	10	200 (90)	50 (23)	50 (23)
TBQC075	1 3/4 (44.5)	1 11/16 (43)	100	12	200 (90)	50 (23)	50 (23)
TBQC100	1 13/16 (46)	1 3/4 (44.5)	100	13	200 (90)	50 (23)	50 (23)
TBQC125	2 1/8 (54)	2 (51)	50	15	200 (90)	50 (23)	50 (23)
TBQC150	2 3/8 (60.5)	2 3/16 (55.5)	50	16	200 (90)	50 (23)	50 (23)
TBQC200	2 5/8 (66.5)	2 1/2 (63.5)	50	19	200 (90)	50 (23)	50 (23)
TBQC250	3 1/16 (78)	3 1/16 (78)	25	29	350 (158)	50 (23)	50 (23)
TBQC300	3 11/16 (93.5)	3 11/16 (93.5)	25	34	350 (158)	50 (23)	50 (23)
TBQC350	4 3/16 (106.5)	4 3/16 (106.5)	25	38	350 (158)	50 (23)	50 (23)
TBQC400	4 11/16 (119)	4 11/16 (119)	25	42	350 (158)	50 (23)	50 (23)

Diagrams



Design load 1 has a safety factor of 4.
Design loads 2 and 3 have a safety factor of 1.
Standard material electrogalvanized steel.

Pipe straps, pipe and conduit clamps and hangers

Conduit and cable clamps



Cobra® clamp



Diagram	Cat. no.	Rigid EMT trade size (in.)	cond. trade size (in.)	Cable O.D. range (in.)	Static load limit (lb) safety factor = 4	Qty. per box	Wt./C lb	Torque value lb (ft.-lb)	Design load 1		
									Static load limit lb (kg)	Design load 2 lb (kg)	Design load 3 lb (kg)
	CPC025	–	–	0.312–0.600	200	100	8	35	200 (91)	50 (23)	50 (23)
	CPC050	½	½	0.650–0.890	200	100	10	35	200 (91)	50 (23)	50 (23)
	CPC075	¾	¾	0.860–1.110	200	100	12	35	200 (91)	50 (23)	50 (23)
	CPC100	1	1	1.100–1.400	200	100	14	35	200 (91)	50 (23)	50 (23)
	CPC125	1¼	1¼	1.400–1.725	200	50	16	35	200 (91)	50 (23)	50 (23)
	CPC150	1½	1½	1.690–1.980	200	50	18	35	200 (91)	50 (23)	50 (23)
	CPC200	2	2	1.980–2.576	200	50	24	35	200 (91)	50 (23)	50 (23)
	CPC250	2½	2½	2.576–3.060	350*	25	36	35	350 (159)	50 (23)	50 (23)
	CPC300	3	3	3.060–3.626	350*	25	42	35	350 (159)	50 (23)	50 (23)
	CPC350	3½	3½	3.626–4.126	350*	25	46	35	350 (159)	50 (23)	50 (23)
	CPC400	4	4	4.126–4.626	350*	25	50	35	350 (159)	50 (23)	50 (23)

* Aluminum product has a static load of 250 lb

Standard material is commercial-grade, bright electrogalvanized steel.

Aluminum: Add the suffix AL to the catalogue number (i.e. CPC050AL)

Stainless steel: Add the suffix SS6 to catalogue number (i.e.: CPC050SS6). Stainless steel bolt head is hexagonal and slotted only.



Loc-King Cobra™ clamp


- Superior design load capabilities for heavy-duty applications
- Pre-set torque prevents over-tightening
- Anti-vibration nut
- Steel construction with GoldGalv® finish



Diagram	Cat. no.	Rigid EMT trade size (in.)	cond. trade size (in.)	Cable O.D. range (in.)	Static load limit (lb) safety factor = 4	Qty. per box	Wt./C lb	Torque value lb (ft.-lb)	Design load 1		
									Static load limit lb (kg)	Design load 2 lb (kg)	Design load 3 lb (kg)
	LKCPC050	½	½	0.650–0.890	100	15	10	35	300 (136)	50 (23)	50 (23)
	LKCPC075	¾	¾	0.860–1.110	100	16	12	35	300 (136)	50 (23)	50 (23)
	LKCPC100	1	1	1.100–1.400	50	19	14	35	300 (136)	50 (23)	50 (23)
	LKCPC125	1¼	1¼	1.400–1.725	50	23	16	35	300 (136)	50 (23)	50 (23)
	LKCPC150	1½	1½	1.690–1.980	50	27	18	35	300 (136)	50 (23)	50 (23)
	LKCPC200	2	2	1.980–2.576	50	38	24	35	300 (136)	50 (23)	50 (23)
	LKCPC250	2½	2½	2.576–3.060	25	44	36	35	450 (204)	50 (23)	50 (23)
	LKCPC300	3	3	3.060–3.626	25	53	42	35	450 (204)	50 (23)	50 (23)
	LKCPC350	3½	3½	3.626–4.126	25	58	46	35	450 (204)	50 (23)	50 (23)
	LKCPC400	4	4	4.126–4.626	25	66	50	35	450 (204)	50 (23)	50 (23)

Pipe straps, pipe and conduit clamps and hangers

Conduit and cable clamps



CH118 Heavy-duty cable clamp

Diagram	Cat. no.	O.D. of cable or pipe		Rigid cond. (in.)	EMT cond. (in.)	WT./C. lb
		(in.)	(mm)			
	CH118-055EG	0.40–0.55	10–14	–	–	8
	CH118-081EG	0.50–0.81	13–21	½	½	9
	CH118-110EG	0.70–1.10	18–28	¾	¾	17
	CH118-125EG	0.85–1.25	22–27	¾	1	18
	CH118-135EG	1.00–1.35	26–36	1	1	19
	CH118-175EG	1.33–1.75	34–44	1¼	1¼	21
	CH118-205EG	1.65–2.05	42–52	1½	1½	24
	CH118-250EG	2.12–2.50	54–64	2	2	48
	CH118-300EG	2.60–3.00	66–76	2½	2½	54
	CH118-325EG	2.75–3.25	70–82	–	–	65
	CH118-375EG	3.25–3.75	82–94	3	3	105
	CH118-425EG	3.75–4.25	94–110	3½	3½	113
	CH118-475EG	4.25–4.75	110–120	4	4	124

Available in double or triple configurations.

Example: Double – CH128-047EG

Triple – CH138-047EG

Standard finishes – Electrogalvanized (EG)

Stainless steel type 316 clamp comes with type 304 stainless steel hardware.

CB118 Counterbed

EB118 Extended bed

DB118 Double bed

Diagrams	Cat. no.	Wt./C. lb
CB118 Counterbed EB118 Extended bed DB118 Double bed Not sold in pairs	Counterbed	
	CB118-055PG	1
	CB118-090PG	2
	CB118-110PG	3½
	CB118-140PG	4
	CB118-175PG	4½
	CB118-200PG	5
	CB118-250PG	11
	CB118-300PG	13
	Extended bed	
	EB118-047PG	4
	EB118-055PG	4½
	EB118-090PG	6
	EB118-110PG	13½
	EB118-140PG	16
	EB118-175PG	17
	EB118-200PG	20
	EB118-250PG	30
	EB118-300PG	38
	Double bed	
	DB118-047PG	2
	DB118-055PG	2
	DB118-070PG	3

Standard finish – Pregalvanized (PG)

Pipe straps, pipe and conduit clamps and hangers

Conduit and cable clamps



A716 Snap-Guard® cushioned clamp tube series

P716 Snap-Guard® cushioned clamp pipe series

- Assembly consisting of GoldGalv® finish steel clamp with bolt/locknut and cushion
- Secure pipes, tubes and hoses for fluid conductors
- Installation is easy and requires no more time than a simple pipe clamp installation
- Cushion absorbs the shocks and associated vibrations from fluid surges in tubes, pipes and hoses
- It can handle temperatures from 149 °C to -40 °C (300 °F to -40 °F)
- Cushioned clamp assemblies are available individually bagged


	Assembly cat. no.	Tubing		Assembly cat. no.	Standard pipe		
		Tube O.D. (in.)	Wt./C lb		Nominal pipe size (in.)	Std. ctn.	Wt./C lb
Diagram A716 / P716	A716-1/4	¼	10	P716-1/4	¼	25	10
	A716-3/8	⅜	14	P716-3/8	⅜	25	14
	A716-1/2	½	16	P716-1/2	½	25	16
	A716-5/8	⅝	16	P716-3/4	¾	25	18
	A716-3/4	¾	18	P716-1	1	25	22
	A716-7/8	⅞	18	P716-1-1/4	1¼	25	27
	A716-1	1	22	P716-1-1/2	1½	10	36
	A716-1-1/8	1⅛	24	P716-2	2	10	43
	A716-1-1/4	1¼	27	P716-2-1/2	2½	10	49
	A716-1-3/8	1⅜	27	P716-3	3	10	60
	A716-1-1/2	1½	36	P716-3-1/2	3½	10	62
	A716-1-5/8	1⅝	37	P716-4	4	10	94
	A716-1-3/4	1¾	37	–	–	10	–
	A716-1-7/8	1⅞	43	–	–	10	–
	A716-2	2	43	–	–	10	–
	A716-2-1/8	2⅛	44	–	–	10	–
	A716-2-3/8	2⅜	49	–	–	10	–
	A716-2-5/8	2⅝	53	–	–	10	–
	A716-3-1/8	3⅛	62	–	–	10	–
	A716-4-1/8	4⅛	94	–	–	10	–

Pipe straps, pipe and conduit clamps and hangers

Conduit and cable clamps

U716 Two-hole cushioned clamp

- Guides, protects and uniformly spaces line runs.
Low cost, time saving method of attaching tubing and hose to equipment.
- Cushion is built to withstand the effects of most oils, chemical and industrial cleaning compounds, in temperatures from -45 °C to 121 °C (-50 °F to 275 °F). Interlock edge ensures cushion remains in place.
- Attached with two standard fasteners to any flat surface, this clamp eliminates the use of special channels, providing a savings in both space requirements and cost
- Cushioned clamps reduce vibration, shock and noise in fluid systems and eliminates electrolysis

	Assembly cat. no.	Copper and steel tubing O.D. (in.)	Copper water pipe (nom.) (in.)	Normal pipe size (in.)	Std. ctn.	Wt./C lb
Diagram  U716	U716-1/4	1/4	—	—	25	3
	U716-3/8	3/8	1/4	—	25	4
	U716-1/2	1/2	3/8	1/4	25	6
	U716-5/8	5/8	1/2	3/8	25	6
	U716-3/4	3/4	5/8	—	25	7
	U716-7/8	7/8	3/4	1/2	25	7
	U716-1	1	—	—	25	8
	U716-1-1/8	1-1/8	1	—	25	8
	U716-1-1/4	1-1/4	—	—	10	17
	U716-1-3/8	1-3/8	1 1/4	—	10	20
	U716-1-1/2	1-1/2	—	—	10	22
	U716-1-5/8	1-5/8	1 1/2	—	10	23
	U716-2	2	—	—	10	41
	U716-2-1/8	2-1/8	—	—	10	41
	U716-2-3/8	2-3/8	—	—	10	44

Standard finish – GoldGalv®





Pipe straps, pipe and conduit clamps and hangers

Conduit and cable clamps

6H series conduit and pipe hanger

Features

- Accommodates ½ in. through 4 in. EMT or rigid conduit
- Can be used for either vertical or horizontal installation
- 6HTB Series have a built-in nut so there are fewer parts to handle or drop
- Installs easily with a screwdriver

Diagrams	Cat. no.	Conduit size		Wt./C. lb
		Rigid (in.)	EMT (in.)	
	6H0	¾–½	½	5
	6H0-B	¾–½	½	7
	6H0-T	¾–½	½	5
	6H0-TB	¾–½	½	6
	6H1	¾	¾	6
	6H1-B	¾	¾	7
	6H1-T	¾	¾	6
	6H1-TB	¾	¾	7
	6H2	1	1	7
	6H2-B	1	1	9
	6H2-1/2	–	1½	8
	6H2-1/2-B	–	1½	10
	6H3-SC	1¼	1½	8
	6H3-B	1¼	1½	10
	6H3-TB	1¼	1½	10
	6H4	1½	–	17
	6H4-B	1½	–	19
	6H4-TB	1½	–	19
	6H5	2	2	24
	6H5-B	2	2	26
	6H5-TB	2	2	26
	6H6	2½	2½	28
	6H6-B	2½	2½	30
	6H7	3	3	36
	6H7-B	3	3	38
	6H8	3½	3½	39
	6H8-B	3½	3½	41
	6H9	4	4	44
	6H9-B	4	4	47

Standard finish – Electrogalvanized (no suffix)

Pipe straps, pipe and conduit clamps and hangers

Conduit and cable clamps






When fastening wire bundles, cables or hoses to framing channels, you can cut costs considerably by using this mounting base. It is made of smooth, weather-resistant nylon and designed to protect cable insulation and hoses from the wear or damage that can occur with metal clamps. The mounting base may be used for both indoor or outdoor applications. It installs in the framing channel with a simple push and twist. It requires

no screws, nuts or tools. The mounting base fits all 1½ in. and 1⅝ in. channels regardless of channel depth. Ty-Rap® and Ty-Fast® cable ties can be ordered separately.

- Installs with a push and twist
- Designed for indoor or outdoor use
- Smooth design protects cable insulation
- Takes range of cable diameters

Cat. no.	Channel size (in.)	Maximum tie width accom. (in.)	Unit qty.	Std. pkg.
TC5363X	1½ and 1⅝	0.301	50	250

Installation




Pipe straps, pipe and conduit clamps and hangers

Conduit and cable clamps

WS716 Maple hardwood saddle
Std. pack 10

	Cat. no.	Dimensions					
		Depth		Width		Height	
	Hardwood paraffin imp.	(in.)	(mm)	(in.)	(mm)	(in.)	(mm)
	WS716-3/4	¾	19.0	3	76.2	1¾	44.4
	WS716-1	1	25.4	3	76.2	1¾	44.4
	WS716-1-1/4	1¼	31.7	3½	88.9	2	50.8
	WS716-1-1/2	1½	38.1	3½	88.9	2	50.8
	WS716-1-3/4	1¾	44.4	4	101.6	2¼	57.1
	WS716-2	2	50.8	4	101.6	2¼	57.1
	WS716-2-1/4	2¼	57.1	4½	114.3	2½	63.5
	WS716-2-1/2	2½	63.5	4½	114.3	2½	63.5
	WS716-2-3/4	2¾	69.8	5	127	2¾	69.8
	WS716-3	3	76.2	5	127	2¾	69.8
	WS716-3-1/4	3¼	82.5	5½	139.7	2¾	76.2
	WS716-3-1/2	3½	88.9	5½	139.7	3	76.
	WS716-3-3/4	3¾	95.2	6	152.4	3¼	82.5
	WS716-4	4	101	6	152.4	3¼	82.5
	WS716-4-1/2	4½	114.3	6½	165.1	3½	88.9
	WS716-5	5	127	7	177.8	3¾	95.2
	WS716-5-1/2	5½	139.7	7½	190.5	4	101.6
	WS716-6	6	152.4	8	203.2	4¼	107.9
	WS716-6-1/2	6½	165.1	8½	215.9	4½	114.3
	WS716-7	7	177.8	9	228.6	4¾	120.6

Diagram



Pipe straps, pipe and conduit clamps and hangers


Conduit and cable clamps

AB880 3 in. Porcelain saddle

AB881 4 in. Porcelain saddle




Diagram



Cat. no.	A (in.)	Max. cable diam. (in.)	Wt./C lb
AB880	3	3	73
AB881	4	4 1/2	104


C755 Porcelain cable clamps



Cat. no.	Hole size (in.)	A (in.)	Wt./C lb
C755-1A	3/8	1 1/16	50
C755-1B	1/2	1 1/16	50
C755-1C	5/8	1 1/16	50
C755-2	3/4	2 5/32	91
C755-2A	7/8	2 5/32	90
C755-2B	1	2 5/32	85
C755-2C	1 1/8	2 5/32	82
C755-3	1 1/4	2 5/8	114
C755-3A	1 3/8	2 5/8	110
C755-3B	1 1/2	2 5/32	105
C755-3C	1 5/8	2 5/8	102
C755-4	1 3/4	3 3/4	220
C755-4A	1 7/8	3 3/4	214
C755-4B	2	3 3/4	205
C755-4C	2 1/8	3 3/4	200
C755-5	2 1/4	4 1/4	260
C755-5A	2 3/8	4 1/4	250
C755-5B	2 1/2	4 1/4	243
C755-5C	2 5/8	4 1/4	240
C755-6	2 3/4	4 3/4	250
C755-6A	2 7/8	4 3/4	240
C755-6B	3	4 3/4	230
C755-6C	3 1/8	4 3/4	220

Cat. no.	Hole size (in.)	A (in.)	Wt./C lb
C755-7	3 1/4	5 13/16	340
C755-7A	3 3/8	5 13/16	330
C755-7B	3 1/2	5 13/16	318
C755-7C	3 5/8	5 13/16	387
C755-8	3 3/4	6 7/8	565
C755-8A	3 7/8	6 7/8	550
C755-8B	4	6 7/8	535
C755-8C	4 1/8	6 7/8	520
C755-8D	4 1/4	6 7/8	490
C755-8E	4 3/8	6 7/8	475
C755-8F	4 1/2	6 7/8	460

Diagram



Standard finish – GoldGalv® with bronze hardware
Also fits 1 1/2 in. wide channel.
For minimum order quantities, contact your Regional Sales Office.


Pipe straps, pipe and conduit clamps and hangers

Conduit and cable clamps




For use with 701 O.D. tubing and pipe clamp. To determine 701 clamp size add ¼ in. to O.D. tube size to allow for the cushioned strip material.


S716 Cushioned strip for isolation and vibration applications
¼ in. markings for fast measuring and cutting. Measurement chart is printed on back of carton. 20 feet included in each carton. Prevent metal-to-metal contact with the cushioned strip material. It aids in sound insulation, shock



absorption and protects against corrosion, distortion and abrasion. Cushioned strip material is designed for optimal use between -1 °C and 149 °C (30 °F and 300 °F). Cushioned strip material combined with the Superstrut 701 pipe strap can handle clamping assignments from ¼ in. to 6 in.



Order 701 clamp separately.



Carbon Steel

C708U Short strap for channel or wall mounting

	Pipe size (in.)	A (in.)	B (in.)	Thickness (in.)	Width (in.)	Hole size (in.)	Design load lb	Wt./C lb
Diagram	½	2⅞	2	⅛	1⅝	⅜ ₃₂	650	23
	¾	3⅛ ₁₆	2⅜ ₁₆	⅛	1⅝	⅜ ₃₂	650	26
	1	3⅝	2½	⅛	1⅝	⅜ ₃₂	650	31
	1¼	3⅞ ₁₆	2⅞ ₁₆	⅛	1⅝	⅜ ₃₂	650	35
	1½	3⅞ ₁₆	3⅛ ₁₆	⅛	1⅝	⅜ ₃₂	650	39
	2	5¾	4⅞	¼	1⅝	⅞ ₁₆	650	94
	2½	6⅜ ₁₆	4⅞ ₁₆	¼	1⅝	⅞ ₁₆	1,000	114
	3	6⅞ ₁₆	5⅜ ₁₆	¼	1⅝	⅞ ₁₆	1,000	133
	3½	7⅞ ₁₆	5⅞ ₁₆	¼	1⅝	⅞ ₁₆	1,000	152
	4	7⅞ ₁₆	6⅜ ₁₆	¼	1⅝	⅞ ₁₆	1,200	176
	5	8⅞	7¼	¼	1⅝	⅞ ₁₆	1,200	198
	6	9⅞ ₁₆	8⅞ ₁₆	¼	1⅝	⅞ ₁₆	1,200	246

Standard finish – GoldGalv®
Example: C708U-1/2
No clearance between pipe and channel.

Pipe straps, pipe and conduit clamps and hangers

Conduit and cable clamps




Standard

C711 "J" Pipe hanger

Pipe size (in.)	A rod size (in.)	B (in.)	C (in.)	Overall dimension D (in.)	E (in.)	F (in.)	Bolt size (in.)	G (in.)	Thickness	Width (in.)	Max. rec. load lb	Approx. Wt./C lb
1/2	3/8	2 5/8	1 3/4	7/16	1 1/2	1 15/16	1/4	3 7/32	12 ga	3/4	400	18
3/4	3/8	2 7/8	1 7/8	7/16	1 11/16	2 1/8	1/4	3 1/2	12 ga	3/4	400	21
1	3/8	2 15/16	1 15/16	7/16	1 13/16	2 5/16	1/4	3 11/16	12 ga	3/4	400	22
1 1/4	3/8	3 1/4	2	7/16	2 1/16	2 5/8	1/4	4 1/8	12 ga	3/4	400	25
1 1/2	3/8	3 9/16	2 3/16	7/16	2 7/16	2 7/8	1/4	4 5/8	12 ga	3/4	400	27
2	3/8	3 11/16	2 1/8	7/16	2 9/16	3 1/16	1/4	5	12 ga	3/4	400	29
2 1/2	1/2	4 7/16	2 7/16	9/16	3 3/16	3 5/8	3/8	6	12 ga	1 1/4	500	64
3	1/2	4 13/16	2 9/16	9/16	3 1/2	4 1/16	3/8	6 21/32	12 ga	1 1/4	500	72
3 1/2	1/2	5 1/8	2 5/8	9/16	3 3/4	4 3/8	3/8	7 1/16	3/16	1 1/4	500	84
4	5/8	6 1/8	3 3/16	9/16	4 5/8	5 1/16	3/8	8 9/16	3/16	1 1/4	550	138
5	5/8	6 3/4	3 1/4	9/16	5 1/16	5 5/8	3/8	9 27/32	3/16	1 1/4	550	162
6*	3/4	7 3/4	3 9/16	9/16	5 13/16	6 5/8	3/8	11 1/4	3/16	1 1/4	600	249
8*	7/8	9 1/16	3 11/16	9/16	6 15/16	8	3/8	13 11/16	3/16	1 1/4	760	291

Diagram



*Hangers 6 in. and over have hole instead of slot.

Standard finishes – GoldGalv®, electrogalvanized (EG)

Complies with specification MSS SP69, Type 5. Hole provided for side mounting to wall as bracket.

Example: C711-1/2


Pipe straps, pipe and conduit clamps and hangers

Conduit and cable clamps



C727 Adjustable ring


Tube size (in.)	Rod size (in.)	A (in.)	B (in.)	C (in.)	Thickness	Width (in.)	Approx max. rec. load	Wt./C lb
½	⅜	3⅝	2⅞	1⅝	16 ga	1	400	9
¾	⅜	3⅝	2½	1⅝	16 ga	1	400	9
1	⅜	3⅝	2⅞	1⅝	16 ga	1	400	9
1¼	⅜	3¾	2⅞	1⅝	16 ga	1	400	10
1½	⅜	3⅞	2⅞	1	16 ga	1	400	11
2	⅜	4¼	3	1	16 ga	1	400	12
2½	½*	5¾	4¼	1⅝	14 ga	1⅜ ₁₆	600	28
3	½*	6	4⅞	1¼	14 ga	1⅜ ₁₆	600	30
3½	½*	7⅜	5¼	2⅞	14 ga	1⅜ ₁₆	600	34
4	⅝*	7⅜	5	2⅞	14 ga	1¼	1,000	37
5	⅝*	9	6⅞	2¼	14 ga	1¼	1,250	83
6	¾**	9⅜	6½	1⅞	14 ga	1¼	1,250	95



*⅜ in. nut is used when NFPA rod sizing is requested.
**½ in. nut is used when NFPA rod sizing is requested.
Standard finish – Pregalvanized (no suffix)
Carbon steel. For suspension of non-insulated pipe lines. Complies with specification MSS SP69, Type 10.
Example: C727-1/2


Pipe straps, pipe and conduit clamps and hangers

Pipe hangers



C710 Adjustable clevis hanger

Pipe size (in.)	Size of steel (in.)		A (in.)	B (in.)	C (in.)	D (in.)	E (in.)	F (in.)	Max. rec. load, lb	Wt./C lb
	Upper	Lower								
1/2	1/8 x 1	1/8 x 1	3/8	1 11/16	2 1/8	2 1/2	7/8	7/16	610	30
3/4	1/8 x 1	1/8 x 1	3/8	1 7/8	2 7/16	2 1/2	1	1/2	610	32
1	1/8 x 1	1/8 x 1	3/8	2 1/8	2 3/16	2 1/2	1 1/4	5/8	610	36
1 1/4	1/8 x 1	1/8 x 1	3/8	2 9/16	3 7/16	2 1/2	1 3/4	7/8	610	42
1 1/2	1/8 x 1	1/8 x 1	3/8	3	4	2 1/2	2 1/8	1 1/16	610	55
2	1/8 x 1	1/8 x 1	3/8	3 11/16	4 7/8	2 1/2	2 15/16	1 5/8	610	60
2 1/2	3/16 x 1 1/4	3/16 x 1 1/4	1/2	4 11/16	6 1/8	3	3 3/16	2	1,130	115
3	3/16 x 1 1/4	3/16 x 1 1/4	1/2	4 3/4	6 9/16	3	3 7/8	1 3/4	1,130	132
3 1/2	3/16 x 1 1/4	3/16 x 1 1/4	1/2	4 15/16	6 15/16	3	4 1/16	1 3/4	1,130	156
4	1/4 x 1 1/4	3/16 x 1 1/4	5/8	5 9/16	7 13/16	3 1/2	4 1/2	1 15/16	1,430	190
5	1/4 x 1 1/4	3/16 x 1 1/4	5/8	6 3/16	9	3 1/2	5 5/8	1 3/4	1,430	240
6	1/4 x 1 1/2	3/16 x 1 1/2	3/4	6 13/16	10 5/8	4	5 5/8	1 7/8	1,940	320
8	1/4 x 1 3/4	3/16 x 1 3/4	7/8	8 5/16	12 5/8	4 1/4	7	2 1/8	1,940	500



Standard finishes – GoldGalv®, electrogalvanized (EG)
Complies with specification MSS SP69, Type 1.
Example: C710-1/2EG


Pipe straps, pipe and conduit clamps and hangers

Pipe hangers



CL710 Light-duty adjustable clevis hanger

Pipe size (in.)	Thickness of steel (in.)		A (in.)	B (in.)	C (in.)	D (in.)	E (in.)	F (in.)	Max. rec. load, lb	Wt./C lb
	Upper	Lower								
3/8	16 ga. x 7/8	16 ga. x 7/8	3/8	1 1/8	2 3/16	2 1/2	1 1/4	9/16	150	12
1/2	16 ga. x 7/8	16 ga. x 7/8	3/8	1 3/4	2 3/16	2 1/2	1 1/8	9/16	150	13
3/4	16 ga. x 7/8	16 ga. x 7/8	3/8	1 7/8	2 1/4	2 1/2	1 1/4	1/2	250	15
1	16 ga. x 7/8	16 ga. x 7/8	3/8	2 3/16	2 3/4	2 1/2	1 1/2	3/4	250	18
1 1/4	16 ga. x 7/8	16 ga. x 7/8	3/8	2 5/8	3 3/8	2 1/2	1 3/4	1	250	20
1 1/2	13 ga. x 7/8	13 ga. x 7/8	3/8	3	3 7/8	2 1/2	2 1/4	1 3/16	250	30
2	13 ga. x 7/8	13 ga. x 7/8	3/8	3 9/16	4 3/4	2 1/2	2 13/16	1 5/8	250	38
2 1/2	1/8 x 1 1/4	1/8 x 1 1/4	1/2	4	5 1/2	3	3 1/4	1 3/8	350	80
3	1/8 x 1 1/4	1/8 x 1 1/4	1/2	4 9/16	6 1/2	3	3 9/16	1 1/2	350	89
3 1/2	1/8 x 1 1/4	1/8 x 1 1/4	1/2	5	7	3	4 1/8	1 3/4	350	106
4	3/16 x 1 1/4	1/8 x 1 1/4	1/2	5 1/4	7 1/2	3 1/2	4 1/4	1 7/8	400	146
6	1/4 x 1 1/2	3/16 x 1 1/2	3/4	6 13/16	10 3/8	4	5 5/8	1 7/8	1,940	320
8	1/4 x 1 3/4	3/16 x 1 3/4	7/8	8 5/16	12 5/8	4 1/4	7	2 1/8	1,940	500



Standard finishes – GoldGalv®, Bare (B), electrogalvanized (EG), fiberglass (FG).
Carbon steel
Used on non-insulated, stationary pipelines. A lock nut above the clevis yoke is required for full rated load.
Example: CL710-3/8B

Pipe straps, pipe and conduit clamps and hangers

Pipe hangers




M718 Split pipe ring

	Pipe size (in.)	A (in.)	B (in.)	Max. rec. load, lb	Wt./C approx.
Diagram	$\frac{3}{8}$	$\frac{3}{8}$	$1\frac{13}{16}$	180	10
	$\frac{1}{2}$	$\frac{3}{8}$	$\frac{7}{8}$	180	13
	$\frac{3}{4}$	$\frac{3}{8}$	1	180	14
	1	$\frac{3}{8}$	$1\frac{1}{8}$	180	16
	$1\frac{1}{4}$	$\frac{3}{8}$	$1\frac{5}{16}$	180	22
	$1\frac{1}{2}$	$\frac{3}{8}$	$1\frac{7}{16}$	180	24
	2	$\frac{3}{8}$	$1\frac{11}{16}$	180	31
	$2\frac{1}{2}$	$\frac{1}{2}$	$2\frac{1}{8}$	300	60
	3	$\frac{1}{2}$	$2\frac{7}{16}$	300	74
	4	$\frac{1}{2}$	$2\frac{15}{16}$	300	116

Standard finishes – Bare (B) or electrogalvanized (EG) malleable iron.

For suspension of non-insulated, stationary pipelines.

Example: M718-3/8B



C725 Medium pipe clamp

	Pipe size (in.)	B (in.)	C (in.)	D (in.)	E (in.)	F (in.)	H (in.)	S (in.)	Max. rec. load, lb	Wt./C approx.
Diagram	$\frac{1}{2}$	1	$\frac{7}{16}$	$1\frac{3}{8}$	1	$\frac{5}{16}$	$1\frac{1}{2}$	$\frac{1}{8} \times 1$	500	29
	$\frac{3}{4}$	$1\frac{1}{8}$	$\frac{7}{16}$	$1\frac{3}{4}$	$1\frac{1}{4}$	$\frac{5}{16}$	$1\frac{3}{4}$	$\frac{1}{8} \times 1$	500	32
	1	$1\frac{1}{4}$	$\frac{7}{16}$	$1\frac{13}{16}$	$1\frac{1}{4}$	$\frac{5}{16}$	$1\frac{13}{16}$	$\frac{1}{8} \times 1$	500	33
	$1\frac{1}{4}$	$1\frac{7}{16}$	$\frac{7}{16}$	2	$1\frac{7}{16}$	$\frac{5}{16}$	2	$\frac{1}{8} \times 1$	500	38
	$1\frac{1}{2}$	$1\frac{5}{8}$	$\frac{1}{2}$	$2\frac{1}{16}$	$1\frac{1}{2}$	$\frac{5}{16}$	$2\frac{1}{4}$	$\frac{1}{8} \times 1$	715	39
	2	$2\frac{1}{8}$	$\frac{9}{16}$	$3\frac{3}{8}$	$2\frac{1}{4}$	$\frac{1}{2}$	3	$\frac{1}{4} \times 1$	1,040	117
	$2\frac{1}{2}$	$2\frac{5}{16}$	$\frac{9}{16}$	$3\frac{5}{16}$	$2\frac{1}{2}$	$\frac{1}{2}$	$3\frac{3}{4}$	$\frac{1}{4} \times 1$	1,040	128
	3	$2\frac{3}{4}$	$\frac{9}{16}$	$3\frac{3}{4}$	$2\frac{3}{4}$	$\frac{1}{2}$	$3\frac{5}{8}$	$\frac{1}{4} \times 1$	1,040	140
	$3\frac{1}{2}$	$3\frac{3}{8}$	$\frac{5}{8}$	$3\frac{3}{4}$	3	$\frac{1}{2}$	$3\frac{7}{8}$	$\frac{1}{4} \times 1$	1,040	145
	4	$3\frac{5}{16}$	$\frac{3}{4}$	$4\frac{1}{4}$	$3\frac{5}{16}$	$\frac{5}{8}$	$4\frac{1}{4}$	$\frac{1}{4} \times 1\frac{1}{4}$	1,040	238
	6	$4\frac{7}{8}$	$\frac{7}{8}$	$5\frac{7}{8}$	5	$\frac{3}{4}$	$5\frac{3}{4}$	$\frac{3}{8} \times 1\frac{1}{2}$	1,615	542
	8	6	1	7	$6\frac{5}{8}$	$\frac{3}{4}$	$6\frac{7}{8}$	$\frac{3}{8} \times 1\frac{1}{2}$	1,615	651
	10	$7\frac{1}{16}$	1	$8\frac{3}{16}$	$7\frac{1}{16}$	$\frac{7}{8}$	$8\frac{7}{16}$	$\frac{1}{2} \times 2$	2,490	1,360
	12	$8\frac{1}{4}$	1	$9\frac{9}{16}$	$8\frac{7}{16}$	$\frac{7}{8}$	$9\frac{3}{8}$	$\frac{1}{2} \times 2$	2,490	1,605

Based on the allowable stresses shown in ANSI Code for pressure piping.

For sizes 14 to 24, contact your regional sales office.

Standard finishes – GoldGalv®, Bare (B), electrogalvanized (EG)

carbon steel. For suspension of pipelines where little or no insulation is required.

Complies with specification MSS SP69, Type 23.

Example: C725-1/2B

Pipe straps, pipe and conduit clamps and hangers

Pipe hangers



C720 Riser clamp

	Pipe size (in.)	A (in.)	Thickness (in.)	Width (in.)	Bolt (in.)	Max. rec. load, lb	Wt./ea. approx.
Diagram	1/2	9 1/8	3/16	1	3/8 x 1 1/2	220	1,01
	3/4	9 1/4	3/16	1	3/8 x 1 1/2	220	1,06
	1	9 3/8	3/16	1	3/8 x 1 1/2	220	1,07
	1 1/4	9 7/8	1/4	1	3/8 x 1 1/2	250	1,12
	1 1/2	10	1/4	1	3/8 x 1 1/2	250	1,20
	2	10 1/2	1/4	1	3/8 x 1 1/2	300	1,25
	2 1/2	11 1/16	1/4	1	3/8 x 1 1/2	400	1,67
	3	11 13/16	1/4	1	3/8 x 1 1/2	500	1,81
	3 1/2	13	1/4	1	1/2 x 1 1/2	600	2,12
	4	13 1/2	1/4	1	1/2 x 1 1/2	750	2,22
	5	14	1/4	1 1/2	1/2 x 1 3/4	1,500	3,44
	6	15 3/16	1/4	1 1/2	1/2 x 1 3/4	1,600	3,65
	8	19	3/8	1 1/2	3/4 x 2 1/2	2,500	7,24

Standard riser

Standard finishes – GoldGalv®, bare (B)
Available in sizes 1/2 in. through 10 in.
Complies with specification MSS SP69, Type 8.
Example: C720-1-1/2B




C726 Double bolt pipe clamp

	Pipe size (in.)	B (in.)	C (in.)	D (in.)	E (in.)	F (in.)	H (in.)	S (in.)	Max. rec. load, lb	Wt./C approx.
Diagram	3/4	1 1/16	5/8	3 3/16	2 1/2	3/8	1 11/16	3/16 x 1	950	66
	1	1 1/2	5/8	3 3/4	2 1/2	3/8	2 1/16	3/16 x 1	950	69
	1 1/4	1 1/2	3/4	3 11/16	2 7/8	3/8	2 1/4	3/16 x 1	950	75
	1 1/2	1 13/16	1 1/16	4 7/8	3 3/4	5/8	2 13/16	1/4 x 1 1/4	1,545	181
	2	2 1/4	1 1/16	5 11/16	4 1 1/16	5/8	3 3/16	1/4 x 1 1/4	1,545	200
	2 1/2	2 5/8	1 1/16	6 1/2	5 3/8	5/8	3 1/2	1/4 x 1 1/4	1,545	232
	3	2 3/4	1 1/16	6 7/8	6	5/8	3 3/4	1/4 x 1 1/4	1,545	258
	3 1/2	3	1 1/16	7 1/16	6 3/16	5/8	4	1/4 x 1 1/4	1,545	264
	4	3 3/8	1 1/16	7 7/8	6 1/2	3/4	4 1/2	3/8 x 2	2,500	750
	5	3 15/16	1 1/16	8 7/8	7	3/4	5	3/8 x 2	2,500	813
	6	4 3/4	1 1/16	9 15/16	8 3/16	1	6 1/8	3/8 x 2 1/2	2,865	1311
	8	5 3/4	1 1/16	10 15/16	9 3/16	1	7 7/8	3/8 x 2 1/2	2,865	1467


Standard finish – bare (B)
carbon steel. For the suspension of insulated pipelines.
Normally used with weldless eye nut.
Example: C726-1/2B

Pipe straps, pipe and conduit clamps and hangers


Seismic bracing




01




02



03



04



05

01 **C749N-5/8 Seismic brace**
Standard finish
– GoldGalv®
1650 lb load
Safety factor 3
Wt./C 61 lb

02 **C749N-7/8 Seismic brace**
Standard finish
– GoldGalv®
1650 lb load
Safety factor 3
Wt./C 56 lb

03 **C749N-1 1/8 Seismic brace**
Standard finish
– GoldGalv®
1650 lb load
Safety factor 3
Wt./C 74 lb

04 **C749N-1 1/4 Seismic brace**
Standard finish
– GoldGalv®
1650 lb load
safety factor 3
Wt./C 72 lb

05 **ES142**
Standard finish
– GoldGalv®

Cat. no.	Bolt dia.	Wt./C lb
ES-142-1/2 x 1-1/2	1/2	21

Seismic bracing rod
stiffener connector.
Wt./C 21 lb
All dimensions shown are in.

All braces have
plastisol coating
on the flat member.
Plastisol insulates
against vibration noise
transmission and
eliminates rattle at
the connection points.